

**CRIMPFIX LS PZ3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

**General ordering data**

Version	Automatic stripper and crimper
Order No.	<a href="#">9025300000</a>
Type	CRIMPFIX LS PZ3
GTIN (EAN)	4008190380335
Qty.	1 pc(s).

## CRIMPFIX LS PZ3

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	330 mm	Depth (inches)	12.992 inch
Height	460 mm	Height (inches)	18.11 inch
Width	390 mm	Width (inches)	15.354 inch
Net weight	35,000 g		

## PW65 maintenance - automatic stripping/crimping

Compressed-air connection	5 - 5.5 bar	Consumables	loose cable lugs
Crimping length	6/8/10 mm	Drive	Electropneumatic
Electrical connection	100-240 V / 50/60 Hz / 110 VA	Length of wire-end ferrule	12/14/16 mm
Pulse time	approx. 1 s	Stripping range	0.5 - 2.5 mm <sup>2</sup> (~AWG 20-14)
Wire end ferrules cross-section, max.	2.5 mm <sup>2</sup>	Wire end ferrules cross-section, min.	0.5 mm <sup>2</sup>

## Classifications

ETIM 6.0	EC002778	ETIM 7.0	EC002778
ETIM 8.0	EC002778	ETIM 9.0	EC002778
ECLASS 9.0	17-13-01-01	ECLASS 9.1	17-13-01-01
ECLASS 10.0	17-13-01-01	ECLASS 11.0	17-13-01-01
ECLASS 12.0	17-13-01-01	ECLASS 13.0	17-13-01-01

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	d2df479e-2b79-4e98-adc7-b03577df98ae

## Approvals

Approvals



ROHS	Conform
------	---------

## Downloads

User Documentation	<a href="#">Manual</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>