

**H0,5/16 OR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

- supplied loose in polybag
- Weidmüller colour code
- DIN colour code

**General ordering data**

Version	Wire-end ferrule, Standard, 12 mm, 10 mm, orange
Order No.	<a href="#">9025870000</a>
Type	H0,5/16 OR
GTIN (EAN)	4008190025045
Qty.	500 pc(s).
Packaging	loose

## H0,5/16 OR

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	0.078 g
------------	---------

## Technical data

Description of article	Wire end ferrule with plastic collar, orange	Version	Standard
------------------------	--	---------	----------

## Wire-end ferrules

Collar diameter (D2)	2.6 mm	Colour code	Weidmueller
Conductor cross-section	0.5 mm <sup>2</sup>	Contact surface diameter (D1)	1 mm
Contact surface length (L2)	10 mm	L1 in mm	16 mm
Metal sleeve thickness (S1)	0.15 mm	Plastic collar thickness (S2)	0.25 mm
Stripping length	12 mm	Wire connection cross section AWG, max.	AWG 20

## Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ETIM 9.0	EC000005
ECLASS 9.0	27-40-02-01	ECLASS 9.1	27-40-02-01
ECLASS 10.0	27-40-02-01	ECLASS 11.0	27-40-02-01
ECLASS 12.0	27-40-02-01	ECLASS 13.0	27-40-02-01

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
User Documentation	<a href="#">Technical information - EN</a> <a href="#">Technical information - DE</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**H0,5/16 OR**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Drawing

