

AM 12**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Sheathing stripper for PVC cables

General ordering data

Version	Tools, Sheathing strippers
Order No.	9030060000
Type	AM 12
GTIN (EAN)	4008190337827
Qty.	1 pc(s).

AM 12**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	10 mm	Depth (inches)	0.394 inch
Height	46 mm	Height (inches)	1.811 inch
Width	97 mm	Width (inches)	3.819 inch
Net weight	32.42 g		

Technical data

Description of article	Sheathing stripper for UTP and STP data cables
------------------------	--

Stripping tools

Cable type	UTP and STP data cables	Conductor cross-section, min.	0.25 mm ²
Copper cable - flexible, max.	4 mm ²	Cut depth	adjustable
Max. conductor diameter	12.5 mm	Min. conductor diameter	0.5 mm
Stripping range AWG, max.	11 AWG	Stripping range AWG, min.	18 AWG
UTP und STP data cables, max. diameter 8 mm			

Classifications

ETIM 6.0	EC000163	ETIM 7.0	EC000163
ETIM 8.0	EC000163	ETIM 9.0	EC000163
ECLASS 9.0	21-04-90-90	ECLASS 9.1	21-04-37-06
ECLASS 10.0	21-04-90-90	ECLASS 11.0	21-04-90-90
ECLASS 12.0	21-04-90-90	ECLASS 13.0	21-04-90-90

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Downloads

User Documentation	Manual
Catalogues	Catalogues in PDF-format
Brochures	

AM 12

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Example of use



Example of use



Example of use

