

H2,5/16 TS GR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

- Polypropylene conical cable entry funnel
 - Heat-resistant up to 105°C
- For conductors from 0.5 – 10.0 mm² (AWG 20-7)
Material: E-Cu, tin galvanised
Dimensional tolerance acc. to DIN 46228 sect. 4

General ordering data

| | |
|------------|--|
| Version | Wire-end ferrule, Standard, 12 mm, 10 mm, grey |
| Order No. | 9036210000 |
| Type | H2,5/16 TS GR |
| GTIN (EAN) | 4032248068005 |
| Qty. | 500 pc(s). |
| Packaging | loose |

H2,5/16 TS GR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | |
|------------|---------|
| Net weight | 0.164 g |
|------------|---------|

Technical data

| | | | |
|------------------------|--|---------|----------|
| Description of article | Wire end ferrule with plastic collar, special size, grey | Version | Standard |
|------------------------|--|---------|----------|

Wire-end ferrules

| | | | |
|-------------------------------|-------------|---|---------------------|
| Collar diameter (D2) | 4.4 mm | Conductor cross-section | 2.5 mm ² |
| Contact surface diameter (D1) | 2.2 mm | Contact surface length (L2) | 10 mm |
| L1 in mm | 16 mm | Metal sleeve thickness (S1) | 0.15 mm |
| Military designation | T 20A 023 A | Plastic collar thickness (S2) | 0.25 mm |
| Stripping length | 12 mm | Wire connection cross section AWG, max. | AWG 14 |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000005 | ETIM 7.0 | EC000005 |
| ETIM 8.0 | EC000005 | ETIM 9.0 | EC000005 |
| ECLASS 9.0 | 27-40-02-01 | ECLASS 9.1 | 27-40-02-01 |
| ECLASS 10.0 | 27-40-02-01 | ECLASS 11.0 | 27-40-02-01 |
| ECLASS 12.0 | 27-40-02-01 | ECLASS 13.0 | 27-40-02-01 |

Approvals

Approvals



| | |
|-----------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E354986 |

Downloads

| | |
|--------------------|--|
| User Documentation | Technical information - EN Technical information - DE |
| Catalogues | Catalogues in PDF-format |

H2,5/16 TS GR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing

