


**H4,0/15TS OR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

- Polypropylene conical cable entry funnel
  - Heat-resistant up to 105°C
- For conductors from 0.5 – 10.0 mm<sup>2</sup> (AWG 20-7)  
Material: E-Cu, tin galvanised  
Dimensional tolerance acc. to DIN 46228 sect. 4

**General ordering data**

Version	Wire-end ferrule, Standard, 10 mm, 8 mm, orange
Order No.	<a href="#">9036230000</a>
Type	H4,0/15TS OR
GTIN (EAN)	4032248068029
Qty.	500 pc(s).
Packaging	loose

## H4,0/15TS OR

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	0.224 g
------------	---------

## Technical data

Description of article	Wire end ferrule with plastic collar, special size, or-ange	Version	Standard
------------------------	---	---------	----------

## Wire-end ferrules

Collar diameter (D2)	4.8 mm	Conductor cross-section	4 mm <sup>2</sup>
Contact surface diameter (D1)	2.8 mm	Contact surface length (L2)	8 mm
L1 in mm	15 mm	Metal sleeve thickness (S1)	0.2 mm
Military designation	T 20A 023 A	Plastic collar thickness (S2)	0.3 mm
Stripping length	10 mm	Wire connection cross section AWG, max.	AWG 12

## Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ETIM 9.0	EC000005
ECLASS 9.0	27-40-02-01	ECLASS 9.1	27-40-02-01
ECLASS 10.0	27-40-02-01	ECLASS 11.0	27-40-02-01
ECLASS 12.0	27-40-02-01	ECLASS 13.0	27-40-02-01

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E354986

## Downloads

User Documentation	<a href="#">Technical information - EN</a> <a href="#">Technical information - DE</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**H4,0/15TS OR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Drawings****Drawing**