

CRIMPER 25 N D4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Crimping tools for non-insulated connectors**

Rolled cable lugs, tubular cable lugs, terminal pins, parallel and serial connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

| | |
|------------|--|
| Version | Tools, Crimping tool for contacts, 10mm ² , 25mm ² |
| Order No. | 9040460000 |
| Type | CRIMPER 25 N D4 |
| GTIN (EAN) | 4008190461508 |
| Qty. | 1 pc(s). |

CRIMPER 25 N D4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|--------|----------------|------------|
| Width | 250 mm | Width (inches) | 9.842 inch |
| Net weight | 550 g | | |

Technical data

| | | | |
|------------------------|---|---------|---|
| Description of article | Crimping tool for non-insulated connectors, 10-25 mm ² | Version | Mechanical, without interchangeable inserts |
|------------------------|---|---------|---|

Description of contact

| | | | |
|-----------------------------------|------------------------|-----------------------------------|--------------------|
| Conductor cross-section, max. AWG | AWG 4 | Conductor cross-section, min. AWG | AWG 8 |
| Crimping range, max. | 25 mm ² | Crimping range, min. | 10 mm ² |
| Type of contact | Uninsulated connection | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000168 | ETIM 7.0 | EC000168 |
| ETIM 8.0 | EC000168 | ETIM 9.0 | EC000168 |
| ECLASS 9.0 | 21-04-38-11 | ECLASS 9.1 | 21-04-38-11 |
| ECLASS 10.0 | 21-04-38-11 | ECLASS 11.0 | 21-04-38-11 |
| ECLASS 12.0 | 21-04-38-11 | ECLASS 13.0 | 21-04-38-11 |

Environmental Product Compliance

| | |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
|------------|--|