

STRIPPER 6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

Version	Stripping and cutting tool
Order No.	9046240000
Type	STRIPPER 6
GTIN (EAN)	4032248298648
Qty.	1 pc(s).

STRIPPER 6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	19 mm	Depth (inches)	0.748 inch
Height	87 mm	Height (inches)	3.425 inch
Width	200 mm	Width (inches)	7.874 inch
Net weight	180 g		

Technical data

Description of article	Stripping tool for wires up to 6 mm ² / with integrated cable cutter
------------------------	---

Stripping tools

Cable type	Flexible and solid conductors with PVC insulation	Conductor cross-section, max.	6 mm ²
Conductor cross-section, min.	0.08 mm ²	Stripping length, max.	20 mm
Stripping range AWG, max.	10 AWG	Stripping range AWG, min.	28 AWG

Classifications

ETIM 6.0	EC002109	ETIM 7.0	EC002109
ETIM 8.0	EC002109	ETIM 9.0	EC002109
ECLASS 9.0	21-04-37-06	ECLASS 9.1	21-04-37-06
ECLASS 10.0	21-04-37-06	ECLASS 11.0	21-04-37-06
ECLASS 12.0	21-04-37-06	ECLASS 13.0	21-04-37-06

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Downloads

Catalogues	Catalogues in PDF-format
------------	--