

**H1,5/24 XS SW****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

- In multi-pack bag
- Weidmüller colour code

**General ordering data**

Version	Wire-end ferrule, Standard, 18 mm, 14.5 mm, black
Order No.	<a href="#">9202870000</a>
Type	H1,5/24 XS SW
GTIN (EAN)	4032248517947
Qty.	100 pc(s).
Packaging	loose

**H1,5/24 XS SW****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight	0.29 g
------------	--------

**Technical data**

Description of article	Wire end ferrule for short-circuit-proof and earth-fault-proof lines, black	Version	Standard
------------------------	---	---------	----------

**Wire-end ferrules**

Collar diameter (D2)	6.8 mm	Colour code	Weidmueller
Conductor cross-section	1.5 mm <sup>2</sup>	Contact surface diameter (D1)	1.8 mm
Contact surface length (L2)	14.5 mm	L1 in mm	24 mm
Metal sleeve thickness (S1)	0.15 mm	Plastic collar thickness (S2)	0.3 mm
Stripping length	18 mm	Wire connection cross section AWG, max.	AWG 16

**Classifications**

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ETIM 9.0	EC000005
ECLASS 9.0	27-40-02-01	ECLASS 9.1	27-40-02-01
ECLASS 10.0	27-40-02-01	ECLASS 11.0	27-40-02-01
ECLASS 12.0	27-40-02-01	ECLASS 13.0	27-40-02-01

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Technical information - EN</a> <a href="#">Technical information - DE</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**H1,5/24 XS SW**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Drawing**

