

KOBBS 19X55**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- Overpressure valve protects against overloading
- Cylinder head angled at 90°
- Angled head can be rotated through 360°
- Ergonomic handle springs back automatically
- The waste piece no longer becomes jammed thanks to triple splitting
- Hydraulic punch made of high-strength aluminium (approx. 40% weight saving)
- Service life greatly reduced when stainless steel sheets are used

Általános rendelési adatok

Verzió	Lemezlyukasztó
Rendelési szám	9205040000
Típus	KOBBS 19X55
GTIN (EAN)	4032248694273
Qty.	1 Stück

KOBBS 19X55

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Műszaki adatok

Méretek és tömegek

Magasság	55 mm	Magasság (coll)	2,165 inch
Átmérő	19 mm	Nettó tömeg	245 g

Műszaki adatok

Árucikk leírása	Feszítőcsavar csapággyakkal, 19,0 x 55,0 mm
-----------------	---

Besorolások

ETIM 6.0	EC000149	ETIM 7.0	EC000149
ETIM 8.0	EC000149	ETIM 9.0	EC000149
ECLASS 9.0	21-04-50-03	ECLASS 9,1	21-01-92-90
ECLASS 10.0	21-04-50-03	ECLASS 11.0	21-04-50-03
ECLASS 12.0	21-04-50-03	ECLASS 13.0	21-04-50-03

Termékek környezetvédelmi megfelelősége

REACH SVHC	Lead 7439-92-1
SCIP	6a3438d7-aa8c-48e4-8879-adf736ca79e3

Letöltések

Katalógusok	Catalogues in PDF-format
Kiadványok	