

CTIN CM 1.6/2.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Crimping tools for turned contacts**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.

General ordering data

Version	Pressing tool, Crimping tool for contacts, 0.14mm², 6mm², 4-indent crimp
Order No.	9205430000
Type	CTIN CM 1.6/2.5
GTIN (EAN)	4032248733446
Qty.	1 pc(s).

CTIN CM 1.6/2.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Width	230 mm	Width (inches)	9.055 inch
Net weight	1,175 g		

Technical data

Description of article	Crimping tool for HD, HE and ConCEPT M10/M5 contacts, 0.14-6 mm ²	Version	Mechanical, without interchangeable inserts
------------------------	--	---------	---

Description of contact

Conductor cross-section, max. AWG	AWG 10	Conductor cross-section, min. AWG	AWG 26
Crimping range, max.	6 mm ²	Crimping range, min.	0.14 mm ²
Type of contact	Turned contacts		

tool data crimping

Crimping type/profile	4-indent crimp
-----------------------	----------------

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ETIM 9.0	EC000168
ECLASS 9.0	21-04-38-11	ECLASS 9.1	21-04-38-11
ECLASS 10.0	21-04-38-11	ECLASS 11.0	21-04-38-11
ECLASS 12.0	21-04-38-11	ECLASS 13.0	21-04-38-11

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Downloads

User Documentation	Manual_other_languages Manual_DE_EN
Catalogues	Catalogues in PDF-format
Brochures	