













WEITERGABE SOWIE Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patent-, Gebrauchsmuster- oder Geschmacksmusterantragungsverfahren, die Reproduktion und Utilization of its contents as well as the communication of its contents to others without explicit authorization is prohibited. OFFENDERS WILL BE HELD LIABLE FOR THE PAYMENT OF DAMAGES. WEDMUELLER EXCLUSIVELY RESERVES THE RIGHT TO FILE FOR PATENTS, UTILITY MODELS OR DESIGNS. (C) WEDMUELLER INTERFACE GmbH & Co. KG



| | | | | | |
|---------------|---------------------|-------------|---|--|--|
| MATERIAL: | | | PART NO.: | MAT.NO.: | CAT.NO.: |
| | | | FINISH TO WN 2 11 001 - | | |
| | | | FINISH: SURFACE AREA: . mm ² | | |
| | | | GENERAL TOLERANCES: TOLERANCES TO ISO 8015 | | |
| | | | <input type="checkbox"/> WN 2 12 010 | <input checked="" type="checkbox"/> ISO 2768-f |  |
| | 72825/5 16.10.13 | 00 | Weidmüller  | | C 48761  |
| MODIFICATION | | DRAWING NO. | | | ISSUE NO. |
| | | DATE | NAME | SHEET 04 OF 05 SHEETS | |
| R.PART NO.: | | DRAWN | 13.10.2009 | LP CH20M 5.0 LP-KONTUREN PCB-CONTOURS | |
| SCALE: 1/1 | | RESPONSIBLE | VAN_GIESEN_B | | |
| SUPERSEDES: . | | CHECKED | 25.10.2013 | | |
| | | APPROVED | HANKE_D | PRODUCT FILE:CH20M... 5670 | |