IH 2.8 DB

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



With insulating sleeve for cable lug, an increase of the rated voltage within the application is possible.

General ordering data

Version	W-Series, Insulating sleeve
Order No.	0386060000
Type	IH 2.8 DB
GTIN (EAN)	4008190043414
Qty.	100 pc(s).

IH 2.8 DB

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	5.1 mm	Depth (inches)	0.201 inch
Height	18 mm	Height (inches)	0.709 inch
Width	3.6 mm	Width (inches)	0.142 inch
Net weight	0.18 g		

Temperatures

Storage temperature	-25 °C...55 °C	Operating temperature	-50 °C...
Continuous operating temp., max.	120 °C		

Material data

Material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting

General

Installation advice	Direct mounting

UL rating data

Certificate No. (UR)	E60693

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-90

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E60693

Downloads

Approval/Certificate/Document of Conformity	Confirmation of Standards EN 45545-2_2020-10
Engineering Data	CAD data – STEP
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format