VH 35/11/5.5 SAK95

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



Similar to illustration

General ordering data

Version	SAK Series, Connecting sleeve, for cross-connection link, Number of poles:
Order No.	0551100000
Type	VH 35/11/5.5 SAK95
GTIN (EAN)	4008190052669
Qty.	10 pc(s).
Delivery status	Discontinued

VH 35/11/5.5 SAK95

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	35 mm	Depth (inches)	1.378 inch
Height	11 mm	Height (inches)	0.433 inch
Width	11 mm	Width (inches)	0.433 inch
Net weight	21.2 g		

Temperatures

Storage temperature	-25 °C...55 °C

Material data

Material	Cu Zn	Colour	grey

System specifications

Version	for cross-connection link

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

Cross-connector

Number of cross-connected terminals	1	Type	Cross-connector

General

Installation advice	Direct mounting

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-90

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	73c55621-8329-401d-bde2-7fd78e0e60e4

Approvals

ROHS	Conform

Downloads

Engineering Data	CAD data – STEP
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format