PAC-UNIV-HE14-F-2M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

General ordering data

Version	Pre-assembled cable, PAC
Order No.	1349740020
Type	PAC-UNIV-HE14-F-2M
GTIN (EAN)	4032248276431
Qty.	1 pc(s).

PAC-UNIV-HE14-F-2M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	141.6 g

Temperatures

Storage temperature	-10...60 °C	Operating temperature	-10...50

General Data

Cable	Cable LiYY	Cable length	2 m
Connector PLC side	H0.14/10 (FERRULES 0.14mm²)	Interface connector	FLAT CABLE CONECTOR HE10 14P
Material	PVC	Number of poles, min.	14-pole
Outer diameter	7,6 ± 1 mm	Suitable for	Digital signals
Wire cross-section	0.14 mm²		

Electrical Data

Capacity wire / shield	300 pF/m	Capacity wire / wires	300 pF/m
Operating voltage	≤ 60 V DC ≤ 25 V AC	Permissible current strength per path, max.	1 A
Rated voltage	≤ 60 V DC ≤ 25 V AC	Resistance	≤ 150 mΩ/m
Total current, max.	3 A		

Classifications

ETIM 6.0	EC000237	ETIM 7.0	EC000237
ETIM 8.0	EC000237	ETIM 9.0	EC000237
ECLASS 9.0	27-24-22-20	ECLASS 9.1	27-24-22-20
ECLASS 10.0	27-24-22-20	ECLASS 11.0	27-24-22-20
ECLASS 12.0	27-24-22-20	ECLASS 13.0	27-24-22-20

Approvals

ROHS	Conform

Downloads

User Documentation	Colours chart
Catalogues	Catalogues in PDF-format