C300-32B-F-2S-M14-1M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product is no longer available



Similar to illustration

The pre-wired cables allow connecting the Honeywell C300 IOTAs (Input Output Terminal Assemblies) and the Weidmüller FTAs (Field Terminal Assemblies) in a manner that is quick, simple and error free.
The cables may be delivered with single or dual connectors, or even with free ends and end ferrules.
The hood makes it easier to handle and it offers a robust connection with the IOTA. It also allows using cables of different gauge sizes and lengths of up to 50m.

General ordering data

Version	Pre-assembled cable, PAC, Cable LiYCY, 0.14 mm²
Order No.	1373740010
Type	C300-32B-F-2S-M14-1M
GTIN (EAN)	4032248208920
Qty.	1 pc(s).
Delivery status	Discontinued
Available until	2020-10-01

C300-32B-F-2S-M14-1M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	263 g

Temperatures

Storage temperature	-10...60 °C	Operating temperature	-10...50

General Data

Cable	Cable LiYCY	Cable length	1 m
Connector PLC side	H0.14/10 (FERRULES 0.14mm²)	Interface connector	SP-BLZ 5.08 32P with CLAMSHELL
Material	PVC	Number of poles, min.	32-pole
Outer diameter	9,7 ± 1 mm	Suitable for	Digital signals
Wire cross-section	0.14 mm²		

Electrical Data

Capacity wire / shield	300 pF/m	Capacity wire / wires	300 pF/m
High voltage test	1 KV/1s	Operating voltage	≤ 250 V DC ≤ 250 V AC
Permissible current strength per path, max.	1 A	Rated voltage	≤ 250 Vdc ≤ 250 Vac
Resistance	≤ 150 mΩ/m	Total current, max.	3 A

Classifications

ETIM 6.0	EC000237	ETIM 7.0	EC000237
ETIM 8.0	EC000237	ETIM 9.0	EC000237
ECLASS 9.0	27-24-22-20	ECLASS 9.1	27-24-22-20
ECLASS 10.0	27-24-22-20	ECLASS 11.0	27-24-22-20
ECLASS 12.0	27-24-22-20	ECLASS 13.0	27-24-22-20

Approvals

ROHS	Conform

Downloads

User Documentation	Colours chart
Catalogues	Catalogues in PDF-format
Brochures	