FBCON SS DP M12 1WAY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



For Profibus DP and Modbus RS485, FBCon standard T-distributors and terminators connect individual field devices or remote I/O to the bus cable.
Their EMC cable glands, protection class IP66 and a wide operating temperature range safely protect your connections in harsh environments.
Functionality

- EMC cable glands for trunk and spurs
- M12 connector for spurs
- External earthing stud
- Pressure equalizing element
- Protection class IP66
- Aluminium and stainless-steel versions
- Profibus DP / Modbus RS485 compatible

Note: The use of FBCon products with aluminum enclosures and / or M12 connectors is not recommended in strongly saline environments.

General ordering data

Version	Standard distributor without bus termination, 1-way distributor, IP66
Order No.	8714270000
Type	FBCON SS DP M12 1WAY
GTIN (EAN)	4032248404735
Qty.	1 pc(s).
Delivery status	Discontinued
Available until	2020-10-30
Alternative product	8714260000

FBCON SS DP M12 1WAY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	36 mm	Height (inches)	1.417 inch
Width	58 mm	Width (inches)	2.283 inch
Length	64 mm	Length (inches)	2.52 inch
Net weight	409 g		

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...80 °C

Technical data

Bus system	Profibus-DP, Modbus RS485	Cable entry	Stainless steel cable gland, Branch line M12
Connection type PE	M12 spur line	Design of housing	With pressure compensation element
Housing main material	Stainless steel, rust-proof	Protection degree	IP66
Type of distribution	1-way distributor	Type of mounting	surface-mounted

Classifications

ETIM 6.0	EC001604	ETIM 7.0	EC001604
ETIM 8.0	EC001604	ETIM 9.0	EC001604
ECLASS 9.0	27-24-26-08	ECLASS 9.1	27-24-26-08
ECLASS 10.0	27-24-26-08	ECLASS 11.0	27-24-26-08
ECLASS 12.0	27-44-01-11	ECLASS 13.0	27-44-01-11

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	3a5f5913-76fc-4ff5-8563-4463f80bbe02

Approvals

ROHS	Conform

Downloads

Approval/Certificate/Document of Conformity	Application notes – Certification UL Application notes – Declaration of Conformity
User Documentation	Quick start guide – assembly instruction german / english Quick start guide – Application-Guide-Planning and installing Fieldbus networks-using-FBCon_english_deutsch
Catalogues	Catalogues in PDF-format
Brochures	

FBCON SS DP M12 1WAY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

