STRIPPER PC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- For fast and accurate stripping of cables for damp areas ranging from 8 - 13 mm diameter, e.g. NYM cable, 3 x 1.5 mm² to 5 x 2.5 mm²
- No need to set cutting depth
- Ideal for working in junction and distribution boxes

General ordering data

Version	Sheathing strippers
Order No.	9918060000
Type	STRIPPER PC
GTIN (EAN)	4032248359172
Qty.	1 pc(s).

STRIPPER PC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	25 mm	Depth (inches)	0.984 inch
Height	35 mm	Height (inches)	1.378 inch
Width	125 mm	Width (inches)	4.921 inch
Net weight	44.4 g		

Technical data

Description of article	Cable sheathing stripper for data communication lines with 5-15 mm O.D. ø

Stripping tools

Cable type	Data cable / telecommunications and IT	Conductor cross-section, max.	4 mm²
Conductor cross-section, min.	0.25 mm²	Max. conductor diameter	15 mm
Min. conductor diameter	5 mm	Stripping range AWG, max.	12 AWG
Stripping range AWG, min.	24 AWG	Stripping range, min.	0.25 mm²

Classifications

ETIM 6.0	EC000163	ETIM 7.0	EC000163
ETIM 8.0	EC000163	ETIM 9.0	EC000163
ECLASS 9.0	21-04-90-90	ECLASS 9.1	21-04-37-06
ECLASS 10.0	21-04-90-90	ECLASS 11.0	21-04-90-90
ECLASS 12.0	21-04-90-90	ECLASS 13.0	21-04-90-90

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1

Downloads

Catalogues	Catalogues in PDF-format
Brochures	

STRIPPER PC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

