


**SAKS 1/35 G20 LD 24VDC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Similar to illustration

In some applications it is useful to protect the feed through connection with a separate fuse. Fuse terminal blocks are made up of one terminal block bottom section with a fuse insertion carrier. The fuses vary from pivoting fuse levers and pluggable fuse holders to screwable closures and flat plug-in fuses.

**General ordering data**

Version	Fuse terminal, Screw connection, Fuse cartridge, with LED, One end without connector, Screw connection, 10 mm <sup>2</sup> , 24 V, G-Si. 5 x 20, medium yellow
Order No.	<a href="#">0225820000</a>
Type	SAKS 1/35 G20 LD 24VDC
GTIN (EAN)	4008190057626
Qty.	10 pc(s).

## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	53 mm	Depth (inches)	2.087 inch
Height	54 mm	Height (inches)	2.126 inch
Width	13 mm	Width (inches)	0.512 inch
Net weight	36.41 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

## Material data

Material	KrG	Colour	medium yellow
UL 94 flammability rating	V-0, 5VA		

## System specifications

Version	Screw connection, Fuse cartridge, with LED, One end without connector	End cover plate required	Yes
Number of potentials	1	Number of levels	1
Number of clamping points per level	2	Number of potentials per tier	1
Levels cross-connected internally	No	PE connection	No
Rail	TS 35	N-function	No
PE function	No	PEN function	No

## Additional technical data

Installation advice	Direct mounting	Number of similar terminals	1
Open sides	right	Type of mounting	Snap-on

## Conductors for clamping (additional connection)

Connection type, additional connection	Screw connection
--	------------------

## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Conductors for clamping (rated connection)

Blade size	1.0 x 5.5 mm	Clamping range, max.	16 mm <sup>2</sup>
Clamping range, min.	0.5 mm <sup>2</sup>	Clamping screw	M 4
Connection cross-section, stranded, max.	10 mm <sup>2</sup>	Connection cross-section, stranded, min.	1.5 mm <sup>2</sup>
Connection direction	on side	Gauge to IEC 60947-1	B6
Number of connections	2	Stripping length	12 mm
Tightening torque, max.	2.4 Nm	Tightening torque, min.	1.2 Nm
Torque level with DMS electric screwdriver	4	Type of connection	Screw connection
Type of connection 2	Screw connection	Wire connection cross section AWG, max.	AWG 8
Wire connection cross section AWG, min.	AWG 20	Wire connection cross section, finely stranded, max.	10 mm <sup>2</sup>
Wire connection cross section, finely stranded, min.	0.5 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	10 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.5 mm <sup>2</sup>	Wire connection cross-section, solid core, max.	16 mm <sup>2</sup>
Wire connection cross-section, solid core, min.	0.5 mm <sup>2</sup>		

## Display element

Current	50 A	Type of voltage for indicator	AC/DC
---------	------	-------------------------------	-------

## Fuse terminals

Cartridge fuse	G-Si. 5 x 20	Current	50 A
Display	LED	Fuse holder (cartridge holder)	for screw fixing
Operating voltage, max.	24 V	Type of voltage for indicator	AC/DC

## General

Installation advice	Direct mounting	Rail	TS 35
Wire connection cross section AWG, max.	AWG 8	Wire connection cross section AWG, min.	AWG 20

## Rating data

Rated cross-section	10 mm <sup>2</sup>	Rated voltage	24 V
Rated DC voltage	24 V	Current at maximum wires	6.3 A
Volume resistance according to IEC 60947-7-x	0.56 mΩ	Rated impulse withstand voltage	4 kV
Power loss in accordance with IEC 60947-7-x	1.82 W		

## Classifications

ETIM 6.0	EC000899	ETIM 7.0	EC000899
ETIM 8.0	EC000899	ETIM 9.0	EC000899
ECLASS 9.0	27-14-11-16	ECLASS 9.1	27-14-11-16
ECLASS 10.0	27-14-11-16	ECLASS 11.0	27-14-11-16
ECLASS 12.0	27-14-11-16	ECLASS 13.0	27-25-01-13

## SAKS 1/35 G20 LD 24VDC

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Important note

Product information	The voltage depends on the selected fuse element or the selected indicator light
---------------------	--

## Approvals

Approvals



ROHS	Conform
------	---------

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">Declaration of Conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Beipackzettel_SAKS_GL_LD.pdf</a> <a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**SAKS 1/35 G20 LD 24VDC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Custom printing**

The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Type	DEK 5/8 PLUS MC SDR	Version
Order No.	<a href="#">1046370000</a>	Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00
GTIN (EAN)	4032248782079	Weidmueller, To customer specification
Qty.	160 pc(s).	
Type	DEK 5/8 MC SDR	Version
Order No.	<a href="#">1856750000</a>	Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00
GTIN (EAN)	4032248400867	Weidmueller, To customer specification
Qty.	160 pc(s).	

## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/5 MC NE WS	Version
Order No.	<a href="#">1609801044</a>	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00
GTIN (EAN)	4008190397111	Weidmueller, white
Qty.	1,000 pc(s).	

## SAK-Series



End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

## General ordering data

Type	AP SAKB/C/T KRG	Version
Order No.	<a href="#">0146720000</a>	End plate (terminals), 65 mm x 3 mm, dark beige, yellow
GTIN (EAN)	4008190027995	
Qty.	20 pc(s).	
Type	AP SAKS1+3 KRG	Version
Order No.	<a href="#">0191320000</a>	End plate (terminals), 54 mm x 3 mm, dark beige, yellow
GTIN (EAN)	4008190031688	
Qty.	20 pc(s).	
Type	AP SAK4-10 I	Version
Order No.	<a href="#">0117910000</a>	End plate (terminals), 40 mm x 1.5 mm, Light Grey
GTIN (EAN)	4008190183707	
Qty.	20 pc(s).	

## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	AP SAK4-10 BL	Version
Order No.	<a href="#">0117980000</a>	End plate (terminals), 40 mm x 1.5 mm, blue
GTIN (EAN)	4008190171087	
Qty.	20 pc(s).	
Type	AP SAK4-10 RT	Version
Order No.	<a href="#">0117900000</a>	End plate (terminals), 40 mm x 1.5 mm, red
GTIN (EAN)	4008190125059	
Qty.	20 pc(s).	
Type	AP RSF1 KRG	Version
Order No.	<a href="#">0270420000</a>	End plate (terminals), 50 mm x 3 mm, medium yellow
GTIN (EAN)	4008190099107	
Qty.	10 pc(s).	
Type	AP SAK35/TW SAK16 BL	Version
Order No.	<a href="#">0303680000</a>	End plate (terminals), 58 mm x 1.5 mm, blue
GTIN (EAN)	4008190025199	
Qty.	10 pc(s).	
Type	AP SAK4-10 DB	Version
Order No.	<a href="#">0105100000</a>	End plate (terminals), 40 mm x 1.5 mm, dark beige
GTIN (EAN)	4008190394875	
Qty.	20 pc(s).	
Type	AP SAKS1+3 KRG/DB	Version
Order No.	<a href="#">0191300000</a>	End plate (terminals), 54 mm x 3 mm, dark beige
GTIN (EAN)	4008190099763	
Qty.	20 pc(s).	
Type	AP KSKM	Version
Order No.	<a href="#">9509630000</a>	SAK Series, End plate, 1.5 mm, beige, Direct mounting
GTIN (EAN)	4008190456771	
Qty.	20 pc(s).	
Type	AP SAK35/TW SAK16	Version
Order No.	<a href="#">0303660000</a>	End plate (terminals), 58 mm x 1.5 mm, beige
GTIN (EAN)	4008190110765	
Qty.	10 pc(s).	
Type	AP SAK4-10	Version
Order No.	<a href="#">0117960000</a>	End plate (terminals), 40 mm x 1.5 mm, beige
GTIN (EAN)	4008190081485	
Qty.	20 pc(s).	
Type	AP SAK4-10 KRG	Version
Order No.	<a href="#">0117920000</a>	End plate (terminals), 40 mm x 1.5 mm, dark beige, yellow
GTIN (EAN)	4008190135904	
Qty.	20 pc(s).	
Type	AP SAK4-10 KRG/BL	Version
Order No.	<a href="#">0117970000</a>	End plate (terminals), 40 mm x 1.5 mm, blue
GTIN (EAN)	4008190049607	
Qty.	20 pc(s).	
Type	AP SAKA KRG	Version
Order No.	<a href="#">0134220000</a>	End plate (terminals), 82 mm x 3 mm, dark beige, yellow
GTIN (EAN)	4008190167943	
Qty.	20 pc(s).	

## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## SchT group marker carrier



The SchT 5 S group tag carriers are clipped directly onto the TS 32 mounting rail (G-rail) or the TS 35 mounting rail (top-hat rail). It is therefore possible to label the terminal strip irrespective of the terminal and the type of terminal. SchT 5 and SchT 5 S are fitted with ESO 5, STR 5 protective strips.

The SchT 7 is a hinged group tag carrier for inlay tags which enables easy access to the clamping screw. The SchT 7 is fitted with ESO 7, STR 7 protective strips or DEK 5.

Inlay tags and protective strips can be found under "Accessories".

## General ordering data

Type	SCHT 7	Version
Order No.	<a href="#">0517960000</a>	SCHT, Terminal marker, 39.3 x 8 mm, Pitch in mm (P): 7.00
GTIN (EAN)	4008190001742	Weidmueller, white
Qty.	20 pc(s).	

## Steel



Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

## General ordering data

Type	TS 32X15/LL 2M/ST/ZN	Version
Order No.	<a href="#">0514400000</a>	Terminal rail, with slot, Accessories, 33 x 15 x 2000 mm, Slit width:
GTIN (EAN)	4008190086152	5.20 mm, Slit length: 25.00 mm, Steel, galvanic zinc plated and
Qty.	2 m	passivated



## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/8 MC NE WS	Version
Order No.	<a href="#">1856740000</a>	Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00
GTIN (EAN)	4032248400850	Weidmueller, white
Qty.	800 pc(s).	

## Q / SAK



Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

## General ordering data

Type	Q 2 SAK10	Version
Order No.	<a href="#">0457100000</a>	Cross-connector (terminal), when screwed in, Number of poles: 2,
GTIN (EAN)	4008190103545	Pitch in mm (P): 9.90, Insulated: No, 57 A, grey
Qty.	50 pc(s).	
Type	Q 10 SAK10	Version
Order No.	<a href="#">0457400000</a>	Cross-connector (terminal), when screwed in, Number of poles: 10,
GTIN (EAN)	4008190016166	Pitch in mm (P): 9.90, Insulated: No, 57 A, grey
Qty.	20 pc(s).	
Type	Q 3 SAK10	Version
Order No.	<a href="#">0457200000</a>	Cross-connector (terminal), when screwed in, Number of poles: 3,
GTIN (EAN)	4008190135379	Pitch in mm (P): 9.90, Insulated: No, 57 A, grey
Qty.	50 pc(s).	

## SAKS 1/35 G20 LD 24VDC

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

Type	Q 4 SAK10	Version
Order No.	<a href="#">0457300000</a>	Cross-connector (terminal), when screwed in, Number of poles: 4,
GTIN (EAN)	4008190129750	Pitch in mm (P): 9.90, Insulated: No, 57 A, grey
Qty.	50 pc(s).	

## Miscellaneous



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

## General ordering data

Type	SS M4 D 128-A 4	Version
Order No.	<a href="#">0136400000</a>	Lock washer, Copper
GTIN (EAN)	4008190118143	
Qty.	100 pc(s).	

## End plate



## Current and voltage transformer wiring

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

## General ordering data

Type	TW SAKB/C/T	Version
Order No.	<a href="#">0242920000</a>	Partition plate (terminal), Intermediate plate, 75 mm x 42.5 mm, beige
GTIN (EAN)	4008190069933	
Qty.	20 pc(s).	

## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Insulated



Bus bar taps with insulation offer finger safety on the one hand. On the other hand, the colored insulation also indicates the respective potential, such as the neutral conductor or PE.

## General ordering data

Type	ZBE 6K BL	Version
Order No.	<a href="#">0525980000</a>	Clamping yoke (bus-bar)
GTIN (EAN)	4008190060886	
Qty.	50 pc(s).	
Type	ZBE 6K SW	Version
Order No.	<a href="#">0525910000</a>	Clamping yoke (bus-bar)
GTIN (EAN)	4008190977054	
Qty.	50 pc(s).	
Type	ZB 16K BL	Version
Order No.	<a href="#">0502880000</a>	Clamping yoke (bus-bar)
GTIN (EAN)	4008190014186	
Qty.	50 pc(s).	
Type	ZB 16K SW	Version
Order No.	<a href="#">0502810000</a>	Clamping yoke (bus-bar)
GTIN (EAN)	4008190332563	
Qty.	50 pc(s).	
Type	ZB 4K GG HENSEL	Version
Order No.	<a href="#">1824560000</a>	Clamping yoke (bus-bar)
GTIN (EAN)	4032248330973	
Qty.	50 pc(s).	
Type	ZB 4G SW	Version
Order No.	<a href="#">0322110000</a>	Clamping yoke (bus-bar)
GTIN (EAN)	4008190189310	
Qty.	50 pc(s).	
Type	ZB 35K GE/GN M6X16	Version
Order No.	<a href="#">0502660000</a>	Clamping yoke (bus-bar)
GTIN (EAN)	4008190052294	
Qty.	20 pc(s).	
Type	ZB 16K GE/GN	Version
Order No.	<a href="#">0502860000</a>	Clamping yoke (bus-bar)
GTIN (EAN)	4008190188795	
Qty.	50 pc(s).	
Type	ZB 4/6K BL	Version
Order No.	<a href="#">0565480000</a>	Clamping yoke (bus-bar)
GTIN (EAN)	4008190086831	
Qty.	50 pc(s).	
Type	ZBE 6K GE/GN	Version
Order No.	<a href="#">0525960000</a>	Clamping yoke (bus-bar)
GTIN (EAN)	4008190145026	
Qty.	50 pc(s).	

Creation date June 4, 2024 2:10:28 AM CEST

## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	ZB 35K SW M6X16	Version
Order No.	<a href="#">0502610000</a>	Clamping yoke (bus-bar)
GTIN (EAN)	4008190332587	
Qty.	20 pc(s).	
Type	ZB 4G BL	Version
Order No.	<a href="#">0322180000</a>	Clamping yoke (bus-bar)
GTIN (EAN)	4008190050504	
Qty.	50 pc(s).	
Type	ZB 4K SW	Version
Order No.	<a href="#">0475310000</a>	Clamping yoke (bus-bar)
GTIN (EAN)	4008190008406	
Qty.	50 pc(s).	
Type	ZB 4G GN/GE	Version
Order No.	<a href="#">0322160000</a>	Clamping yoke (bus-bar)
GTIN (EAN)	4008190014278	
Qty.	50 pc(s).	
Type	ZB 4K BL	Version
Order No.	<a href="#">0475380000</a>	Clamping yoke (bus-bar)
GTIN (EAN)	4008190010942	
Qty.	50 pc(s).	
Type	ZB 4K GE/GN	Version
Order No.	<a href="#">0475360000</a>	Clamping yoke (bus-bar)
GTIN (EAN)	4008190188047	
Qty.	50 pc(s).	
Type	ZB 35K BL M6X16	Version
Order No.	<a href="#">0502680000</a>	Clamping yoke (bus-bar)
GTIN (EAN)	4008190004385	
Qty.	20 pc(s).	
Type	ZB 4/6K GE/GN	Version
Order No.	<a href="#">0565460000</a>	Clamping yoke (bus-bar)
GTIN (EAN)	4008190032609	
Qty.	50 pc(s).	

## W-Series



## Building installation wiring

For building installations, we offer a complete system that revolves around the 10×3 copper rail and comprises perfectly coordinated components: from installation terminal blocks, neutral conductor terminal blocks and distribution terminal blocks to comprehensive accessories such as busbars and busbar holders.

## General ordering data

Type	HP NT6/10 BL	Version
Order No.	<a href="#">0352880000</a>	End and partition plate for terminals, End and intermediate plate, 40
GTIN (EAN)	4008190135126	mm x 2 mm, blue
Qty.	20 pc(s).	

## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Gauge rings



Gauge rings are used to protect against the using of incorrectly selected fuse sizes. They are simply inserted into the respective fuse base and prevent the using of bigger fuses.

## General ordering data

Type	P 14/2 D01 RS SAKS4	Version
Order No.	<a href="#">0138000000</a>	Fuse gauge ring (terminal), Height: 11 mm, Depth: 10.5 mm,
GTIN (EAN)	4008190114664	Aluminium, pink
Qty.	50 pc(s).	
Type	P 14/6 D01 GN SAKS4	Version
Order No.	<a href="#">0328600000</a>	Fuse gauge ring (terminal), Height: 11 mm, Depth: 10.5 mm,
GTIN (EAN)	4008190004248	Aluminium, green
Qty.	50 pc(s).	
Type	P 14/10 D01 RT SAKS4	Version
Order No.	<a href="#">0328700000</a>	Fuse gauge ring (terminal), Height: 11 mm, Depth: 10.5 mm,
GTIN (EAN)	4008190010294	Aluminium, red
Qty.	50 pc(s).	
Type	P 14/4 D01 BR SAKS4	Version
Order No.	<a href="#">0138100000</a>	Fuse gauge ring (terminal), Height: 11 mm, Depth: 10.5 mm,
GTIN (EAN)	4008190077365	Aluminium, brown
Qty.	50 pc(s).	

## Steel



Steel bus bars, together with stainless steel, have the highest strength among metallic busbars and are used in applications where short-circuit resistance plays only a secondary role.

## General ordering data

Type	ESCH 1 M	Version
Order No.	<a href="#">0280300000</a>	Busbar (terminal)
GTIN (EAN)	4008190143053	
Qty.	10 m	

## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Brass



Brass bus bars, as a copper alloy, has positive properties in terms of electrical conductivity and at the same time has a higher strength than copper against mechanical stress.

## General ordering data

Type	SA 3.00X10.00X1000 CUZN ...	Version
Order No.	<a href="#">0259800000</a>	Busbar (terminal)
GTIN (EAN)	4008190049300	
Qty.	1 m	

## Fuse holder



The fuse holder SIHA quickly turns a disconnect terminal into a fuse terminal: simply remove the disconnect lever and attach the fuse unit.

## General ordering data

Type	SK E14 SAKS4	Version
Order No.	<a href="#">0339410000</a>	Screw cover cap (terminal)
GTIN (EAN)	4008190032104	
Qty.	20 pc(s).	
Type	SK E16/SAKS2	Version
Order No.	<a href="#">0284110000</a>	Screw cover cap (terminal)
GTIN (EAN)	4008190006204	
Qty.	25 pc(s).	
Type	SK E18 SAKS5	Version
Order No.	<a href="#">0359310000</a>	Screw cover cap (terminal)
GTIN (EAN)	4008190002121	
Qty.	20 pc(s).	
Type	SK G20/SAKS1	Version
Order No.	<a href="#">0282100000</a>	Screw cover cap (terminal)
GTIN (EAN)	4008190004606	
Qty.	20 pc(s).	
Type	SK SAKS1/G25	Version
Order No.	<a href="#">0282000000</a>	Screw cover cap (terminal)
GTIN (EAN)	4008190078492	
Qty.	20 pc(s).	

## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)


## Accessories

## Mounting rail support

## General ordering data

Type	SH 2	Version
Order No.	<a href="#">0494920000</a>	Busbar support
GTIN (EAN)	4008190007584	
Qty.	10 pc(s).	

## E 14



Weidmueller offers NEOZED fuses in E 14 design in sizes from 2 A to 16 A.

## General ordering data

Type	E 14/16A GR	Version
Order No.	<a href="#">0328500000</a>	Active components, Cartridge fuse
GTIN (EAN)	4008190152161	
Qty.	10 pc(s).	
Type	E 14/4A BR	Version
Order No.	<a href="#">0137500000</a>	Active components, Cartridge fuse
GTIN (EAN)	4008190142629	
Qty.	10 pc(s).	
Type	E 14/6A GN	Version
Order No.	<a href="#">0328300000</a>	Active components, Cartridge fuse
GTIN (EAN)	4008190002190	
Qty.	10 pc(s).	
Type	E 14/2A RS	Version
Order No.	<a href="#">0137400000</a>	Active components, Cartridge fuse
GTIN (EAN)	4008190069094	
Qty.	10 pc(s).	
Type	E 14/10A RT	Version
Order No.	<a href="#">0328400000</a>	Active components, Cartridge fuse
GTIN (EAN)	4008190000288	
Qty.	10 pc(s).	

## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snapped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

## General ordering data

Type	BZT 1 WS 10/5	Version
Order No.	<a href="#">1805490000</a>	Accessories, Marker holder
GTIN (EAN)	4032248270231	
Qty.	100 pc(s).	
Type	BZT 1 ZA WS 10/5	Version
Order No.	<a href="#">1805520000</a>	Accessories, Marker holder
GTIN (EAN)	4032248270248	
Qty.	100 pc(s).	

## 6.3x32



For protection against overcurrent, we offer cartridge fuse with dimensions 6.3x32 mm in sizes from 500 mA to 12.5 A.

## General ordering data

Type	VH 25.4/6.3/4.3	Version
Order No.	<a href="#">0446200000</a>	Dummy fuse
GTIN (EAN)	4008190519759	
Qty.	10 pc(s).	



## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## SAK-Series



A partition plate is used for the optical separation of circuits or used for electrical isolation from neighbouring cross-connectors. In contrast to the end plate, the contour can be larger than the adjacent terminal blocks. However, it should not be smaller, as otherwise the required clearance and creepage distances within the application can no longer be maintained.

## General ordering data

Type	TSCH 6 DKI S4	Version
Order No.	<a href="#">0190260000</a>	Small partition (terminal), PA 66, beige, Continuous operating temp.,
GTIN (EAN)	4008190051075	max.: 100 °C
Qty.	100 pc(s).	
Type	TW SAK4-10 HP/DBR/0.5	Version
Order No.	<a href="#">0197100000</a>	Partition plate (terminal), Intermediate plate, 40 mm x 55 mm, brown,
GTIN (EAN)	4008190146627	dark beige
Qty.	20 pc(s).	
Type	TW SAK16 KRG	Version
Order No.	<a href="#">0281120000</a>	Partition plate (terminal), Intermediate plate, 60 mm x 50 mm, dark
GTIN (EAN)	4008190072360	beige, yellow
Qty.	20 pc(s).	
Type	TW SAK4-10 KRG/BL	Version
Order No.	<a href="#">0130170000</a>	Partition plate (terminal), Intermediate plate, 50 mm x 44 mm, blue
GTIN (EAN)	4008190063757	
Qty.	20 pc(s).	
Type	TW AST1/PA HP/DBR/0.5	Version
Order No.	<a href="#">0474700000</a>	Partition plate (terminal), Intermediate plate, 65 mm x 60 mm, dark
GTIN (EAN)	4008190078508	brown
Qty.	20 pc(s).	
Type	TW 4 SAK4-10	Version
Order No.	<a href="#">0130160000</a>	Partition plate (terminal), Intermediate plate, 50 mm x 44 mm, beige
GTIN (EAN)	4008190096335	
Qty.	20 pc(s).	
Type	TW 4 SAK4-10 BL	Version
Order No.	<a href="#">0130180000</a>	Partition plate (terminal), Intermediate plate, 50 mm x 44 mm, blue
GTIN (EAN)	4008190114138	
Qty.	20 pc(s).	
Type	TSCH 2	Version
Order No.	<a href="#">0353660000</a>	Small partition (terminal), PA 66, beige, Continuous operating temp.,
GTIN (EAN)	4008190128432	max.: 100 °C
Qty.	100 pc(s).	
Type	TSCH 1	Version
Order No.	<a href="#">0319160000</a>	Small partition (terminal), PA 66, beige, Continuous operating temp.,
GTIN (EAN)	4008190097219	max.: 100 °C
Qty.	100 pc(s).	
Type	TSCH 4 AKZ4	Version
Order No.	<a href="#">0363360000</a>	Small partition (terminal), PA 66, beige, Continuous operating temp.,
GTIN (EAN)	4008190136680	max.: 100 °C
Qty.	100 pc(s).	

Creation date June 4, 2024 2:10:28 AM CEST

Catalogue status 01.06.2024 / We reserve the right to make technical changes.

## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	TW SAKS2 HP/DBR/2	Version
Order No.	<a href="#">0607000000</a>	Partition plate (terminal), Intermediate plate, 80 mm x 70 mm, dark
GTIN (EAN)	4008190002732	brown
Qty.	20 pc(s).	
Type	TW DK4 HP/DBR/2	Version
Order No.	<a href="#">3833500000</a>	Partition plate (terminal), Intermediate plate, 65 mm x 47.5 mm, dark
GTIN (EAN)	4008190009052	brown
Qty.	20 pc(s).	
Type	TW SAK4-10 KRG	Version
Order No.	<a href="#">0130120000</a>	Partition plate (terminal), Intermediate plate, 50 mm x 44 mm, dark
GTIN (EAN)	4008190139117	beige, yellow
Qty.	20 pc(s).	
Type	TSCH 3 SAKD2.5 N	Version
Order No.	<a href="#">0366860000</a>	Small partition (terminal), PA 66, beige, Continuous operating temp.,
GTIN (EAN)	4008190010928	max.: 100 °C
Qty.	100 pc(s).	

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/6 MC NE WS	Version
Order No.	<a href="#">1609820000</a>	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
GTIN (EAN)	4008190203436	Weidmueller, white
Qty.	1,000 pc(s).	

## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## 5x20

5x20

For protection against overcurrent, we offer cartridge fuse with dimensions 5x20 mm in sizes from 100 mA to 6.3 A.

## General ordering data

Type	G 20/5.00A/F	Version
Order No.	<a href="#">0431300000</a>	Miniature fuse, quick-acting, 5 A, G-Si. 5 x 20
GTIN (EAN)	4008190185381	
Qty.	10 pc(s).	
Type	G 20/1.60A/F	Version
Order No.	<a href="#">0430800000</a>	Miniature fuse, quick-acting, 1.6 A, G-Si. 5 x 20
GTIN (EAN)	4008190031503	
Qty.	10 pc(s).	
Type	G 20/4.00A/F	Version
Order No.	<a href="#">0431200000</a>	Miniature fuse, quick-acting, 4 A, G-Si. 5 x 20
GTIN (EAN)	4008190022983	
Qty.	10 pc(s).	
Type	G 20/0.10A/F	Version
Order No.	<a href="#">0430300000</a>	Miniature fuse, quick-acting, 0.1 A, G-Si. 5 x 20
GTIN (EAN)	4008190077174	
Qty.	10 pc(s).	
Type	G 20/0.25A/F	Version
Order No.	<a href="#">0430500000</a>	Miniature fuse, quick-acting, 0.25 A, G-Si. 5 x 20
GTIN (EAN)	4008190153991	
Qty.	10 pc(s).	
Type	G 20/2.50A/F	Version
Order No.	<a href="#">0431000000</a>	Miniature fuse, quick-acting, 2.5 A, G-Si. 5 x 20
GTIN (EAN)	4008190085513	
Qty.	10 pc(s).	
Type	G 20/2.00A/F	Version
Order No.	<a href="#">0430900000</a>	Miniature fuse, quick-acting, 2 A, G-Si. 5 x 20
GTIN (EAN)	4008190123567	
Qty.	10 pc(s).	
Type	G 20/3.15A/F	Version
Order No.	<a href="#">0431100000</a>	Miniature fuse, quick-acting, 3.15 A, G-Si. 5 x 20
GTIN (EAN)	4008190012977	
Qty.	10 pc(s).	
Type	G 20/1.00A/F	Version
Order No.	<a href="#">0430700000</a>	Miniature fuse, quick-acting, 1 A, G-Si. 5 x 20
GTIN (EAN)	4008190093877	
Qty.	10 pc(s).	
Type	G 20/6.30A/F	Version
Order No.	<a href="#">0431400000</a>	Miniature fuse, quick-acting, 6.3 A, G-Si. 5 x 20
GTIN (EAN)	4008190086053	
Qty.	10 pc(s).	

Creation date June 4, 2024 2:10:28 AM CEST

Catalogue status 01.06.2024 / We reserve the right to make technical changes.

## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	G 20/0.50A/F	Version
Order No.	<a href="#">0430600000</a>	Miniature fuse, quick-acting, 0.5 A, G-Si. 5 x 20
GTIN (EAN)	4008190046835	
Qty.	10 pc(s).	
Type	G 20/0.63A/F	Version
Order No.	<a href="#">0439000000</a>	Miniature fuse, quick-acting, 0.63 A, G-Si. 5 x 20
GTIN (EAN)	4008190131210	
Qty.	10 pc(s).	
Type	G 20/0.20A/F	Version
Order No.	<a href="#">0430400000</a>	Miniature fuse, quick-acting, 0.2 A, G-Si. 5 x 20
GTIN (EAN)	4008190152383	
Qty.	10 pc(s).	

## Testsockets



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

## General ordering data

Type	STB 18/RSF1	Version
Order No.	<a href="#">0286500000</a>	Socket (terminal), Plug-in depth: 15 mm, Depth: 23 mm
GTIN (EAN)	4008190515591	
Qty.	20 pc(s).	
Type	STB 13.5/D6/4/M4 SAKA10	Version
Order No.	<a href="#">0135200000</a>	SAK Series, Socket
GTIN (EAN)	4008190172862	
Qty.	50 pc(s).	

## Copper



Of all the metals used, copper has the best electrical conductivity, which results in the highest short-circuit resistance. This makes the copper busbar the most widely used variant.

## General ordering data

Type	SSCH 6X6X1000 CU/SN	Version
Order No.	<a href="#">0571300000</a>	Busbar (terminal)
GTIN (EAN)	4008190015039	
Qty.	1 m	

Creation date June 4, 2024 2:10:28 AM CEST

**SAKS 1/35 G20 LD 24VDC****Weidmüller Interface GmbH & Co. KG**


Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories**

Type	SSCH 7.3X1.2X1000	Version
Order No.	<a href="#">1071200000</a>	Busbar (terminal)
GTIN (EAN)	4008190279172	
Qty.	1 m	
Type	SSCH 10X3X1000 CU/SN	Version
Order No.	<a href="#">0348900000</a>	Busbar (terminal)
GTIN (EAN)	4008190024802	
Qty.	1 m	
Type	SSCH 15X6X1000 CU/SN	Version
Order No.	<a href="#">0357400000</a>	Busbar (terminal)
GTIN (EAN)	4008190169572	
Qty.	1 m	

**Slotted screwdriver**

Slotted screwdriver with rounded blade SD DIN 5265,  
ISO 2380/2, output to DIN 5264, ISO 2380/1.  
ChromTop tip, SoftFinish grip

**General ordering data**

Type	SDS 1.0X5.5X150	Version
Order No.	<a href="#">9008350000</a>	Screwdriver, Screwdriver
GTIN (EAN)	4032248056316	
Qty.	1 pc(s).	

## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## DEK 5/6



## WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

## Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

## General ordering data

Type	DEK 5/6 MM WS	Version
Order No.	<a href="#">2007120000</a>	Dekafix, Terminal marker, 5 x 6 mm, Weidmueller, white
GTIN (EAN)	4050118392104	
Qty.	600 pc(s).	

## Screws



Depending on the terminal block or also accessories, we offer different types of screws as additional items or also spare parts.

## General ordering data

Type	BFSC M4X20	Version
Order No.	<a href="#">0362800000</a>	Mounting screw (Terminal)
GTIN (EAN)	4008190114053	
Qty.	100 pc(s).	
Type	BFSC M4X30	Version
Order No.	<a href="#">0267100000</a>	Mounting screw (Terminal)
GTIN (EAN)	4008190187897	
Qty.	50 pc(s).	

## SAKS 1/35 G20 LD 24VDC

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

Type	BFSC M3X25	Version
Order No.	<a href="#">0292500000</a>	Mounting screw (Terminal)
GTIN (EAN)	4008190177027	
Qty.	100 pc(s).	
Type	BFSC M4X9T	Version
Order No.	<a href="#">0103300000</a>	Mounting screw (Terminal)
GTIN (EAN)	4008190023348	
Qty.	100 pc(s).	
Type	BFSC M3X22 PA/RT	Version
Order No.	<a href="#">0128900000</a>	Mounting screw (Terminal)
GTIN (EAN)	4008190084158	
Qty.	100 pc(s).	
Type	KISC M3X6 SAKS1	Version
Order No.	<a href="#">0346200000</a>	Clamping yoke, Mounting screw, Steel
GTIN (EAN)	4008190175658	
Qty.	100 pc(s).	

## Fixing screws



Fixing screws fix the short current bridge within the application. If the short current bridge is slided between two adjacent terminal blocks into the short circuit position, it can be fixed by means of a fastening screw. This ensures a permanent connection or short circuit.

## General ordering data

Type	KISC M3X20 SAK10 CU5	Version
Order No.	<a href="#">0377100000</a>	SAK Series, Mounting screw, Copper
GTIN (EAN)	4008190060350	
Qty.	100 pc(s).	

## Insulation caps



With our accessories for the bus bar taps, you can quickly and easily insulate the tap terminals and visualize the potential through the color coding.

## General ordering data

Type	IK 4 GG ZB4	Version
Order No.	<a href="#">0475460000</a>	Cover hood (terminal), Polyamide 66
GTIN (EAN)	4008190065348	
Qty.	50 pc(s).	

Creation date June 4, 2024 2:10:28 AM CEST

## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold


Germany

www.weidmueller.com

## Accessories

Type	IK 16/ZB 16 GG	Version
Order No.	<a href="#">0502960000</a>	Cover hood (terminal), Polyamide 66
GTIN (EAN)	4008190113438	
Qty.	50 pc(s).	
Type	IK 16/ZB 16 BL	Version
Order No.	<a href="#">0502980000</a>	Terminal (busbar connection)
GTIN (EAN)	4008190159696	
Qty.	50 pc(s).	
Type	IK 4 BL ZB4	Version
Order No.	<a href="#">0475480000</a>	Terminal (busbar connection)
GTIN (EAN)	4008190145668	
Qty.	50 pc(s).	
Type	IK 6 GG ZBE6K	Version
Order No.	<a href="#">0526060000</a>	Cover hood (terminal), Steel
GTIN (EAN)	4008190128647	
Qty.	50 pc(s).	
Type	IK 35/ZB35 BL	Version
Order No.	<a href="#">0502780000</a>	Terminal (busbar connection)
GTIN (EAN)	4008190141455	
Qty.	50 pc(s).	

## 5x25



For protection against overcurrent, we offer cartridge fuse with dimensions 5x25 mm in sizes from 250 mA to 6.3 A.

## General ordering data

Type	G 25/4.00A/F BR	Version
Order No.	<a href="#">0192800000</a>	Miniature fuse, quick-acting, 4 A, G-Si. 5 x 25
GTIN (EAN)	4008190115319	
Qty.	10 pc(s).	
Type	G 25/1.00A/M RT	Version
Order No.	<a href="#">0265800000</a>	Miniature fuse, medium time-lag, 1 A, G-Si. 5 x 25
GTIN (EAN)	4008190141660	
Qty.	10 pc(s).	
Type	G 25/10.0A/M RT	Version
Order No.	<a href="#">0193100000</a>	Miniature fuse, medium time-lag, 10 A, G-Si. 5 x 25
GTIN (EAN)	4008190023799	
Qty.	10 pc(s).	
Type	G 25/0.80A/M GR	Version
Order No.	<a href="#">0646400000</a>	Miniature fuse, medium time-lag, 0.8 A, G-Si. 5 x 25
GTIN (EAN)	4008190060794	
Qty.	10 pc(s).	



## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	G 25/6.30A/F GN	Version
Order No.	<a href="#">0192900000</a>	Miniature fuse, quick-acting, 6.3 A, G-Si. 5 x 25
GTIN (EAN)	4008190135461	
Qty.	10 pc(s).	
Type	G 25/0.25A/M GE	Version
Order No.	<a href="#">0546900000</a>	Miniature fuse, medium time-lag, 0.25 A, G-Si. 5 x 25
GTIN (EAN)	4008190097370	
Qty.	10 pc(s).	
Type	G 25/0.50A/M WS	Version
Order No.	<a href="#">0510300000</a>	Miniature fuse, medium time-lag, 0.5 A, G-Si. 5 x 25
GTIN (EAN)	4008190018368	
Qty.	10 pc(s).	
Type	G 25/2.00A/F BL	Version
Order No.	<a href="#">0192700000</a>	Miniature fuse, quick-acting, 2 A, G-Si. 5 x 25
GTIN (EAN)	4008190176402	
Qty.	10 pc(s).	

## Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/5 MC SDR	Version
Order No.	<a href="#">1609810000</a>	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00
GTIN (EAN)	4008190456597	Weidmueller, To customer specification
Qty.	200 pc(s).	

## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## QL / SAKS



Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

## General ordering data

Type	QL 4 SAKS1	Version
Order No.	<a href="#">0191600000</a>	Cross-connector (terminal), when screwed in, Number of poles: 4,
GTIN (EAN)	4008190105518	Pitch in mm (P): 13.00, Insulated: No, 47 A, grey
Qty.	20 pc(s).	
Type	QL 2 SAKS4	Version
Order No.	<a href="#">0328000000</a>	Cross-connector (terminal), when screwed in, Number of poles: 2,
GTIN (EAN)	4008190071165	Pitch in mm (P): 24.00, Insulated: No, 47 A, grey
Qty.	20 pc(s).	
Type	QL 3 SAKS4	Version
Order No.	<a href="#">0328100000</a>	Cross-connector (terminal), when screwed in, Number of poles: 3,
GTIN (EAN)	4008190097639	Pitch in mm (P): 24.00, Insulated: No, 47 A, grey
Qty.	20 pc(s).	
Type	QL 3 SAKS1	Version
Order No.	<a href="#">0191500000</a>	Cross-connector (terminal), when screwed in, Number of poles: 3,
GTIN (EAN)	4008190036881	Pitch in mm (P): 13.00, Insulated: No, 47 A, grey
Qty.	50 pc(s).	
Type	QL 2 SAKS1	Version
Order No.	<a href="#">0191400000</a>	Cross-connector (terminal), when screwed in, Number of poles: 2,
GTIN (EAN)	4008190123130	Pitch in mm (P): 13.00, Insulated: No, 47 A, grey
Qty.	50 pc(s).	
Type	QL 10 SAKS4	Version
Order No.	<a href="#">0339000000</a>	Cross-connector (terminal), when screwed in, Number of poles: 10,
GTIN (EAN)	4008190025335	Pitch in mm (P): 10.00, Insulated: No, 47 A, grey
Qty.	20 pc(s).	
Type	QL 4 SAKS2	Version
Order No.	<a href="#">0208000000</a>	Cross-connector (terminal), when screwed in, Number of poles: 4,
GTIN (EAN)	4008190069100	Pitch in mm (P): 27.60, Insulated: No, 36 A, grey
Qty.	20 pc(s).	
Type	QL 10 SAKS2	Version
Order No.	<a href="#">0338900000</a>	Cross-connector (terminal), when screwed in, Number of poles: 10,
GTIN (EAN)	4008190105723	Pitch in mm (P): 10.00, Insulated: No, 36 A, grey
Qty.	20 pc(s).	
Type	QL 10 SAKS1	Version
Order No.	<a href="#">0338800000</a>	Cross-connector (terminal), when screwed in, Number of poles: 10,
GTIN (EAN)	4008190127039	Pitch in mm (P): 13.00, Insulated: No, 36 A, grey
Qty.	20 pc(s).	

## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	QL 2 SAKS2	Version
Order No.	<a href="#">0207800000</a>	Cross-connector (terminal), when screwed in, Number of poles: 2,
GTIN (EAN)	4008190144364	Pitch in mm (P): 27.60, Insulated: No, 36 A, grey
Qty.	20 pc(s).	

## QL / RSF1+2



Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

## General ordering data

Type	QL 3 RSF1+2	Version
Order No.	<a href="#">0267500000</a>	Cross-connector (terminal), when screwed in, Number of poles: 3,
GTIN (EAN)	4008190116835	Pitch in mm (P): 11.00, Insulated: No, 57 A, grey
Qty.	50 pc(s).	
Type	QL 10 RSF1+2	Version
Order No.	<a href="#">0341700000</a>	Cross-connector (terminal), when screwed in, Number of poles: 10,
GTIN (EAN)	4008190003173	Pitch in mm (P): 8.00, Insulated: No, grey
Qty.	20 pc(s).	
Type	QL 2 RSF1+2	Version
Order No.	<a href="#">0267400000</a>	Cross-connector (terminal), when screwed in, Number of poles: 2,
GTIN (EAN)	4008190139988	Pitch in mm (P): 11.00, Insulated: No, 57 A, grey
Qty.	50 pc(s).	
Type	QL 4 RSF1+2	Version
Order No.	<a href="#">0267600000</a>	Cross-connector (terminal), when screwed in, Number of poles: 4,
GTIN (EAN)	4008190174859	Pitch in mm (P): 11.00, Insulated: No, 41 A, grey
Qty.	50 pc(s).	

## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## SAK-Series



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

## General ordering data

Type	EW 35	Version
Order No.	<a href="#">0383560000</a>	End bracket, Wemid, beige, Rail: TS 35, when screwed in
GTIN (EAN)	4008190181314	
Qty.	50 pc(s).	

## QL / SAKA

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.



## General ordering data

Type	QL 3 SAKA10	Version
Order No.	<a href="#">0135600000</a>	Cross-connector (terminal), when screwed in, Number of poles: 3,
GTIN (EAN)	4008190032081	Pitch in mm (P): 12.00, Insulated: No, 36 A, grey
Qty.	50 pc(s).	
Type	QL 10 SAKA10	Version
Order No.	<a href="#">0338500000</a>	Cross-connector (terminal), when screwed in, Number of poles: 10,
GTIN (EAN)	4008190063313	Pitch in mm (P): 6.00, Insulated: No, 57 A, grey
Qty.	20 pc(s).	
Type	QL 2 SAKA10	Version
Order No.	<a href="#">0135500000</a>	Cross-connector (terminal), when screwed in, Number of poles: 2,
GTIN (EAN)	4008190099404	Pitch in mm (P): 12.00, Insulated: No, 32 A, grey
Qty.	50 pc(s).	
Type	QL 4 SAKA10	Version
Order No.	<a href="#">0135700000</a>	Cross-connector (terminal), when screwed in, Number of poles: 4,
GTIN (EAN)	4008190118822	Pitch in mm (P): 12.00, Insulated: No, 36 A, grey
Qty.	50 pc(s).	
Type	QL 10 SAKB10	Version
Order No.	<a href="#">0338400000</a>	Cross-connector (terminal), when screwed in, Number of poles: 10,
GTIN (EAN)	4008190139452	Pitch in mm (P): 6.00, Insulated: No, 36 A, grey
Qty.	20 pc(s).	

## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Test plugs




Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

## General ordering data

Type	PS 2.3 RT	Version
Order No.	<a href="#">0180400000</a>	Test adapter (terminal), 20 mA
GTIN (EAN)	4008190060121	
Qty.	20 pc(s).	
Type	PS 2.0 OR	Version
Order No.	<a href="#">0293800000</a>	Test adapter (terminal), 20 mA
GTIN (EAN)	4008190042356	
Qty.	20 pc(s).	
Type	ZS 2.3/4	Version
Order No.	<a href="#">0249600000</a>	Plug (terminal), Plug-in connection, Number of poles: 4, red
GTIN (EAN)	4008190022785	
Qty.	20 pc(s).	
Type	FZS 2/4 RT/80 SAKT4	Version
Order No.	<a href="#">1276300000</a>	Plug (terminal), Plug-in connection, Number of poles: 1, red
GTIN (EAN)	4008190026080	
Qty.	20 pc(s).	
Type	PS 4 F.STB 4	Version
Order No.	<a href="#">0299600000</a>	Test adapter (terminal)
GTIN (EAN)	4008190074043	
Qty.	20 pc(s).	

## TS 32



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

## General ordering data

Type	EWK 1	Version
Order No.	<a href="#">0206160000</a>	End bracket, Wemid, beige, Rail: TS 32, when screwed in
GTIN (EAN)	4008190080020	
Qty.	50 pc(s).	

## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	WEW 32/1	Version
Order No.	<a href="#">1067600000</a>	End bracket, PA 66 GF 30, dark beige, Rail: TS 32, when screwed in
GTIN (EAN)	4008190099657	
Qty.	50 pc(s).	
Type	EWK 2	Version
Order No.	<a href="#">0199360000</a>	End bracket, Wemid, beige, Rail: TS 32, when screwed in
GTIN (EAN)	4008190023546	
Qty.	50 pc(s).	
Type	EWK 1 ALT	Version
Order No.	<a href="#">0495160000</a>	End bracket, Polyamide 66, beige, Rail: TS 32, when screwed in
GTIN (EAN)	4008190160777	
Qty.	50 pc(s).	

## Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/6.5 MC SDR	Version
Order No.	<a href="#">1609850000</a>	Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50
GTIN (EAN)	4008190456610	Weidmueller, To customer specification
Qty.	180 pc(s).	

## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/6 MC SDR	Version
Order No.	<a href="#">1609830000</a>	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
GTIN (EAN)	4008190456603	Weidmueller, To customer specification
Qty.	200 pc(s).	

## Uninsulated



Uninsulated bus bar tap-off terminals offer a space-saving option for connecting conductors on a bus bar.

## General ordering data

Type	ZB 16 ZKSC	Version
Order No.	<a href="#">0316600000</a>	Clamping yoke (bus-bar)
GTIN (EAN)	4008190145989	
Qty.	50 pc(s).	

Type	ZBE 6	Version
Order No.	<a href="#">0459500000</a>	Clamping yoke (bus-bar)
GTIN (EAN)	4008190032692	
Qty.	50 pc(s).	

Type	ZB 35/M6X16	Version
Order No.	<a href="#">0266500000</a>	Clamping yoke (bus-bar)
GTIN (EAN)	4008190102814	
Qty.	20 pc(s).	

## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	ZB 4	Version
Order No.	<a href="#">0316500000</a>	Clamping yoke (bus-bar)
GTIN (EAN)	4008190061999	
Qty.	50 pc(s).	
Type	ZB 4/6	Version
Order No.	<a href="#">0556700000</a>	Clamping yoke (bus-bar)
GTIN (EAN)	4008190188412	
Qty.	50 pc(s).	

## QL / SAKH 10



Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

## General ordering data

Type	QL 3 SAKH10	Version
Order No.	<a href="#">0131500000</a>	Cross-connector (terminal), when screwed in, Number of poles: 3,
GTIN (EAN)	4008190056490	Pitch in mm (P): 14.00, Insulated: No, 36 A, grey
Qty.	50 pc(s).	
Type	QL 2 SAKH10	Version
Order No.	<a href="#">0131400000</a>	Cross-connector (terminal), when screwed in, Number of poles: 2,
GTIN (EAN)	4008190114237	Pitch in mm (P): 14.00, Insulated: No, 36 A, grey
Qty.	50 pc(s).	

## W-Series



A partition plate is used for the optical separation of circuits or used for electrical isolation from neighbouring cross-connectors. In contrast to the end plate, the contour can be larger than the adjacent terminal blocks. However, it should not be smaller, as otherwise the required clearance and creepage distances within the application can no longer be maintained.

## General ordering data

Type	WTW EN	Version
Order No.	<a href="#">1058800000</a>	Partition plate (terminal), Intermediate plate, 86 mm x 62 mm, dark
GTIN (EAN)	4008190140175	beige
Qty.	20 pc(s).	



## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## QL / SAK 10



Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

## General ordering data

Type	QL 2 SAKB10	Version
Order No.	<a href="#">0114100000</a>	Cross-connector (terminal), when screwed in, Number of poles: 2,
GTIN (EAN)	4008190056605	Pitch in mm (P): 10.00, Insulated: No, 36 A, grey
Qty.	100 pc(s).	

## SAK-Series



SAK  
Series

Warning covers with a flash symbol provide more safety for man and machine. They are used where external voltage must be indicated within the application.


## General ordering data

Type	AD 4 SAK10	Version
Order No.	<a href="#">0178600000</a>	Terminal cover, PVC, yellow, Height: 39.6 mm, Width: 25 mm, Depth:
GTIN (EAN)	4008190068288	1 mm
Qty.	50 pc(s).	

**SAKS 1/35 G20 LD 24VDC**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Accessories****E 16**

Weidmueller offers NEOZED fuses in E 16 design in sizes from 10 A to 25 A.

**General ordering data**

Type	E 16/25A GE TNDZ	Version
Order No.	<a href="#">0208800000</a>	Active components, Cartridge fuse
GTIN (EAN)	4008190037314	
Qty.	25 pc(s).	
Type	E 16/10A RT TNDZ	Version
Order No.	<a href="#">0208500000</a>	Active components, Cartridge fuse
GTIN (EAN)	4008190067120	
Qty.	25 pc(s).	
Type	E 16/16A GR TNDZ	Version
Order No.	<a href="#">0208600000</a>	Active components, Cartridge fuse
GTIN (EAN)	4008190015121	
Qty.	25 pc(s).	
Type	E 16/20A BL TNDZ	Version
Order No.	<a href="#">0208700000</a>	Active components, Cartridge fuse
GTIN (EAN)	4008190044886	
Qty.	25 pc(s).	

## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/6.5 MC NE WS	Version
Order No.	<a href="#">1609840000</a>	Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50
GTIN (EAN)	4008190203429	Weidmueller, white
Qty.	900 pc(s).	

## Plus



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/8 PLUS MC NE WS	Version
Order No.	<a href="#">1046350000</a>	Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00
GTIN (EAN)	4032248782055	Weidmueller, white
Qty.	800 pc(s).	

## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Copper



Of all the metals used, copper has the best electrical conductivity, which results in the highest short-circuit resistance. This makes the copper busbar the most widely used variant.

## General ordering data

Type	NSCH 1M	Version
Order No.	<a href="#">0280200000</a>	Busbar (terminal)
GTIN (EAN)	4008190012953	
Qty.	10 m	

## DEK 5/8



## WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

## Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

## General ordering data

Type	DEK 5/8 MM WS	Version
Order No.	<a href="#">2007130000</a>	Dekafix, Terminal marker, 5 x 8 mm, Weidmueller, white
GTIN (EAN)	4050118392012	
Qty.	500 pc(s).	

**SAKS 1/35 G20 LD 24VDC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****QL mounting screws**

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Type	SS M3 D 128-A 3	Version
Order No.	<a href="#">0164400000</a>	Lock washer, Copper
GTIN (EAN)	4008190035914	
Qty.	50 pc(s).	

**Cover profiles**

Cover profiles provide protection against external impact on functional areas of the terminal blocks or in combination with our support brackets for the entire terminal strip. They provide protection against electric shock caused by accidental contact with live parts due to operation or faults.

**General ordering data**

Type	ADP 2/HP2 1M	Version
Order No.	<a href="#">0485300000</a>	SAK Series, Cover profile, Transparent, 1000 mm
GTIN (EAN)	4008190051716	
Qty.	1 m	

## SAKS 1/35 G20 LD 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Connection sleeves



## General ordering data

Type	VH 17.5/5/3.4	Version
Order No.	<a href="#">0285200000</a>	Connecting sleeve (terminal), Height: 5 mm, Width: 5 mm, Depth:
GTIN (EAN)	4008190054717	17.5 mm, Copper
Qty.	50 pc(s).	
Type	VL 2 SAK6N/SAKT	Version
Order No.	<a href="#">0194700000</a>	Cross-connector (terminal), when screwed in, Number of poles: 2,
GTIN (EAN)	4008190148027	Pitch in mm (P): 8.00, Insulated: No, 32 A, grey
Qty.	50 pc(s).	
Type	VH 12/4.9/3.3	Version
Order No.	<a href="#">0249000000</a>	Connecting sleeve (terminal), Height: 4.9 mm, Width: 4.9 mm, Depth:
GTIN (EAN)	4008190129507	12 mm, Copper
Qty.	100 pc(s).	
Type	VL 2 SAK16/SAKA	Version
Order No.	<a href="#">0135800000</a>	Cross-connector (terminal), when screwed in, Number of poles: 2,
GTIN (EAN)	4008190132088	Pitch in mm (P): 12.00, Insulated: No, 57 A, grey
Qty.	50 pc(s).	
Type	VH 13.6/6.3/4.3	Version
Order No.	<a href="#">0299700000</a>	Connecting sleeve (terminal), Height: 7 mm, Width: 7 mm, Depth:
GTIN (EAN)	4008190018313	13.6 mm, Cu Zn
Qty.	50 pc(s).	
Type	VH 20/5/3.4	Version
Order No.	<a href="#">0446100000</a>	Dummy fuse
GTIN (EAN)	4008190519742	
Qty.	10 pc(s).	
Type	VL 2 SAK6/10/SAKB	Version
Order No.	<a href="#">0135900000</a>	Cross-connector (terminal), when screwed in, Number of poles: 2,
GTIN (EAN)	4008190036409	Pitch in mm (P): 6.50, Insulated: No, 32 A, grey
Qty.	50 pc(s).	
Type	VH 23/6/4.2 SAKA10	Version
Order No.	<a href="#">0348700000</a>	Connecting sleeve (terminal), Height: 6 mm, Width: 6 mm, Depth: 23
GTIN (EAN)	4008190185923	mm, Cu Zn
Qty.	50 pc(s).	
Type	VL 2 RSF 1+2	Version
Order No.	<a href="#">0528400000</a>	Cross-connector (terminal), when screwed in, Number of poles: 2,
GTIN (EAN)	4008190059095	Pitch in mm (P): 11.00, Insulated: No, 32 A, grey
Qty.	10 pc(s).	

**SAKS 1/35 G20 LD 24VDC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories**

Type	VH 19/5/3.4	Version
Order No.	<a href="#">0285100000</a>	Connecting sleeve (terminal), Height: 5 mm, Width: 5 mm, Depth:
GTIN (EAN)	4008190189297	17.5 mm, Cu Zn
Qty.	50 pc(s).	