

**SAKS 4/35****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image****General ordering data**

Version	Fuse terminal, Screw connection, medium yellow, 10 mm <sup>2</sup> , 16 A, 400 V, Number of connections: 2, Number of levels: 1, TS 35, V-0, 5VA, KrG, E14
Order No.	<a href="#">0501820000</a>
Type	SAKS 4/35
GTIN (EAN)	4008190090166
Qty.	20 pc(s).

## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	65 mm	Depth (inches)	2.559 inch
Depth including DIN rail	66 mm	Height	75 mm
Height (inches)	2.953 inch	Width	24 mm
Width (inches)	0.945 inch	Net weight	77.2 g

## Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

## Material data

Material	KrG	Colour	medium yellow
UL 94 flammability rating	V-0, 5VA		

## System specifications

Version	Screw connection, Fuse cartridge, for screwable cross-connection, One end without connector	End cover plate required	No
Number of potentials	1	Number of levels	1
Number of clamping points per level	2	Number of potentials per tier	1
Levels cross-connected internally	No	PE connection	No
Rail	TS 35	N-function	No
PE function	No	PEN function	No

## Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Number of similar terminals	1	Open sides	closed
Type of mounting	Snap-on		

## CSA rating data

Certificate No. (CSA)	12400-188	Current size B (CSA)	30 A
Current size C (CSA)	30 A	Current size D (CSA)	5 A
Voltage size B (CSA)	600 V	Voltage size C (CSA)	600 V
Voltage size D (CSA)	600 V	Wire cross section max. (CSA)	8 AWG
Wire cross section min. (CSA)	22 AWG		

## Conductors for clamping (additional connection)

Conductor cross-section, flexible plus plastic collar DIN 46228/1, further connection, max.	10 mm <sup>2</sup>	Connection direction	on side
Connection type, additional connection	Screw connection		

## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Conductors for clamping (rated connection)

Blade size	1.0 x 5.5 mm	Clamping range, max.	16 mm <sup>2</sup>
Clamping range, min.	0.33 mm <sup>2</sup>	Clamping screw	M 4
Connection cross-section, stranded, max.	10 mm <sup>2</sup>	Connection cross-section, stranded, min.	1.5 mm <sup>2</sup>
Connection direction	on side	Gauge to IEC 60947-1	B6
Number of connections	2	Stripping length	14 mm
Tightening torque, max.	2.4 Nm	Tightening torque, min.	1.2 Nm
Torque level with DMS electric screw-driver	4	Type of connection	Screw connection
Type of connection 2	Screw connection	Wire connection cross section AWG, max.	AWG 8
Wire connection cross section AWG, min.	AWG 22	Wire connection cross section, finely stranded, max.	10 mm <sup>2</sup>
Wire connection cross section, finely stranded, min.	0.5 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	10 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.5 mm <sup>2</sup>	Wire connection cross-section, solid core, max.	16 mm <sup>2</sup>
Wire connection cross-section, solid core, min.	0.5 mm <sup>2</sup>		

## Display element

Type of voltage for indicator	AC/DC
-------------------------------	-------

## Fuse terminals

Cartridge fuse	E14	Display	Without LED
Fuse holder (cartridge holder)	for screw fixing	Operating voltage, max.	400 V
Type of voltage for indicator	AC/DC		

## General

Installation advice	Direct mounting	Rail	TS 35
Standards	IEC 60947-7-3	Wire connection cross section AWG, max.	AWG 8
Wire connection cross section AWG, min.	AWG 22		

## Rating data

Rated cross-section	10 mm <sup>2</sup>	Rated voltage	400 V
Rated DC voltage	400 V	Rated current	16 A
Current at maximum wires	16 A	Standards	IEC 60947-7-3
Volume resistance according to IEC 60947-7-x	0.56 mΩ	Rated impulse withstand voltage	6 kV
Power loss in accordance with IEC 60947-7-x	1.82 W	Pollution severity	3

## UL rating data

Certificate No. (UR)	E60693	Conductor size Factory wiring max. (UR)	8 AWG
Conductor size Factory wiring min. (UR)	26 AWG	Conductor size Field wiring max. (UR)	8 AWG
Conductor size Field wiring min. (UR)	22 AWG	Current size C (UR)	30 A
Voltage size C (UR)	600 V		

Creation date August 29, 2024 5:27:42 PM CEST

## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Classifications

ETIM 6.0	EC000899	ETIM 7.0	EC000899
ETIM 8.0	EC000899	ETIM 9.0	EC000899
ECLASS 9.0	27-14-11-16	ECLASS 9.1	27-14-11-16
ECLASS 10.0	27-14-11-16	ECLASS 11.0	27-14-11-16
ECLASS 12.0	27-14-11-16	ECLASS 13.0	27-25-01-13
ECLASS 14.0	27-25-01-13		

## Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

## Important note

Product information	The voltage depends on the selected fuse element or the selected indicator light
---------------------	--

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E60693

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">Lloyds Register Certificate</a> <a href="#">Declaration of Conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Fuse holder



The fuse holder SIHA quickly turns a disconnect terminal into a fuse terminal: simply remove the disconnect lever and attach the fuse unit.

## General ordering data

Type	SK G20/SAKS1	Version
Order No.	<a href="#">0282100000</a>	Screw cover cap (terminal)
GTIN (EAN)	4008190004606	
Qty.	20 pc(s).	
Type	SK SAKS1/G25	Version
Order No.	<a href="#">0282000000</a>	Screw cover cap (terminal)
GTIN (EAN)	4008190078492	
Qty.	20 pc(s).	
Type	SK E16/SAKS2	Version
Order No.	<a href="#">0284110000</a>	Screw cover cap (terminal)
GTIN (EAN)	4008190006204	
Qty.	25 pc(s).	
Type	SK E14 SAKS4	Version
Order No.	<a href="#">0339410000</a>	Screw cover cap (terminal)
GTIN (EAN)	4008190032104	
Qty.	20 pc(s).	
Type	SK E18 SAKS5	Version
Order No.	<a href="#">0359310000</a>	Screw cover cap (terminal)
GTIN (EAN)	4008190002121	
Qty.	20 pc(s).	

## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Plus



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/8 PLUS MC NE WS	Version
Order No.	<a href="#">1046350000</a>	Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00
GTIN (EAN)	4032248782055	Weidmueller, white
Qty.	800 pc(s).	

## Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/8 PLUS MC SDR	Version
Order No.	<a href="#">1046370000</a>	Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00
GTIN (EAN)	4032248782079	Weidmueller, To customer specification
Qty.	160 pc(s).	

## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	DEK 5/8 MC SDR	Version
Order No.	<a href="#">1856750000</a>	Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00
GTIN (EAN)	4032248400867	Weidmueller, To customer specification
Qty.	160 pc(s).	

## SAK-Series



End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

## General ordering data

Type	AP KSKM	Version
Order No.	<a href="#">9509630000</a>	SAK Series, End plate, 1.5 mm, beige, Direct mounting
GTIN (EAN)	4008190456771	
Qty.	20 pc(s).	
Type	AP SAKS1+3 KRG	Version
Order No.	<a href="#">0191320000</a>	End plate (terminals), dark beige, yellow, Height: 54 mm, Width: 3 mm, V-O, KrG
GTIN (EAN)	4008190031688	
Qty.	20 pc(s).	
Type	AP SAKB/C/T KRG	Version
Order No.	<a href="#">0146720000</a>	End plate (terminals), dark beige, yellow, Height: 65 mm, Width: 3 mm, V-O, KrG
GTIN (EAN)	4008190027995	
Qty.	20 pc(s).	
Type	AP SAKS1+3 KRG/DB	Version
Order No.	<a href="#">0191300000</a>	End plate (terminals), dark beige, Height: 54 mm, Width: 3 mm, V-O, KrG
GTIN (EAN)	4008190099763	
Qty.	20 pc(s).	
Type	AP SAKA KRG	Version
Order No.	<a href="#">0134220000</a>	End plate (terminals), dark beige, yellow, Height: 82 mm, Width: 3 mm, V-O, KrG
GTIN (EAN)	4008190167943	
Qty.	20 pc(s).	
Type	AP RSF1 KRG	Version
Order No.	<a href="#">0270420000</a>	End plate (terminals), medium yellow, Height: 50 mm, Width: 3 mm, V-O, KrG
GTIN (EAN)	4008190099107	
Qty.	10 pc(s).	

## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## QL / SAKH 10



Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

## General ordering data

Type	QL 3 SAKH10	Version
Order No.	<a href="#">0131500000</a>	Cross-connector (terminal), when screwed in, grey, 36 A, Number of
GTIN (EAN)	4008190056490	poles: 3, Pitch in mm (P): 14.00, Insulated: No, Width: 26.8 mm
Qty.	50 pc(s).	
Type	QL 2 SAKH10	Version
Order No.	<a href="#">0131400000</a>	Cross-connector (terminal), when screwed in, grey, 36 A, Number of
GTIN (EAN)	4008190114237	poles: 2, Pitch in mm (P): 14.00, Insulated: No, Width: 16.9 mm
Qty.	50 pc(s).	

## Steel



Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

## General ordering data

Type	TS 32X15/LL 2M/ST/ZN	Version
Order No.	<a href="#">0514400000</a>	Terminal rail, Accessories, Steel, galvanic zinc plated and passivated,
GTIN (EAN)	4008190086152	Width: 2000 mm, Height: 33 mm, Depth: 15 mm, Slit width: 5.20
Qty.	2 m	mm, Slit length: 25.00 mm



## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Connection sleeves



## General ordering data

Type	VL 2 SAK6/10/SAKB	Version
Order No.	<a href="#">0135900000</a>	Cross-connector (terminal), when screwed in, grey, 32 A, Number of
GTIN (EAN)	4008190036409	poles: 2, Pitch in mm (P): 6.50, Insulated: No, Width: 1.5 mm
Qty.	50 pc(s).	
Type	VH 19/5/3.4	Version
Order No.	<a href="#">0285100000</a>	Connecting sleeve (terminal), when screwed in, Width: 5, Height: 5
GTIN (EAN)	4008190189297	mm, Depth: 17.5 mm, Number of poles: 1, Cu Zn
Qty.	50 pc(s).	
Type	VH 13.6/6.3/4.3	Version
Order No.	<a href="#">0299700000</a>	Connecting sleeve (terminal), when screwed in, Width: 7 mm, Height:
GTIN (EAN)	4008190018313	7 mm, Depth: 13.6 mm, Number of poles: 1, Cu Zn
Qty.	50 pc(s).	
Type	VL 2 SAK6N/SAKT	Version
Order No.	<a href="#">0194700000</a>	Cross-connector (terminal), when screwed in, grey, 32 A, Number of
GTIN (EAN)	4008190148027	poles: 2, Pitch in mm (P): 8.00, Insulated: No, Width: 7 mm
Qty.	50 pc(s).	
Type	VH 23/6/4.2 SAKA10	Version
Order No.	<a href="#">0348700000</a>	Connecting sleeve (terminal), when screwed in, Width: 6, Height: 6
GTIN (EAN)	4008190185923	mm, Depth: 23 mm, Number of poles: 1, Cu Zn
Qty.	50 pc(s).	
Type	VL 2 SAK16/SAKA	Version
Order No.	<a href="#">0135800000</a>	Cross-connector (terminal), when screwed in, grey, 57 A, Number of
GTIN (EAN)	4008190132088	poles: 2, Pitch in mm (P): 12.00, Insulated: No, Width: 8 mm
Qty.	50 pc(s).	
Type	VH 12/4.9/3.3	Version
Order No.	<a href="#">0249000000</a>	Connecting sleeve (terminal), when screwed in, Width: 4.9, Height:
GTIN (EAN)	4008190129507	4.9 mm, Depth: 12 mm, Copper
Qty.	100 pc(s).	
Type	VL 2 RSF 1+2	Version
Order No.	<a href="#">0528400000</a>	Cross-connector (terminal), when screwed in, grey, 32 A, Number of
GTIN (EAN)	4008190059095	poles: 2, Pitch in mm (P): 11.00, Insulated: No, Width: 19 mm
Qty.	10 pc(s).	
Type	VH 17.5/5/3.4	Version
Order No.	<a href="#">0285200000</a>	Connecting sleeve (terminal), when screwed in, Width: 5 mm, Height:
GTIN (EAN)	4008190054717	5 mm, Depth: 17.5 mm, Number of poles: 1, Copper
Qty.	50 pc(s).	

**SAKS 4/35****Weidmüller Interface GmbH & Co. KG**


Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories**

Type	VH 20/5/3.4	Version
Order No.	<a href="#">0446100000</a>	Dummy fuse
GTIN (EAN)	4008190519742	
Qty.	10 pc(s).	

**E 16**

Weidmueller offers NEOZED fuses in E 16 design in sizes from 10 A to 25 A.

**General ordering data**

Type	E 16/10A RT TNDZ	Version
Order No.	<a href="#">0208500000</a>	Active components, Cartridge fuse
GTIN (EAN)	4008190067120	
Qty.	25 pc(s).	
Type	E 16/20A BL TNDZ	Version
Order No.	<a href="#">0208700000</a>	Active components, Cartridge fuse
GTIN (EAN)	4008190044886	
Qty.	25 pc(s).	
Type	E 16/25A GE TNDZ	Version
Order No.	<a href="#">0208800000</a>	Active components, Cartridge fuse
GTIN (EAN)	4008190037314	
Qty.	25 pc(s).	
Type	E 16/16A GR TNDZ	Version
Order No.	<a href="#">0208600000</a>	Active components, Cartridge fuse
GTIN (EAN)	4008190015121	
Qty.	25 pc(s).	

## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Copper



Of all the metals used, copper has the best electrical conductivity, which results in the highest short-circuit resistance. This makes the copper busbar the most widely used variant.

## General ordering data

Type	NSCH 1M	Version
Order No.	<a href="#">0280200000</a>	Busbar (terminal), Natural, Height: 15 mm, Depth: 2 mm, Copper
GTIN (EAN)	4008190012953	
Qty.	10 m	

## Copper



Of all the metals used, copper has the best electrical conductivity, which results in the highest short-circuit resistance. This makes the copper busbar the most widely used variant.

## General ordering data

Type	SSCH 10X3X1000 CU/SN	Version
Order No.	<a href="#">0348900000</a>	Busbar (terminal), silver, Height: 1000 mm, Depth: 3 mm, Copper
GTIN (EAN)	4008190024802	
Qty.	1 m	
Type	SSCH 6X6X1000 CU/SN	Version
Order No.	<a href="#">0571300000</a>	Busbar (terminal), silver, Height: 1000 mm, Depth: 6 mm, Copper
GTIN (EAN)	4008190015039	
Qty.	1 m	
Type	SSCH 7.3X1.2X1000	Version
Order No.	<a href="#">1071200000</a>	Busbar (terminal), silver, Height: 1000 mm, Depth: 1.2 mm, Copper
GTIN (EAN)	4008190279172	
Qty.	1 m	

## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## TS 32


 TS 32

Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

## General ordering data

Type	EWK 1	Version
Order No.	<a href="#">0206160000</a>	End bracket, beige, TS 32, V-0, Wemid, Width: 9 mm, 100 °C
GTIN (EAN)	4008190080020	
Qty.	50 pc(s).	
Type	EWK 2	Version
Order No.	<a href="#">0199360000</a>	End bracket, beige, TS 32, V-0, Wemid, Width: 15 mm, 100 °C
GTIN (EAN)	4008190023546	
Qty.	50 pc(s).	
Type	WEW 32/1	Version
Order No.	<a href="#">1067600000</a>	End bracket, dark beige, TS 32, V-2, PA 66 GF 30, Width: 12 mm, 100 °C
GTIN (EAN)	4008190099657	
Qty.	50 pc(s).	
Type	EWK 1 ALT	Version
Order No.	<a href="#">0495160000</a>	End bracket, beige, TS 32, V-2, Polyamide 66, Width: 8 mm, 100 °C
GTIN (EAN)	4008190160777	
Qty.	50 pc(s).	

## QL / SAKA

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.



## General ordering data

Type	QL 2 SAKA10	Version
Order No.	<a href="#">0135500000</a>	Cross-connector (terminal), when screwed in, grey, 32 A, Number of poles: 2, Pitch in mm (P): 12.00, Insulated: No, Width: 19.9 mm
GTIN (EAN)	4008190099404	
Qty.	50 pc(s).	
Type	QL 10 SAKA10	Version
Order No.	<a href="#">0338500000</a>	Cross-connector (terminal), when screwed in, grey, 57 A, Number of poles: 10, Pitch in mm (P): 6.00, Insulated: No, Width: 115.1 mm
GTIN (EAN)	4008190063313	
Qty.	20 pc(s).	

## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold


Germany

www.weidmueller.com

## Accessories

Type	QL 3 SAKA10	Version
Order No.	<a href="#">0135600000</a>	Cross-connector (terminal), when screwed in, grey, 36 A, Number of
GTIN (EAN)	4008190032081	poles: 3, Pitch in mm (P): 12.00, Insulated: No, Width: 31.8 mm
Qty.	50 pc(s).	
Type	QL 4 SAKA10	Version
Order No.	<a href="#">0135700000</a>	Cross-connector (terminal), when screwed in, grey, 36 A, Number of
GTIN (EAN)	4008190118822	poles: 4, Pitch in mm (P): 12.00, Insulated: No, Width: 43.7 mm
Qty.	50 pc(s).	
Type	QL 10 SAKB10	Version
Order No.	<a href="#">0338400000</a>	Cross-connector (terminal), when screwed in, grey, 36 A, Number of
GTIN (EAN)	4008190139452	poles: 10, Pitch in mm (P): 6.00, Insulated: No, Width: 97 mm
Qty.	20 pc(s).	

## SAK-Series



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

## General ordering data

Type	EW 35	Version
Order No.	<a href="#">0383560000</a>	End bracket, beige, TS 35, V-2, Wemid, Width: 8.5 mm, 100 °C
GTIN (EAN)	4008190181314	
Qty.	50 pc(s).	

## QL / SAK 10

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.



## General ordering data

Type	QL 2 SAKB10	Version
Order No.	<a href="#">0114100000</a>	Cross-connector (terminal), when screwed in, grey, 36 A, Number of
GTIN (EAN)	4008190056605	poles: 2, Pitch in mm (P): 10.00, Insulated: No, Width: 17 mm
Qty.	100 pc(s).	

## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Testsockets



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

## General ordering data

Type	STB 18/RSF1	Version
Order No.	<a href="#">0286500000</a>	Socket (terminal), Plug-in depth: 15 mm, Depth: 23 mm
GTIN (EAN)	4008190515591	
Qty.	20 pc(s).	
Type	STB 13.5/D6/4/M4 SAKA10	Version
Order No.	<a href="#">0135200000</a>	SAK Series, Socket
GTIN (EAN)	4008190172862	
Qty.	50 pc(s).	

## Test plugs



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

## General ordering data

Type	PS 2.3 RT	Version
Order No.	<a href="#">0180400000</a>	Test adapter (terminal), 230 V, 20 mA
GTIN (EAN)	4008190060121	
Qty.	20 pc(s).	
Type	PS 4 F.STB 4	Version
Order No.	<a href="#">0299600000</a>	Test adapter (terminal), 230 V
GTIN (EAN)	4008190074043	
Qty.	20 pc(s).	

## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## QL / RSF1+2



Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

## General ordering data

Type	QL 10 RSF1+2	Version
Order No.	<a href="#">0341700000</a>	Cross-connector (terminal), when screwed in, grey, 20 A, Number of
GTIN (EAN)	4008190003173	poles: 10, Pitch in mm (P): 8.00, Insulated: No, Width: 106 mm
Qty.	20 pc(s).	
Type	QL 4 RSF1+2	Version
Order No.	<a href="#">0267600000</a>	Cross-connector (terminal), when screwed in, grey, 41 A, Number of
GTIN (EAN)	4008190174859	poles: 4, Pitch in mm (P): 11.00, Insulated: No, Width: 40 mm
Qty.	50 pc(s).	
Type	QL 3 RSF1+2	Version
Order No.	<a href="#">0267500000</a>	Cross-connector (terminal), when screwed in, grey, 57 A, Number of
GTIN (EAN)	4008190116835	poles: 3, Pitch in mm (P): 11.00, Insulated: No, Width: 29 mm
Qty.	50 pc(s).	
Type	QL 2 RSF1+2	Version
Order No.	<a href="#">0267400000</a>	Cross-connector (terminal), when screwed in, grey, 57 A, Number of
GTIN (EAN)	4008190139988	poles: 2, Pitch in mm (P): 11.00, Insulated: No, Width: 18 mm
Qty.	50 pc(s).	

## Miscellaneous



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

## General ordering data

Type	SS M4 D 128-A 4	Version
Order No.	<a href="#">0136400000</a>	Lock washer, Copper
GTIN (EAN)	4008190118143	
Qty.	100 pc(s).	

## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## W-Series



A partition plate is used for the optical separation of circuits or used for electrical isolation from neighbouring cross-connectors. In contrast to the end plate, the contour can be larger than the adjacent terminal blocks. However, it should not be smaller, as otherwise the required clearance and creepage distances within the application can no longer be maintained.

## General ordering data

Type	WTW EN	Version
Order No.	<a href="#">1058800000</a>	Partition plate (terminal), dark beige, Height: 86 mm, Width: 3 mm,
GTIN (EAN)	4008190140175	V-O, Wemid
Qty.	20 pc(s).	

## Fixing screws



Fixing screws fix the short current bridge within the application. If the short current bridge is slided between two adjacent terminal blocks into the short circuit position, it can be fixed by means of a fastening screw. This ensures a permanent connection or short circuit.

## General ordering data

Type	KISC M3X20 SAK10 CU5	Version
Order No.	<a href="#">0377100000</a>	SAK Series, Mounting screw, Copper
GTIN (EAN)	4008190060350	
Qty.	100 pc(s).	



## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## DEK 5/6



## WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

## Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

## General ordering data

Type	DEK 5/6 MM WS	Version
Order No.	<a href="#">2007120000</a>	Dekafix, Terminal marker, 5 x 6 mm, Weidmueller, white
GTIN (EAN)	4050118392104	
Qty.	600 pc(s).	

## QL / SAKS

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.



## General ordering data

Type	QL 10 SAKS2	Version
Order No.	<a href="#">0338900000</a>	Cross-connector (terminal), when screwed in, grey, 36 A, Number of poles: 10, Pitch in mm (P): 10.00, Insulated: No, Width: 261.4 mm
GTIN (EAN)	4008190105723	
Qty.	20 pc(s).	
Type	QL 3 SAKS4	Version
Order No.	<a href="#">0328100000</a>	Cross-connector (terminal), when screwed in, grey, 47 A, Number of poles: 3, Pitch in mm (P): 24.00, Insulated: No, Width: 58 mm
GTIN (EAN)	4008190097639	
Qty.	20 pc(s).	

## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	QL 2 SAKS4	Version
Order No.	<a href="#">0328000000</a>	Cross-connector (terminal), when screwed in, grey, 47 A, Number of
GTIN (EAN)	4008190071165	poles: 2, Pitch in mm (P): 24.00, Insulated: No, Width: 34 mm
Qty.	20 pc(s).	
Type	QL 10 SAKS4	Version
Order No.	<a href="#">0339000000</a>	Cross-connector (terminal), when screwed in, grey, 47 A, Number of
GTIN (EAN)	4008190025335	poles: 10, Pitch in mm (P): 10.00, Insulated: No, Width: 226 mm
Qty.	20 pc(s).	
Type	QL 3 SAKS1	Version
Order No.	<a href="#">0191500000</a>	Cross-connector (terminal), when screwed in, grey, 47 A, Number of
GTIN (EAN)	4008190036881	poles: 3, Pitch in mm (P): 13.00, Insulated: No, Width: 31.9 mm
Qty.	50 pc(s).	
Type	QL 4 SAKS1	Version
Order No.	<a href="#">0191600000</a>	Cross-connector (terminal), when screwed in, grey, 47 A, Number of
GTIN (EAN)	4008190105518	poles: 4, Pitch in mm (P): 13.00, Insulated: No, Width: 44.7 mm
Qty.	20 pc(s).	
Type	QL 2 SAKS1	Version
Order No.	<a href="#">0191400000</a>	Cross-connector (terminal), when screwed in, grey, 47 A, Number of
GTIN (EAN)	4008190123130	poles: 2, Pitch in mm (P): 13.00, Insulated: No, Width: 18.9 mm
Qty.	50 pc(s).	
Type	QL 2 SAKS2	Version
Order No.	<a href="#">0207800000</a>	Cross-connector (terminal), when screwed in, grey, 36 A, Number of
GTIN (EAN)	4008190144364	poles: 2, Pitch in mm (P): 27.60, Insulated: No, Width: 40.6 mm
Qty.	20 pc(s).	
Type	QL 10 SAKS1	Version
Order No.	<a href="#">0338800000</a>	Cross-connector (terminal), when screwed in, grey, 36 A, Number of
GTIN (EAN)	4008190127039	poles: 10, Pitch in mm (P): 13.00, Insulated: No, Width: 122.1 mm
Qty.	20 pc(s).	
Type	QL 4 SAKS2	Version
Order No.	<a href="#">0208000000</a>	Cross-connector (terminal), when screwed in, grey, 36 A, Number of
GTIN (EAN)	4008190069100	poles: 4, Pitch in mm (P): 27.60, Insulated: No, Width: 95.8 mm
Qty.	20 pc(s).	

## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## SchT group marker carrier



The SchT 5 S group tag carriers are clipped directly onto the TS 32 mounting rail (G-rail) or the TS 35 mounting rail (top-hat rail). It is therefore possible to label the terminal strip irrespective of the terminal and the type of terminal. SchT 5 and SchT 5 S are fitted with ESO 5, STR 5 protective strips.

The SchT 7 is a hinged group tag carrier for inlay tags which enables easy access to the clamping screw.

The SchT 7 is fitted with ESO 7, STR 7 protective strips or DEK 5.

Inlay tags and protective strips can be found under "Accessories".

## General ordering data

Type	Version
SCHT 7	
Order No. <a href="#">0517960000</a>	SCHT, Terminal marker, 39.3 x 8 mm, Pitch in mm (P): 7.00
GTIN (EAN) 4008190001742	Weidmueller, white
Qty. 20 pc(s).	

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	Version
DEK 5/6 MC NE WS	
Order No. <a href="#">1609820000</a>	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
GTIN (EAN) 4008190203436	Weidmueller, white
Qty. 1,000 pc(s).	

## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Gauge rings



Gauge rings are used to protect against the using of incorrectly selected fuse sizes. They are simply inserted into the respective fuse base and prevent the using of bigger fuses.

## General ordering data

Type	P 14/2 D01 RS SAKS4	Version
Order No.	<a href="#">0138000000</a>	Fuse gauge ring (terminal), Height: 11 mm, Depth: 10.5 mm,
GTIN (EAN)	4008190114664	Aluminium, pink
Qty.	50 pc(s).	
Type	P 14/4 D01 BR SAKS4	Version
Order No.	<a href="#">0138100000</a>	Fuse gauge ring (terminal), Height: 11 mm, Depth: 10.5 mm,
GTIN (EAN)	4008190077365	Aluminium, brown
Qty.	50 pc(s).	
Type	P 14/10 D01 RT SAKS4	Version
Order No.	<a href="#">0328700000</a>	Fuse gauge ring (terminal), Height: 11 mm, Depth: 10.5 mm,
GTIN (EAN)	4008190010294	Aluminium, red
Qty.	50 pc(s).	
Type	P 14/6 D01 GN SAKS4	Version
Order No.	<a href="#">0328600000</a>	Fuse gauge ring (terminal), Height: 11 mm, Depth: 10.5 mm,
GTIN (EAN)	4008190004248	Aluminium, green
Qty.	50 pc(s).	

## Cover profiles



Cover profiles provide protection against external impact on functional areas of the terminal blocks or in combination with our support brackets for the entire terminal strip. They provide protection against electric shock caused by accidental contact with live parts due to operation or faults.

## General ordering data

Type	ADP 2/HP2 1M	Version
Order No.	<a href="#">0485300000</a>	SAK Series, Cover profile, Transparent, 1000 mm
GTIN (EAN)	4008190051716	
Qty.	1 m	

## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/5 MC SDR	Version
Order No.	<a href="#">1609810000</a>	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00
GTIN (EAN)	4008190456597	Weidmueller, To customer specification
Qty.	200 pc(s).	

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/8 MC NE WS	Version
Order No.	<a href="#">1856740000</a>	Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00
GTIN (EAN)	4032248400850	Weidmueller, white
Qty.	800 pc(s).	

## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## E 14



Weidmueller offers NEOZED fuses in E 14 design in sizes from 2 A to 16 A.

## General ordering data

Type	E 14/6A GN	Version
Order No.	<a href="#">0328300000</a>	Active components, Cartridge fuse
GTIN (EAN)	4008190002190	
Qty.	10 pc(s).	
Type	E 14/4A BR	Version
Order No.	<a href="#">0137500000</a>	Active components, Cartridge fuse
GTIN (EAN)	4008190142629	
Qty.	10 pc(s).	
Type	E 14/16A GR	Version
Order No.	<a href="#">0328500000</a>	Active components, Cartridge fuse
GTIN (EAN)	4008190152161	
Qty.	10 pc(s).	
Type	E 14/2A RS	Version
Order No.	<a href="#">0137400000</a>	Active components, Cartridge fuse
GTIN (EAN)	4008190069094	
Qty.	10 pc(s).	
Type	E 14/10A RT	Version
Order No.	<a href="#">0328400000</a>	Active components, Cartridge fuse
GTIN (EAN)	4008190000288	
Qty.	10 pc(s).	

## Steel



Steel bus bars, together with stainless steel, have the highest strength among metallic busbars and are used in applications where short-circuit resistance plays only a secondary role.

## General ordering data

Type	ESCH 1 M	Version
Order No.	<a href="#">0280300000</a>	Busbar (terminal), silver, Height: 12 mm, Depth: 2 mm, Steel
GTIN (EAN)	4008190143053	
Qty.	10 m	

## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## End plate



## Current and voltage transformer wiring

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

## General ordering data

Type	TW SAKB/C/T	Version
Order No.	<a href="#">0242920000</a>	Partition plate (terminal), beige, Height: 75 mm, Width: 3 mm, V-2, PA
GTIN (EAN)	4008190069933	66
Qty.	20 pc(s).	

## Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snapped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

## General ordering data

Type	BZT 1 ZA WS 10/5	Version
Order No.	<a href="#">1805520000</a>	Accessories, Marker holder
GTIN (EAN)	4032248270248	
Qty.	100 pc(s).	
Type	BZT 1 WS 10/5	Version
Order No.	<a href="#">1805490000</a>	Accessories, Marker holder
GTIN (EAN)	4032248270231	
Qty.	100 pc(s).	

## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Q / SAK



Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

## General ordering data

Type	Q 10 SAK10	Version
Order No.	<a href="#">0457400000</a>	Cross-connector (terminal), when screwed in, grey, 57 A, Number of
GTIN (EAN)	4008190016166	poles: 10, Pitch in mm (P): 9.90, Insulated: No, Width: 96.1 mm
Qty.	20 pc(s).	
Type	Q 4 SAK10	Version
Order No.	<a href="#">0457300000</a>	Cross-connector (terminal), when screwed in, grey, 57 A, Number of
GTIN (EAN)	4008190129750	poles: 4, Pitch in mm (P): 9.90, Insulated: No, Width: 36.7 mm
Qty.	50 pc(s).	
Type	Q 2 SAK10	Version
Order No.	<a href="#">0457100000</a>	Cross-connector (terminal), when screwed in, grey, 57 A, Number of
GTIN (EAN)	4008190103545	poles: 2, Pitch in mm (P): 9.90, Insulated: No, Width: 16.9 mm
Qty.	50 pc(s).	
Type	Q 3 SAK10	Version
Order No.	<a href="#">0457200000</a>	Cross-connector (terminal), when screwed in, grey, 57 A, Number of
GTIN (EAN)	4008190135379	poles: 3, Pitch in mm (P): 9.90, Insulated: No, Width: 26.8 mm
Qty.	50 pc(s).	

## SAK-Series



A partition plate is used for the optical separation of circuits or used for electrical isolation from neighbouring cross-connectors. In contrast to the end plate, the contour can be larger than the adjacent terminal blocks. However, it should not be smaller, as otherwise the required clearance and creepage distances within the application can no longer be maintained.

## General ordering data

Type	TW AST1/PA HP/DBR/0.5	Version
Order No.	<a href="#">0474700000</a>	Partition plate (terminal), dark brown, Height: 65 mm, Width: 0.5 mm,
GTIN (EAN)	4008190078508	V-2
Qty.	20 pc(s).	
Type	TW DK4 HP/DBR/2	Version
Order No.	<a href="#">3833500000</a>	Partition plate (terminal), dark brown, Height: 65 mm, Width: 2 mm,
GTIN (EAN)	4008190009052	V-2, PA 66
Qty.	20 pc(s).	



## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Mounting rail support



## General ordering data

Type	SH 2	Version
Order No.	<a href="#">0494920000</a>	Busbar support, medium yellow, 130 °C, Width: 40 mm, V-0, KrG,
GTIN (EAN)	4008190007584	when screwed in
Qty.	10 pc(s).	

## Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/6 MC SDR	Version
Order No.	<a href="#">1609830000</a>	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
GTIN (EAN)	4008190456603	Weidmueller, To customer specification
Qty.	200 pc(s).	

## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## 6.3x32



For protection against overcurrent, we offer cartridge fuse with dimensions 6.3x32 mm in sizes from 500 mA to 12.5 A.

## General ordering data

Type	VH 25.4/6.3/4.3	Version
Order No.	<a href="#">0446200000</a>	Dummy fuse
GTIN (EAN)	4008190519759	
Qty.	10 pc(s).	

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/5 MC NE WS	Version
Order No.	<a href="#">1609801044</a>	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00
GTIN (EAN)	4008190397111	Weidmueller, white
Qty.	1,000 pc(s).	

## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.


- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/6.5 MC SDR	Version
Order No.	<a href="#">1609850000</a>	Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50
GTIN (EAN)	4008190456610	Weidmueller, To customer specification
Qty.	180 pc(s).	

## SAK-Series



Warning covers with a flash symbol provide more safety for man and machine. They are used where external voltage must be indicated within the application.

## General ordering data

Type	AD 4 SAK10	Version
Order No.	<a href="#">0178600000</a>	Terminal cover, yellow, PVC, Height: 39.6 mm, Width: 25 mm, Depth:
GTIN (EAN)	4008190068288	1 mm, HB
Qty.	50 pc(s).	

## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Slotted screwdriver



Slotted screwdriver with rounded blade SD DIN 5265, ISO 2380/2, output to DIN 5264, ISO 2380/1. ChromTop tip, SoftFinish grip

## General ordering data

Type	SDS 1.0X5.5X150	Version
Order No.	<a href="#">9008350000</a>	Screwdriver, Screwdriver
GTIN (EAN)	4032248056316	
Qty.	1 pc(s).	

## Brass



Brass bus bars, as a copper alloy, has positive properties in terms of electrical conductivity and at the same time has a higher strength than copper against mechanical stress.

## General ordering data

Type	SA 3.00X10.00X1000 CUZN ...	Version
Order No.	<a href="#">0259800000</a>	Busbar (terminal), silver, Height: 1000 mm, Depth: 3 mm, Brass
GTIN (EAN)	4008190049300	
Qty.	1 m	

## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Screws



Depending on the terminal block or also accessories, we offer different types of screws as additional items or also spare parts.

## General ordering data

Type	BFSC M3X22 PA/RT	Version
Order No.	<a href="#">0128900000</a>	Mounting screw (Terminal), 3.00 mm, Polyamide 66, Depth: 4.8 mm,
GTIN (EAN)	4008190084158	Width: 4.8 mm, Height: 22 mm
Qty.	100 pc(s).	
Type	BFSC M4X20	Version
Order No.	<a href="#">0362800000</a>	Mounting screw (Terminal), 4.00 mm, Steel, Depth: 7 mm, Width: 7
GTIN (EAN)	4008190114053	mm, Height: 20 mm
Qty.	100 pc(s).	
Type	BFSC M4X9T	Version
Order No.	<a href="#">0103300000</a>	Mounting screw (Terminal), 4.00 mm, Steel, Depth: 7 mm, Width: 7
GTIN (EAN)	4008190023348	mm, Height: 9 mm
Qty.	100 pc(s).	
Type	BFSC M4X30	Version
Order No.	<a href="#">0267100000</a>	Mounting screw (Terminal), 4.00 mm, Steel, Depth: 7 mm, Width: 7
GTIN (EAN)	4008190187897	mm, Height: 30 mm
Qty.	50 pc(s).	
Type	KISC M3X6 SAKS1	Version
Order No.	<a href="#">0346200000</a>	Clamping yoke, Mounting screw, Steel
GTIN (EAN)	4008190175658	
Qty.	100 pc(s).	
Type	BFSC M3X25	Version
Order No.	<a href="#">0292500000</a>	Mounting screw (Terminal), 3.00 mm, Steel, Depth: 4.8 mm, Width:
GTIN (EAN)	4008190177027	4.8 mm, Height: 25 mm
Qty.	100 pc(s).	

## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## QL mounting screws



Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

## General ordering data

Type	SS M3 D 128-A 3	Version
Order No.	<a href="#">0164400000</a>	Lock washer, Copper
GTIN (EAN)	4008190035914	
Qty.	50 pc(s).	

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/6.5 MC NE WS	Version
Order No.	<a href="#">1609840000</a>	Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50
GTIN (EAN)	4008190203429	Weidmueller, white
Qty.	900 pc(s).	

## SAKS 4/35

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## DEK 5/8



## WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

## Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

## General ordering data

Type	DEK 5/8 MM WS	Version
Order No.	<a href="#">2007130000</a>	Dekafix, Terminal marker, 5 x 8 mm, Weidmueller, white
GTIN (EAN)	4050118392012	
Qty.	500 pc(s).	