


ZT 4/4AN/2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Some applications demand for a pluggable, modular solution to be more flexible or to facilitate the installation. Where complete functional units have to be prefabricated or replaced, modular and flexible connection systems are required. Our pluggable terminal blocks can be quickly assembled and are completely factory tested.

General ordering data

| | |
|------------|--|
| Version | Z-series, Feed-through terminal, Rated cross-section: 4 mm ² , Plug-in connection, dark beige |
| Order No. | 1848350000 |
| Type | ZT 4/4AN/2 |
| GTIN (EAN) | 4032248403516 |
| Qty. | 50 pc(s). |

ZT 4/4AN/2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|--------------------------|------------|----------------|------------|
| Depth | 43 mm | Depth (inches) | 1.693 inch |
| Depth including DIN rail | 43.5 mm | Height | 100.5 mm |
| Height (inches) | 3.957 inch | Width | 6.5 mm |
| Width (inches) | 0.256 inch | Net weight | 18.06 g |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature | -25 °C...55 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 120 °C | | |

Material data

| | | | |
|---------------------------|-------|--------|------------|
| Material | Wemid | Colour | dark beige |
| UL 94 flammability rating | V-0 | | |

System specifications

| | | | |
|-------------------------------|--|-------------------------------------|-------|
| Version | 2 tension-clamp connections - 2 plug-in connections, pluggable | End cover plate required | Yes |
| Number of levels | 1 | Number of clamping points per level | 2 |
| Number of potentials per tier | 1 | Levels cross-connected internally | No |
| PE connection | No | Rail | TS 35 |

Additional technical data

| | | | |
|--------------------------|---------|------------|-------|
| Explosion-tested version | No | Open sides | right |
| Type of mounting | Snap-on | | |

CSA rating data

| | | | |
|-------------------------------|----------------|-------------------------------|--------|
| Certificate No. (CSA) | 200039-1720292 | Current size C (CSA) | 28 A |
| Voltage size C (CSA) | 600 V | Wire cross section max. (CSA) | 10 AWG |
| Wire cross section min. (CSA) | 26 AWG | | |

Conductors for clamping (additional connection)

| | | | |
|---|-------------------|--|--------------------|
| Conductor cross-section, flexible plus plastic collar DIN 46228/1, further connection, max. | 4 mm ² | Connection type, additional connection | Plug-in connection |
|---|-------------------|--|--------------------|

Conductors for clamping (rated connection)

| | | | |
|---------------------------------------|--|---------|----------------------|
| Blade size | 0.6 x 3.5 mm | | |
| Clamping range, max. | 6 mm ² | | |
| Clamping range, min. | 0.13 mm ² | | |
| Connection direction | top | | |
| Gauge to IEC 60947-1 | A3 | | |
| Number of connections | 2 | | |
| Stripping length | 12 mm | | |
| Tube length for twin wire-end ferrule | Cross-section for conductor connection | nominal | 0.5 mm ² |
| | Cross-section for conductor connection | nominal | 0.75 mm ² |

ZT 4/4AN/2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

| | | | |
|---|--|---------|----------------------|
| Tube length for wire-end ferrule with plastic collar DIN 46228/4 | Cross-section for conductor connection | nominal | 0.5 mm ² |
| | Cross-section for conductor connection | nominal | 0.75 mm ² |
| | Cross-section for conductor connection | nominal | 1 mm ² |
| | Cross-section for conductor connection | nominal | 1.5 mm ² |
| | Cross-section for conductor connection | nominal | 4 mm ² |
| Tube length for wire-end ferrule without plastic collar DIN 46228/1 | Cross-section for conductor connection | nominal | 0.5 mm ² |
| | Cross-section for conductor connection | nominal | 0.75 mm ² |
| | Cross-section for conductor connection | nominal | 1 mm ² |
| | Cross-section for conductor connection | nominal | 1.5 mm ² |
| | Cross-section for conductor connection | nominal | 4 mm ² |
| Type of connection | Plug-in connection | | |
| Wire connection cross section AWG, max. | AWG 10 | | |
| Wire connection cross section AWG, min. | AWG 26 | | |
| Wire connection cross section, finely stranded, max. | 6 mm ² | | |
| Wire connection cross section, finely stranded, min. | 0.5 mm ² | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 4 mm ² | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm ² | | |
| Wire connection cross-section, solid core, max. | 6 mm ² | | |
| Wire connection cross-section, solid core, min. | 0.5 mm ² | | |

General

| | | | |
|---|--------|---|----------------------------------|
| Rail | TS 35 | Standards | In accordance with IEC 60947-7-1 |
| Wire connection cross section AWG, max. | AWG 10 | Wire connection cross section AWG, min. | AWG 26 |

Rating data

| | | | |
|---|----------------------------------|--|--------|
| Rated cross-section | 4 mm ² | Rated voltage | 800 V |
| Max. voltage of clamp support & plug-gable system | 800 V | Rated DC voltage | 800 V |
| Rated current | 32 A | Current at maximum wires | 32 A |
| Standards | In accordance with IEC 60947-7-1 | Volume resistance according to IEC 60947-7-x | 1 mΩ |
| Rated impulse withstand voltage | 8 kV | Power loss in accordance with IEC 60947-7-x | 1.02 W |
| Pollution severity | 3 | | |

UL rating data

| | | | |
|--|--------|--|--------|
| Certificate No. (cURus) | E60693 | Conductor size Factory wiring max. (cURus) | 10 AWG |
| Conductor size Factory wiring min. (cURus) | 26 AWG | Conductor size Field wiring max. (cURus) | 10 AWG |
| Conductor size Field wiring min. (cURus) | 26 AWG | Current size C (cURus) | 28 A |
| Voltage size C (cURus) | 600 V | | |

Creation date June 5, 2024 3:51:09 PM CEST

ZT 4/4AN/2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000897 | ETIM 7.0 | EC000897 |
| ETIM 8.0 | EC000897 | ETIM 9.0 | EC000897 |
| ECLASS 9.0 | 27-14-11-20 | ECLASS 9.1 | 27-14-11-20 |
| ECLASS 10.0 | 27-14-11-20 | ECLASS 11.0 | 27-14-11-20 |
| ECLASS 12.0 | 27-14-11-20 | ECLASS 13.0 | 27-25-01-01 |

Approvals

Approvals



| | |
|-------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (cURus) | E60693 |

Downloads

| | |
|---|---|
| Approval/Certificate/Document of Conformity | Declaration of Conformity UKCA declaration of conformity Confirmation of Standards EN 45545-2_2020-10 |
| Engineering Data | CAD data – STEP |
| Engineering Data | Zuken E3.S |
| User Documentation | StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |
| Brochures | |


Data sheet

ZT 4/4AN/2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



ZT 4/4AN/2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

4 mm²

The plugs for our WeiCoS-System are available for all different connection systems. The product range includes preassembled connectors from 1 to 10 poles and the possibility of an individual assembly. This ensures maximum flexibility for every application. The customized accessories increase the safety and protection against environmental influences.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | ZP 4/1AN/4 | Version |
| Order No. | 1855010000 | Z-series, Plug-in connector, beige, Direct mounting |
| GTIN (EAN) | 4032248396085 | |
| Qty. | 25 pc(s). | |
| Type | ZP 4/1AN/2 | Version |
| Order No. | 1854990000 | Z-series, Plug-in connector, beige, Direct mounting |
| GTIN (EAN) | 4032248396061 | |
| Qty. | 25 pc(s). | |
| Type | ZP 4/1AN/1 | Version |
| Order No. | 1848340000 | Z-series, Plug-in connector, beige, Direct mounting |
| GTIN (EAN) | 4032248402908 | |
| Qty. | 50 pc(s). | |
| Type | ZP 4/1AN/3 | Version |
| Order No. | 1855000000 | Z-series, Plug-in connector, beige, Direct mounting |
| GTIN (EAN) | 4032248396078 | |
| Qty. | 25 pc(s). | |
| Type | ZP 4/1AN/10 | Version |
| Order No. | 1855070000 | Z-series, Plug-in connector, beige, Direct mounting |
| GTIN (EAN) | 4032248396146 | |
| Qty. | 10 pc(s). | |
| Type | ZP 4/1AN/13 | Version |
| Order No. | 1855100000 | Z-series, Plug-in connector, beige, Direct mounting |
| GTIN (EAN) | 4032248396177 | |
| Qty. | 10 pc(s). | |
| Type | ZP 4/1AN/14 | Version |
| Order No. | 1855110000 | Z-series, Plug-in connector, beige, Direct mounting |
| GTIN (EAN) | 4032248396184 | |
| Qty. | 10 pc(s). | |
| Type | ZP 4/1AN/12 | Version |
| Order No. | 1855090000 | Z-series, Plug-in connector, beige, Direct mounting |
| GTIN (EAN) | 4032248396160 | |
| Qty. | 10 pc(s). | |
| Type | ZP 4/1AN/8 | Version |
| Order No. | 1855050000 | Z-series, Plug-in connector, beige, Direct mounting |
| GTIN (EAN) | 4032248396122 | |
| Qty. | 20 pc(s). | |
| Type | ZP 4/1AN/11 | Version |
| Order No. | 1855080000 | Z-series, Plug-in connector, beige, Direct mounting |
| GTIN (EAN) | 4032248396153 | |
| Qty. | 20 pc(s). | |

Creation date June 5, 2024 3:51:09 PM CEST


ZT 4/4AN/2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|---|
| Type | ZP 4/1AN/7 | Version |
| Order No. | 1855040000 | Z-series, Plug-in connector, beige, Direct mounting |
| GTIN (EAN) | 4032248396115 | |
| Qty. | 20 pc(s). | |
| Type | ZP 4/1AN/9 | Version |
| Order No. | 1855060000 | Z-series, Plug-in connector, beige, Direct mounting |
| GTIN (EAN) | 4032248396139 | |
| Qty. | 10 pc(s). | |
| Type | ZP 4/1AN/1 GN | Version |
| Order No. | 1854980000 | Z-series, Plug-in connector, green, Direct mounting |
| GTIN (EAN) | 4032248396054 | |
| Qty. | 50 pc(s). | |
| Type | ZP 4/1AN/5 | Version |
| Order No. | 1855020000 | Z-series, Plug-in connector, beige, Direct mounting |
| GTIN (EAN) | 4032248396092 | |
| Qty. | 20 pc(s). | |
| Type | ZP 4/1AN/6 | Version |
| Order No. | 1855030000 | Z-series, Plug-in connector, beige, Direct mounting |
| GTIN (EAN) | 4032248396108 | |
| Qty. | 20 pc(s). | |

4 mm²

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

General ordering data

| | | |
|------------|----------------------------|------------------------------------|
| Type | ZQV 4/2 GE | Version |
| Order No. | 1608950000 | Accessories, Cross-connector, 32 A |
| GTIN (EAN) | 4008190263225 | |
| Qty. | 60 pc(s). | |

ZT 4/4AN/2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Locking elements



The plugs can be securely and easily fixed to the base terminal by using a locking element. The locking element avoids an unintentional disconnection of the plugs from the base terminal and ensures maximum safety.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | ZVR ZP4 | Version |
| Order No. | 1855250000 | Z-series, Locking clips, Direct mounting |
| GTIN (EAN) | 4032248396481 | |
| Qty. | 25 pc(s). | |

Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | DEK 5/6 MC NE WS | Version |
| Order No. | 1609820000 | Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 |
| GTIN (EAN) | 4008190203436 | Weidmueller, white |
| Qty. | 1,000 pc(s). | |

ZT 4/4AN/2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Custom printing



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.


- Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | WS 12/6.5 MC SDR | Version |
| Order No. | 1609930000 | WS, Terminal marker, 12 x 6.5 mm, Pitch in mm (P): 6.50 |
| GTIN (EAN) | 4008190456665 | Weidmueller, Allen-Bradley, To customer specification |
| Qty. | 108 pc(s). | |

Slotted screwdriver



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | SDIS SLIM 0.6X3.5X100 | Version |
| Order No. | 2749610000 | Mounting tool, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade thickness (A): 0.6 mm |
| GTIN (EAN) | 4050118896350 | |
| Qty. | 1 pc(s). | |

ZT 4/4AN/2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | WS 10/6 M MC NE WS | Version |
| Order No. | 1818400000 | WS, Terminal marker, 10 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, |
| GTIN (EAN) | 4032248310876 | Allen-Bradley, white |
| Qty. | 600 pc(s). | |
| Type | WS 10/6 MC NE WS | Version |
| Order No. | 1828450000 | WS, Terminal marker, 10 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, |
| GTIN (EAN) | 4032248350513 | Allen-Bradley, white |
| Qty. | 600 pc(s). | |

Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | DEK 5/6.5 MC SDR | Version |
| Order No. | 1609850000 | Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50 |
| GTIN (EAN) | 4008190456610 | Weidmueller, To customer specification |
| Qty. | 180 pc(s). | |

ZT 4/4AN/2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|---|
| Type | DEK 5/6.5 PLUS MC SDR | Version |
| Order No. | 1046360000 | Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50 |
| GTIN (EAN) | 4032248782062 | Weidmueller, To customer specification |
| Qty. | 180 pc(s). | |

Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | WS 12/6.5 MC NE RT | Version |
| Order No. | 1773561686 | WS, Terminal marker, 12 x 6.5 mm, Pitch in mm (P): 6.50 |
| GTIN (EAN) | 4032248142026 | Weidmueller, Allen-Bradley, red |
| Qty. | 540 pc(s). | |
| Type | WS 12/6.5 MC NE GE | Version |
| Order No. | 1773561687 | WS, Terminal marker, 12 x 6.5 mm, Pitch in mm (P): 6.50 |
| GTIN (EAN) | 4032248142033 | Weidmueller, Allen-Bradley, yellow |
| Qty. | 540 pc(s). | |
| Type | WS 12/6.5 MC NE WS | Version |
| Order No. | 1609920000 | WS, Terminal marker, 12 x 6.5 mm, Pitch in mm (P): 6.50 |
| GTIN (EAN) | 4008190203511 | Weidmueller, Allen-Bradley, white |
| Qty. | 540 pc(s). | |
| Type | WS 12/6.5 MC NE BL | Version |
| Order No. | 1773561693 | WS, Terminal marker, 12 x 6.5 mm, Pitch in mm (P): 6.50 |
| GTIN (EAN) | 4032248142095 | Weidmueller, Allen-Bradley, blue |
| Qty. | 540 pc(s). | |

ZT 4/4AN/2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.


Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | DEK 5/6.5 MC NE WS | Version |
| Order No. | 1609840000 | Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50 |
| GTIN (EAN) | 4008190203429 | Weidmueller, white |
| Qty. | 900 pc(s). | |

4 mm²

End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

General ordering data

| | | |
|------------|----------------------------|--------------------------------------|
| Type | ZAP/TW ZT4/4AN/2 | Version |
| Order No. | 1848360000 | Z-series, End plate, Partition plate |
| GTIN (EAN) | 4032248403592 | |
| Qty. | 50 pc(s). | |
| Type | ZAP/TW ZT4/2AN OR | Version |
| Order No. | 1855230000 | Z-series, End plate, Partition plate |
| GTIN (EAN) | 4032248396511 | |
| Qty. | 50 pc(s). | |


ZT 4/4AN/2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Coding elements



Through the use of coding pins, individual coding options ensure trouble-free plug-in connection.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | KOSF ZT4 | Version |
| Order No. | 1856860000 | Z-series, Coding element, Direct mounting |
| GTIN (EAN) | 4032248400744 | |
| Qty. | 50 pc(s). | |

WS 12/6.5



WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

General ordering data

| | | |
|------------|----------------------------|--|
| Type | WS 12/6.5 MM WS | Version |
| Order No. | 2619930000 | WS, Terminal marker, 12 x 6.5 mm, Weidmueller, white |
| GTIN (EAN) | 4050118626155 | |
| Qty. | 600 pc(s). | |

ZT 4/4AN/2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

DEK 5/6

**WS/ DEK**

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

General ordering data

| | | |
|------------|----------------------------|--|
| Type | DEK 5/6 MM WS | Version |
| Order No. | 2007120000 | Dekafix, Terminal marker, 5 x 6 mm, Weidmueller, white |
| GTIN (EAN) | 4050118392104 | |
| Qty. | 600 pc(s). | |

Strain reliefs

The strain relief protects the contact against mechanical stress and protects the connector against inadvertent release from the contact point.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | ZZE ZP4 | Version |
| Order No. | 1855260000 | Z-series, Strain relief, Direct mounting |
| GTIN (EAN) | 4032248396498 | |
| Qty. | 25 pc(s). | |

ZT 4/4AN/2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Marker holder




The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snapped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

General ordering data

| | | |
|------------|----------------------------|----------------------------|
| Type | BZT 1 WS 10/5 | Version |
| Order No. | 1805490000 | Accessories, Marker holder |
| GTIN (EAN) | 4032248270231 | |
| Qty. | 100 pc(s). | |
| Type | BZT 1 ZA WS 10/5 | Version |
| Order No. | 1805520000 | Accessories, Marker holder |
| GTIN (EAN) | 4032248270248 | |
| Qty. | 100 pc(s). | |

4 mm²



The plugs for our WeiCoS-System are available for all different connection systems. The product range includes preassembled connectors from 1 to 10 poles and the possibility of an individual assembly. This ensures maximum flexibility for every application. The customized accessories increase the safety and protection against environmental influences.

General ordering data

| | | |
|------------|----------------------------|-----------------------------|
| Type | WP4/ 1AN/ 1 | Version |
| Order No. | 1107790000 | W-Series, Plug-in connector |
| GTIN (EAN) | 4032248882915 | |
| Qty. | 50 pc(s). | |
| Type | WP4/ 1AN/ 10 | Version |
| Order No. | 1107800000 | W-Series, Plug-in connector |
| GTIN (EAN) | 4032248882922 | |
| Qty. | 10 pc(s). | |

ZT 4/4AN/2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Plus



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | DEK 5/6.5 PLUS MC NE GE | Version |
| Order No. | 1364020000 | Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50 |
| GTIN (EAN) | 4050118166057 | Weidmueller, yellow |
| Qty. | 900 pc(s). | |
| Type | DEK 5/6.5 PLUS MC NE WS | Version |
| Order No. | 1046340000 | Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50 |
| GTIN (EAN) | 4032248782048 | Weidmueller, white |
| Qty. | 900 pc(s). | |