

**HTN 21****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Crimping tools for non-insulated connectors**

Rolled cable lugs, tubular cable lugs, terminal pins, parallel and serial connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

**General ordering data**

Version	Pressing tool, Crimping tool for contacts, 0.5mm <sup>2</sup> , 6mm <sup>2</sup> , Indent crimp
Order No.	<a href="#">9014610000</a>
Type	HTN 21
GTIN (EAN)	4008190152734
Qty.	1 pc(s).

**HTN 21****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Width	200 mm	Width (inches)	7.874 inch
Net weight	421.6 g		

**Technical data**

Description of article	Crimping tool for non-insulated connectors, 0.5-6 mm <sup>2</sup>	Version	Mechanical, without interchangeable inserts
------------------------	---	---------	---

**Description of contact**

Conductor cross-section, max. AWG	AWG 10	Conductor cross-section, min. AWG	AWG 21
Crimping range, max.	6 mm <sup>2</sup>	Crimping range, min.	0.5 mm <sup>2</sup>
Type of contact	Uninsulated connection		

**tool data crimping**

Crimping type/profile	Indent crimp	Wire end ferrules cross-section, max.	6 mm <sup>2</sup>
Wire end ferrules cross-section, min.	0.5 mm <sup>2</sup>		

**Classifications**

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ETIM 9.0	EC000168
ECLASS 9.0	21-04-38-11	ECLASS 9.1	21-04-38-11
ECLASS 10.0	21-04-38-11	ECLASS 11.0	21-04-38-11
ECLASS 12.0	21-04-38-11	ECLASS 13.0	21-04-38-11

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

**Downloads**


Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Manual</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

## HTN 21

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



## HTN 21

Weidmüller Interface GmbH &amp; Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

25 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KRN-M5/-25	Version
Order No.	<a href="#">1495830000</a>	cable lug, terminal end, 25 mm <sup>2</sup>
GTIN (EAN)	4050118305562	
Qty.	100 pc(s).	
Type	KRN-M6/-25	Version
Order No.	<a href="#">1496490000</a>	cable lug, terminal end, 25 mm <sup>2</sup>
GTIN (EAN)	4050118305784	
Qty.	100 pc(s).	
Type	KRN-M14/-25	Version
Order No.	<a href="#">1496530000</a>	cable lug, terminal end, 25 mm <sup>2</sup>
GTIN (EAN)	4050118305883	
Qty.	100 pc(s).	
Type	KRN-M8/-25	Version
Order No.	<a href="#">1496500000</a>	cable lug, terminal end, 25 mm <sup>2</sup>
GTIN (EAN)	4050118305975	
Qty.	100 pc(s).	
Type	KRN-M10/-25	Version
Order No.	<a href="#">1496510000</a>	cable lug, terminal end, 25 mm <sup>2</sup>
GTIN (EAN)	4050118305814	
Qty.	100 pc(s).	
Type	KRN-M12/-25	Version
Order No.	<a href="#">1496520000</a>	cable lug, terminal end, 25 mm <sup>2</sup>
GTIN (EAN)	4050118306163	
Qty.	100 pc(s).	

## HTN 21

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

2.5 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	VSTN/-2,5	Version
Order No.	<a href="#">1497350000</a>	cable lug, terminal end, 2.5 mm <sup>2</sup> , 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118306859	
Qty.	100 pc(s).	

0.5 - 1 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KQN-M8/-1	Version
Order No.	<a href="#">1493810000</a>	cable lug, terminal end, 0.5 mm <sup>2</sup> - 1 mm <sup>2</sup>
GTIN (EAN)	4050118303476	
Qty.	100 pc(s).	
Type	KQN-M4/-1	Version
Order No.	<a href="#">1493770000</a>	cable lug, terminal end, 0.5 mm <sup>2</sup> - 1 mm <sup>2</sup>
GTIN (EAN)	4050118303377	
Qty.	100 pc(s).	
Type	KQN-M5/-1	Version
Order No.	<a href="#">1493790000</a>	cable lug, terminal end, 0.5 mm <sup>2</sup> - 1 mm <sup>2</sup>
GTIN (EAN)	4050118303704	
Qty.	100 pc(s).	
Type	KQN-M10/-1	Version
Order No.	<a href="#">1493710000</a>	cable lug, terminal end, 0.5 mm <sup>2</sup> - 1 mm <sup>2</sup>
GTIN (EAN)	4050118303353	
Qty.	100 pc(s).	

## HTN 21

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	KQN-M3/-1	Version
Order No.	<a href="#">1493740000</a>	cable lug, terminal end, 0.5 mm <sup>2</sup> - 1 mm <sup>2</sup>
GTIN (EAN)	4050118303568	
Qty.	100 pc(s).	
Type	KQN-M2/-1	Version
Order No.	<a href="#">1493720000</a>	cable lug, terminal end, 0.5 mm <sup>2</sup> - 1 mm <sup>2</sup>
GTIN (EAN)	4050118303612	
Qty.	100 pc(s).	
Type	KQN-M5/S/-1	Version
Order No.	<a href="#">1493780000</a>	cable lug, terminal end, 0.5 mm <sup>2</sup> - 1 mm <sup>2</sup>
GTIN (EAN)	4050118303575	
Qty.	100 pc(s).	
Type	KQN-M3,5/-1	Version
Order No.	<a href="#">1493750000</a>	cable lug, terminal end, 0.5 mm <sup>2</sup> - 1 mm <sup>2</sup>
GTIN (EAN)	4050118303469	
Qty.	100 pc(s).	
Type	KQN-M2,5/-1	Version
Order No.	<a href="#">1493730000</a>	cable lug, terminal end, 0.5 mm <sup>2</sup> - 1 mm <sup>2</sup>
GTIN (EAN)	4050118303452	
Qty.	100 pc(s).	
Type	KQN-M4/S/-1	Version
Order No.	<a href="#">1493760000</a>	cable lug, terminal end, 0.5 mm <sup>2</sup> - 1 mm <sup>2</sup>
GTIN (EAN)	4050118303384	
Qty.	100 pc(s).	
Type	KQN-M6/-1	Version
Order No.	<a href="#">1493800000</a>	cable lug, terminal end, 0.5 mm <sup>2</sup> - 1 mm <sup>2</sup>
GTIN (EAN)	4050118303735	
Qty.	100 pc(s).	

0.5 - 1 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	VPLN/0,5-1,0	Version
Order No.	<a href="#">1492860000</a>	cable lug, terminal end, 0.5 mm <sup>2</sup> - 1 mm <sup>2</sup>
GTIN (EAN)	4050118302615	
Qty.	100 pc(s).	

## HTN 21

Weidmüller Interface GmbH &amp; Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories


4 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	VSTN/-4	Version
Order No.	<a href="#">1497370000</a>	cable lug, terminal end, 4 mm <sup>2</sup> , 4 mm <sup>2</sup>
GTIN (EAN)	4050118307009	
Qty.	100 pc(s).	

1.0 - 1.5 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KRN-M3/-1,5	Version
Order No.	<a href="#">1495040000</a>	cable lug, terminal end, 1 mm <sup>2</sup> - 1.5 mm <sup>2</sup>
GTIN (EAN)	4050118304916	
Qty.	100 pc(s).	
Type	KRN-M6/-1,5	Version
Order No.	<a href="#">1495080000</a>	cable lug, terminal end, 1 mm <sup>2</sup> - 1.5 mm <sup>2</sup>
GTIN (EAN)	4050118304732	
Qty.	100 pc(s).	
Type	KRN-M4/-1,5	Version
Order No.	<a href="#">1495050000</a>	cable lug, terminal end, 1 mm <sup>2</sup> - 1.5 mm <sup>2</sup>
GTIN (EAN)	4050118304886	
Qty.	100 pc(s).	
Type	KRN-M5/-1,5	Version
Order No.	<a href="#">1495070000</a>	cable lug, terminal end, 1 mm <sup>2</sup> - 1.5 mm <sup>2</sup>
GTIN (EAN)	4050118304565	
Qty.	100 pc(s).	

## HTN 21

Weidmüller Interface GmbH &amp; Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories


0.1 - 0.5 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	VSTN/0,1-0,5	Version
Order No.	<a href="#">1492980000</a>	cable lug, terminal end, 0.1 mm <sup>2</sup> - 0.5 mm <sup>2</sup>
GTIN (EAN)	4050118302974	
Qty.	100 pc(s).	

1.5 - 2.5 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	VSTN/1,5-2,5	Version
Order No.	<a href="#">1493010000</a>	cable lug, terminal end, 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118302820	
Qty.	100 pc(s).	



## HTN 21

Weidmüller Interface GmbH &amp; Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

2.5 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KRN-M6/-2,5	Version
Order No.	<a href="#">1495110000</a>	cable lug, terminal end, 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118304596	
Qty.	100 pc(s).	
Type	KRN-M4/-2,5	Version
Order No.	<a href="#">1495090000</a>	cable lug, terminal end, 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118305029	
Qty.	100 pc(s).	
Type	KRN-M5/-2,5	Version
Order No.	<a href="#">1495100000</a>	cable lug, terminal end, 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118304879	
Qty.	100 pc(s).	
Type	KRN-M8/-2,5	Version
Order No.	<a href="#">1495120000</a>	cable lug, terminal end, 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118304824	
Qty.	100 pc(s).	

0.1 - 0.5 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	VPLN/0,1-0,5	Version
Order No.	<a href="#">1492850000</a>	cable lug, terminal end, 0.1 mm <sup>2</sup> - 0.5 mm <sup>2</sup>
GTIN (EAN)	4050118302554	
Qty.	100 pc(s).	

## HTN 21

Weidmüller Interface GmbH &amp; Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

1.0 - 1.5 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KWN-M6/-1,5 90	Version
Order No.	<a href="#">1495240000</a>	cable lug, terminal end, 1 mm <sup>2</sup> - 1.5 mm <sup>2</sup>
GTIN (EAN)	4050118304862	
Qty.	100 pc(s).	
Type	KWN-M3/-1,5 90	Version
Order No.	<a href="#">1495210000</a>	cable lug, terminal end, 1 mm <sup>2</sup> - 1.5 mm <sup>2</sup>
GTIN (EAN)	4050118304893	
Qty.	100 pc(s).	
Type	KWN-M4/-1,5 90	Version
Order No.	<a href="#">1495220000</a>	cable lug, terminal end, 1 mm <sup>2</sup> - 1.5 mm <sup>2</sup>
GTIN (EAN)	4050118304572	
Qty.	100 pc(s).	
Type	KWN-M5/-1,5 90	Version
Order No.	<a href="#">1495230000</a>	cable lug, terminal end, 1 mm <sup>2</sup> - 1.5 mm <sup>2</sup>
GTIN (EAN)	4050118304749	
Qty.	100 pc(s).	

0.5 - 1 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	VSTN/0,5-1	Version
Order No.	<a href="#">1492990000</a>	cable lug, terminal end, 0.5 mm <sup>2</sup> - 1 mm <sup>2</sup>
GTIN (EAN)	4050118303001	
Qty.	100 pc(s).	

## HTN 21

Weidmüller Interface GmbH &amp; Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

2.5 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KWN-M8/-2,5 90	Version
Order No.	<a href="#">1495290000</a>	cable lug, terminal end, 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118304923	
Qty.	100 pc(s).	
Type	KWN-M6/-2,5 90	Version
Order No.	<a href="#">1495280000</a>	cable lug, terminal end, 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118305111	
Qty.	100 pc(s).	
Type	KWN-M4/-2,5 90	Version
Order No.	<a href="#">1495250000</a>	cable lug, terminal end, 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118304725	
Qty.	100 pc(s).	
Type	KWN-M5/-2,5 90	Version
Order No.	<a href="#">1495270000</a>	cable lug, terminal end, 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118304954	
Qty.	100 pc(s).	

4 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KRN-M4/-4	Version
Order No.	<a href="#">1495130000</a>	cable lug, terminal end, 4 mm <sup>2</sup>
GTIN (EAN)	4050118304831	
Qty.	100 pc(s).	

## HTN 21

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	KRN-M6/-4	Version
Order No.	<a href="#">1495150000</a>	cable lug, terminal end, 4 mm <sup>2</sup>
GTIN (EAN)	4050118305067	
Qty.	100 pc(s).	
Type	KRN-M5/-4	Version
Order No.	<a href="#">1495140000</a>	cable lug, terminal end, 4 mm <sup>2</sup>
GTIN (EAN)	4050118305043	
Qty.	100 pc(s).	
Type	KRN-M8/-4	Version
Order No.	<a href="#">1495170000</a>	cable lug, terminal end, 4 mm <sup>2</sup>
GTIN (EAN)	4050118304855	
Qty.	100 pc(s).	

4 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KWN-M4/-4 90	Version
Order No.	<a href="#">1495300000</a>	cable lug, terminal end, 4 mm <sup>2</sup>
GTIN (EAN)	4050118305081	
Qty.	100 pc(s).	
Type	KWN-M5/-4 90	Version
Order No.	<a href="#">1495310000</a>	cable lug, terminal end, 4 mm <sup>2</sup>
GTIN (EAN)	4050118304794	
Qty.	100 pc(s).	
Type	KWN-M8/-4 90	Version
Order No.	<a href="#">1495330000</a>	cable lug, terminal end, 4 mm <sup>2</sup>
GTIN (EAN)	4050118305128	
Qty.	100 pc(s).	
Type	KWN-M6/-4 90	Version
Order No.	<a href="#">1495320000</a>	cable lug, terminal end, 4 mm <sup>2</sup>
GTIN (EAN)	4050118304763	
Qty.	100 pc(s).	

## HTN 21

Weidmüller Interface GmbH &amp; Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

4 - 6 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	VPLN/4-6,0	Version
Order No.	<a href="#">1492880000</a>	cable lug, terminal end, 4 mm <sup>2</sup> - 6 mm <sup>2</sup>
GTIN (EAN)	4050118302721	
Qty.	100 pc(s).	

0.1 - 0.5 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KQN-M3/-0,5	Version
Order No.	<a href="#">1493680000</a>	cable lug, terminal end, 0.1 mm <sup>2</sup> - 0.5 mm <sup>2</sup>
GTIN (EAN)	4050118303445	
Qty.	100 pc(s).	
Type	KQN-M4/-0,5	Version
Order No.	<a href="#">1493690000</a>	cable lug, terminal end, 0.1 mm <sup>2</sup> - 0.5 mm <sup>2</sup>
GTIN (EAN)	4050118303346	
Qty.	100 pc(s).	
Type	KQN-M5/-0,5	Version
Order No.	<a href="#">1493700000</a>	cable lug, terminal end, 0.1 mm <sup>2</sup> - 0.5 mm <sup>2</sup>
GTIN (EAN)	4050118303582	
Qty.	100 pc(s).	
Type	KQN-M2/-0,5	Version
Order No.	<a href="#">1493670000</a>	cable lug, terminal end, 0.1 mm <sup>2</sup> - 0.5 mm <sup>2</sup>
GTIN (EAN)	4050118303438	
Qty.	100 pc(s).	

## HTN 21

Weidmüller Interface GmbH &amp; Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

1.5 -2.5 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KQN-M8/-2,5	Version
Order No.	<a href="#">1493910000</a>	cable lug, terminal end, 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118303766	
Qty.	100 pc(s).	
Type	KQN-M10/-2,5	Version
Order No.	<a href="#">1493930000</a>	cable lug, terminal end, 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118303841	
Qty.	100 pc(s).	
Type	KQN-M5/S/-2,5	Version
Order No.	<a href="#">1493870000</a>	cable lug, terminal end, 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118303759	
Qty.	100 pc(s).	
Type	KQN-M12/-2,5	Version
Order No.	<a href="#">1493940000</a>	cable lug, terminal end, 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118303834	
Qty.	100 pc(s).	
Type	KQN-M3,5/-2,5	Version
Order No.	<a href="#">1493830000</a>	cable lug, terminal end, 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118303599	
Qty.	100 pc(s).	
Type	KQN-M4/S/-2,5	Version
Order No.	<a href="#">1493840000</a>	cable lug, terminal end, 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118303391	
Qty.	100 pc(s).	
Type	KQN-M4/-2,5	Version
Order No.	<a href="#">1493850000</a>	cable lug, terminal end, 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118303643	
Qty.	100 pc(s).	
Type	KQN-M6/-2,5	Version
Order No.	<a href="#">1493900000</a>	cable lug, terminal end, 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118303698	
Qty.	100 pc(s).	
Type	KQN-M3/-2,5	Version
Order No.	<a href="#">1493820000</a>	cable lug, terminal end, 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118303360	
Qty.	100 pc(s).	

## HTN 21

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	KQN-M5/-2,5	Version
Order No.	<a href="#">1493890000</a>	cable lug, terminal end, 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118303605	
Qty.	100 pc(s).	

4 - 6 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	VSTN/4-6	Version
Order No.	<a href="#">1493020000</a>	cable lug, terminal end, 4 mm <sup>2</sup> - 6 mm <sup>2</sup>
GTIN (EAN)	4050118302950	
Qty.	100 pc(s).	

4 - 6 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KQNG-M5/-6	Version
Order No.	<a href="#">1492650000</a>	cable lug, terminal end, 4 mm <sup>2</sup> , 6 mm <sup>2</sup>
GTIN (EAN)	4050118302462	
Qty.	100 pc(s).	
Type	KQNG-M6/-6	Version
Order No.	<a href="#">1492660000</a>	cable lug, terminal end, 4 mm <sup>2</sup> , 6 mm <sup>2</sup>
GTIN (EAN)	4050118302547	
Qty.	100 pc(s).	
Type	KQNG-M4/-6	Version
Order No.	<a href="#">1493660000</a>	cable lug, terminal end, 4 mm <sup>2</sup> , 6 mm <sup>2</sup>
GTIN (EAN)	4050118303339	
Qty.	100 pc(s).	

## HTN 21

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	KQNG-M8/-6	Version
Order No.	<a href="#">1492670000</a>	cable lug, terminal end, 4 mm <sup>2</sup> , 6 mm <sup>2</sup>
GTIN (EAN)	4050118302608	
Qty.	100 pc(s).	


4 - 6 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KSN/-6,0	Version
Order No.	<a href="#">1492770000</a>	cable lug, terminal end, 4 mm <sup>2</sup> - 6 mm <sup>2</sup>
GTIN (EAN)	4050118302530	
Qty.	100 pc(s).	

0.5 - 0.75 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	VSTN-M0,5/-0,75	Version
Order No.	<a href="#">1497330000</a>	cable lug, terminal end, 0.5 mm <sup>2</sup> - 0.75 mm <sup>2</sup>
GTIN (EAN)	4050118306637	
Qty.	100 pc(s).	



## HTN 21

Weidmüller Interface GmbH &amp; Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

16 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KRN-M12/-16	Version
Order No.	<a href="#">1497010000</a>	cable lug, terminal end, 16 mm <sup>2</sup>
GTIN (EAN)	4050118306538	
Qty.	100 pc(s).	
Type	KRN-M8/-16	Version
Order No.	<a href="#">1496990000</a>	cable lug, terminal end, 16 mm <sup>2</sup>
GTIN (EAN)	4050118306514	
Qty.	100 pc(s).	
Type	KRN-M5/-16	Version
Order No.	<a href="#">1496970000</a>	cable lug, terminal end, 16 mm <sup>2</sup>
GTIN (EAN)	4050118306569	
Qty.	100 pc(s).	
Type	KRN-M6/-16	Version
Order No.	<a href="#">1496980000</a>	cable lug, terminal end, 16 mm <sup>2</sup>
GTIN (EAN)	4050118306583	
Qty.	100 pc(s).	
Type	KRN-M10/-16	Version
Order No.	<a href="#">1497000000</a>	cable lug, terminal end, 16 mm <sup>2</sup>
GTIN (EAN)	4050118306460	
Qty.	100 pc(s).	

## HTN 21

Weidmüller Interface GmbH &amp; Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

4 - 6 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KQN-M12/-6	Version
Order No.	<a href="#">1494000000</a>	cable lug, terminal end, 4 mm <sup>2</sup> - 6 mm <sup>2</sup>
GTIN (EAN)	4050118303490	
Qty.	100 pc(s).	
Type	KQN-M4/-6	Version
Order No.	<a href="#">1493950000</a>	cable lug, terminal end, 4 mm <sup>2</sup> - 6 mm <sup>2</sup>
GTIN (EAN)	4050118303919	
Qty.	100 pc(s).	
Type	KQN-M8/-6	Version
Order No.	<a href="#">1493980000</a>	cable lug, terminal end, 4 mm <sup>2</sup> - 6 mm <sup>2</sup>
GTIN (EAN)	4050118303674	
Qty.	100 pc(s).	
Type	KQN-M10/-6	Version
Order No.	<a href="#">1493990000</a>	cable lug, terminal end, 4 mm <sup>2</sup> - 6 mm <sup>2</sup>
GTIN (EAN)	4050118303797	
Qty.	100 pc(s).	
Type	KQN-M6/-6	Version
Order No.	<a href="#">1493970000</a>	cable lug, terminal end, 4 mm <sup>2</sup> - 6 mm <sup>2</sup>
GTIN (EAN)	4050118303667	
Qty.	100 pc(s).	
Type	KQN-M5/-6	Version
Order No.	<a href="#">1493960000</a>	cable lug, terminal end, 4 mm <sup>2</sup> - 6 mm <sup>2</sup>
GTIN (EAN)	4050118303629	
Qty.	100 pc(s).	

## HTN 21

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories


0.5 - 0.75 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KWN-M4/-0,75 90	Version
Order No.	<a href="#">1495190000</a>	cable lug, terminal end, 0.5 mm <sup>2</sup> - 0.75 mm <sup>2</sup>
GTIN (EAN)	4050118304909	
Qty.	100 pc(s).	
Type	KWN-M5/-0,75 90	Version
Order No.	<a href="#">1495200000</a>	cable lug, terminal end, 0.5 mm <sup>2</sup> - 0.75 mm <sup>2</sup>
GTIN (EAN)	4050118304930	
Qty.	100 pc(s).	
Type	KWN-M3/-0,75 90	Version
Order No.	<a href="#">1495180000</a>	cable lug, terminal end, 0.5 mm <sup>2</sup> - 0.75 mm <sup>2</sup>
GTIN (EAN)	4050118304787	
Qty.	100 pc(s).	

0.1 - 0.5 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KSN/0,1-0,5	Version
Order No.	<a href="#">1492720000</a>	cable lug, terminal end, 0.1 mm <sup>2</sup> - 0.5 mm <sup>2</sup>
GTIN (EAN)	4050118302653	
Qty.	100 pc(s).	

## HTN 21

Weidmüller Interface GmbH &amp; Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

1.5 - 2.5 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KQNG-M4/-2,5	Version
Order No.	<a href="#">1493630000</a>	cable lug, terminal end, 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118303292	
Qty.	100 pc(s).	
Type	KQNG-M3,5/-2,5	Version
Order No.	<a href="#">1493610000</a>	cable lug, terminal end, 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118303537	
Qty.	100 pc(s).	
Type	KQNG-M3/-2,5	Version
Order No.	<a href="#">1493600000</a>	cable lug, terminal end, 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118303278	
Qty.	100 pc(s).	
Type	KQNG-M6/-2,5	Version
Order No.	<a href="#">1493650000</a>	cable lug, terminal end, 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118303421	
Qty.	100 pc(s).	
Type	KQNG-M4/S/-2,5	Version
Order No.	<a href="#">1493620000</a>	cable lug, terminal end, 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118303247	
Qty.	100 pc(s).	
Type	KQNG-M5/-2,5	Version
Order No.	<a href="#">1493640000</a>	cable lug, terminal end, 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118303193	
Qty.	100 pc(s).	

## HTN 21

Weidmüller Interface GmbH &amp; Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

0.5 - 1 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KSN/0,5-1,0	Version
Order No.	<a href="#">1492730000</a>	cable lug, terminal end, 0.5 mm <sup>2</sup> - 1 mm <sup>2</sup>
GTIN (EAN)	4050118302486	
Qty.	100 pc(s).	

6 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KWN-M6/-6 90	Version
Order No.	<a href="#">1496130000</a>	cable lug, terminal end, 6 mm <sup>2</sup>
GTIN (EAN)	4050118305982	
Qty.	100 pc(s).	
Type	KWN-M8/-6 90	Version
Order No.	<a href="#">1496140000</a>	cable lug, terminal end, 6 mm <sup>2</sup>
GTIN (EAN)	4050118306248	
Qty.	100 pc(s).	
Type	KWN-M4/-6 90	Version
Order No.	<a href="#">1497220000</a>	cable lug, terminal end, 6 mm <sup>2</sup>
GTIN (EAN)	4050118306477	
Qty.	100 pc(s).	
Type	KWN-M12/-6 90	Version
Order No.	<a href="#">1496170000</a>	cable lug, terminal end, 6 mm <sup>2</sup>
GTIN (EAN)	4050118305869	
Qty.	100 pc(s).	

## HTN 21

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	KWN-M5/-6 90	Version
Order No.	<a href="#">1496120000</a>	cable lug, terminal end, 6 mm <sup>2</sup>
GTIN (EAN)	4050118305753	
Qty.	100 pc(s).	
Type	KWN-M10/-6 90	Version
Order No.	<a href="#">1496150000</a>	cable lug, terminal end, 6 mm <sup>2</sup>
GTIN (EAN)	4050118305579	
Qty.	100 pc(s).	

1.0 - 1.5 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	VSTN-M1/-1,5	Version
Order No.	<a href="#">1497340000</a>	cable lug, terminal end, 1 mm <sup>2</sup> - 1.5 mm <sup>2</sup>
GTIN (EAN)	4050118306910	
Qty.	100 pc(s).	

10 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KRN-M12/-10	Version
Order No.	<a href="#">1496950000</a>	cable lug, terminal end, 10 mm <sup>2</sup>
GTIN (EAN)	4050118306453	
Qty.	100 pc(s).	
Type	KRN-M4/-10	Version
Order No.	<a href="#">1496900000</a>	cable lug, terminal end, 10 mm <sup>2</sup>
GTIN (EAN)	4050118306293	
Qty.	100 pc(s).	

## HTN 21

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	KRN-M6/-10	Version
Order No.	<a href="#">1496920000</a>	cable lug, terminal end, 10 mm <sup>2</sup>
GTIN (EAN)	4050118306439	
Qty.	100 pc(s).	
Type	KRN-M10/-10	Version
Order No.	<a href="#">1496940000</a>	cable lug, terminal end, 10 mm <sup>2</sup>
GTIN (EAN)	4050118306521	
Qty.	100 pc(s).	
Type	KRN-M5/-10	Version
Order No.	<a href="#">1496910000</a>	cable lug, terminal end, 10 mm <sup>2</sup>
GTIN (EAN)	4050118306378	
Qty.	100 pc(s).	
Type	KRN-M8/-10	Version
Order No.	<a href="#">1496930000</a>	cable lug, terminal end, 10 mm <sup>2</sup>
GTIN (EAN)	4050118306552	
Qty.	100 pc(s).	

1.5 -2.5 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	VPLN/1,5-2,5	Version
Order No.	<a href="#">1492870000</a>	cable lug, terminal end, 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118302578	
Qty.	100 pc(s).	

## HTN 21

Weidmüller Interface GmbH &amp; Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

6 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KRN-M5/-6	Version
Order No.	<a href="#">1497170000</a>	cable lug, terminal end, 6 mm <sup>2</sup>
GTIN (EAN)	4050118306590	
Qty.	100 pc(s).	
Type	KRN-M4/-6	Version
Order No.	<a href="#">1497150000</a>	cable lug, terminal end, 6 mm <sup>2</sup>
GTIN (EAN)	4050118306767	
Qty.	100 pc(s).	
Type	KRN-M10/-6	Version
Order No.	<a href="#">1497200000</a>	cable lug, terminal end, 6 mm <sup>2</sup>
GTIN (EAN)	4050118306385	
Qty.	100 pc(s).	
Type	KRN-M12/-6	Version
Order No.	<a href="#">1497210000</a>	cable lug, terminal end, 6 mm <sup>2</sup>
GTIN (EAN)	4050118306347	
Qty.	100 pc(s).	
Type	KRN-M8/-6	Version
Order No.	<a href="#">1497190000</a>	cable lug, terminal end, 6 mm <sup>2</sup>
GTIN (EAN)	4050118306613	
Qty.	100 pc(s).	
Type	KRN-M6/-6	Version
Order No.	<a href="#">1497180000</a>	cable lug, terminal end, 6 mm <sup>2</sup>
GTIN (EAN)	4050118306729	
Qty.	100 pc(s).	



## HTN 21

Weidmüller Interface GmbH &amp; Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

6 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	VSTN/-6	Version
Order No.	<a href="#">1494720000</a>	cable lug, terminal end, 6 mm <sup>2</sup> , 6 mm <sup>2</sup>
GTIN (EAN)	4050118304190	
Qty.	100 pc(s).	

0.5 - 1 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KQNG-M5/-1	Version
Order No.	<a href="#">1493580000</a>	cable lug, terminal end, 0.5 mm <sup>2</sup> - 1 mm <sup>2</sup>
GTIN (EAN)	4050118303315	
Qty.	100 pc(s).	
Type	KQNG-M4/S/-1	Version
Order No.	<a href="#">1493560000</a>	cable lug, terminal end, 0.5 mm <sup>2</sup> - 1 mm <sup>2</sup>
GTIN (EAN)	4050118303285	
Qty.	100 pc(s).	
Type	KQNG-M6/-1	Version
Order No.	<a href="#">1493590000</a>	cable lug, terminal end, 0.5 mm <sup>2</sup> - 1 mm <sup>2</sup>
GTIN (EAN)	4050118303506	
Qty.	100 pc(s).	
Type	KQNG-M4/-1	Version
Order No.	<a href="#">1493570000</a>	cable lug, terminal end, 0.5 mm <sup>2</sup> - 1 mm <sup>2</sup>
GTIN (EAN)	4050118303254	
Qty.	100 pc(s).	

## HTN 21

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	KQNG-M3/-1	Version
Order No.	<a href="#">1493540000</a>	cable lug, terminal end, 0.5 mm <sup>2</sup> - 1 mm <sup>2</sup>
GTIN (EAN)	4050118303223	
Qty.	100 pc(s).	
Type	KQNG-M3,5/-1	Version
Order No.	<a href="#">1493550000</a>	cable lug, terminal end, 0.5 mm <sup>2</sup> - 1 mm <sup>2</sup>
GTIN (EAN)	4050118303155	
Qty.	100 pc(s).	

1.5 - 2.5 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KSN/1,5-2,5	Version
Order No.	<a href="#">1492740000</a>	cable lug, terminal end, 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118302660	
Qty.	100 pc(s).	
Type	KSN/-2,5	Version
Order No.	<a href="#">1492750000</a>	cable lug, terminal end, 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup>
GTIN (EAN)	4050118302707	
Qty.	100 pc(s).	

0.5 - 0.75 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KRN-M4/-0,75	Version
Order No.	<a href="#">1495020000</a>	cable lug, terminal end, 0.5 mm <sup>2</sup> - 0.75 mm <sup>2</sup>
GTIN (EAN)	4050118304817	
Qty.	100 pc(s).	

**HTN 21****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories**

Type	KRN-M5/-0,75	Version
Order No.	<a href="#">1495030000</a>	cable lug, terminal end, 0.5 mm <sup>2</sup> - 0.75 mm <sup>2</sup>
GTIN (EAN)	4050118304848	
Qty.	100 pc(s).	
Type	KRN-M3/-0,75	Version
Order No.	<a href="#">1495010000</a>	cable lug, terminal end, 0.5 mm <sup>2</sup> - 0.75 mm <sup>2</sup>
GTIN (EAN)	4050118304800	
Qty.	100 pc(s).	