


**DK 4/35 LD GR 24VDC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Why not integrating simple electrical functions into a feed through terminal. It has the same slim design of our feed-through terminal blocks - with additional functions such as cross-connections that can be used. Often, you only need a small component to integrate an external device into your automation technology. Our modular terminal blocks with electronic components make this possible; quickly, simply, and with a perfect fit.

**General ordering data**

|            |  |
|------------|--|
| Version    | Multi-tier modular terminal, Screw connection, 4 mm <sup>2</sup> , 24 V, Number of levels: 2, beige / yellow |
| Order No.  | <a href="#">0210060000</a>   |
| Type       | DK 4/35 LD GR 24VDC  |
| GTIN (EAN) | 4008190157920  |
| Qty.       | 25 pc(s).  |

**DK 4/35 LD GR 24VDC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 52.5 mm | Depth (inches)  | 2.067 inch |
| Height     | 50 mm   | Height (inches) | 1.969 inch |
| Width      | 6 mm    | Width (inches)  | 0.236 inch |
| Net weight | 12 g    |                 |            |

**Temperatures**

|                                  |                |                                  |        |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature              | -25 °C...55 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 100 °C         |                                  |        |

**Material data**

|                           |       |        |                |
|---------------------------|-------|--------|----------------|
| Material                  | PA 66 | Colour | beige / yellow |
| UL 94 flammability rating | V-2   |        |                |

**System specifications**

|                                     |   |                               |     |
|-------------------------------------|---|-------------------------------|-----|
| Version                             | Screw connection, with LED, One end without connector | End cover plate required      | Yes |
| Number of potentials                | 1   | Number of levels              | 2   |
| Number of clamping points per level | 2   | Number of potentials per tier | 1   |
| Levels cross-connected internally   | Yes   | PE connection                 | No  |
| Rail                                | TS 35   | N-function                    | No  |
| PE function                         | No  | PEN function                  | No  |

**Additional technical data**

|                             |         |                     |                 |
|-----------------------------|---------|---------------------|-----------------|
| Explosion-tested version    | No      | Installation advice | Direct mounting |
| Number of similar terminals | 1       | Open sides          | right           |
| Type of mounting            | Snap-on |                     |                 |

**Conductors for clamping (additional connection)**

|  |                           |
|--|---------------------------|
| Connection type, additional connection | Screw / solder connection |
|--|---------------------------|

## DK 4/35 LD GR 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Conductors for clamping (rated connection)

|   |                     |   |                     |
|---|---------------------|---|---------------------|
| Blade size  | 0.6 x 3.5 mm        | Clamping range, max.  | 4 mm <sup>2</sup>   |
| Clamping range, min.  | 0.5 mm <sup>2</sup> | Clamping screw  | M 3                 |
| Connection cross-section, stranded, max.  | 4 mm <sup>2</sup>   | Connection cross-section, stranded, min.  | 0.5 mm <sup>2</sup> |
| Connection direction  | on side             | Gauge to IEC 60947-1  | A3                  |
| Number of connections   | 4                   | Stripping length  | 9 mm                |
| Tightening torque, max.   | 1 Nm                | Tightening torque, min.   | 0.5 Nm              |
| Torque level with DMS electric screwdriver  | 2                   | Type of connection  | Screw connection    |
| Type of connection 2  | Screw connection    | Wire connection cross section AWG, max.   | AWG 12              |
| Wire connection cross section AWG, min.   | AWG 22              | Wire connection cross section, finely stranded, max.                                    | 4 mm <sup>2</sup>   |
| Wire connection cross section, finely stranded, min.                                    | 0.5 mm <sup>2</sup> | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 4 mm <sup>2</sup>   |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm <sup>2</sup> | Wire connection cross-section, solid core, max.   | 4 mm <sup>2</sup>   |
| Wire connection cross-section, solid core, min.   | 0.5 mm <sup>2</sup> |   |                     |

## Dimensions

|              |       |
|--------------|-------|
| TS 35 offset | 25 mm |
|--------------|-------|

## Display element

|                                     |      |                                     |      |
|-------------------------------------|------|-------------------------------------|------|
| Current                             | 5 mA | Indicator element                   | red  |
| Operating voltage for display, max. | 24 V | Operating voltage for display, min. | 24 V |
| Type of voltage for indicator       | DC   |                                     |      |

## General

|   |                 |   |        |
|---|-----------------|---|--------|
| Installation advice                     | Direct mounting | Rail                                    | TS 35  |
| Standards                               | IEC 60947-7-1   | Wire connection cross section AWG, max. | AWG 12 |
| Wire connection cross section AWG, min. | AWG 22          |   |        |

## Rating data

|                                 |                   |  |        |
|---------------------------------|-------------------|--|--------|
| Rated cross-section             | 4 mm <sup>2</sup> | Rated voltage                                | 24 V   |
| Rated DC voltage                | 24 V              | Current at maximum wires                     | 10 A   |
| Standards                       | IEC 60947-7-1     | Volume resistance according to IEC 60947-7-x | 1 mΩ   |
| Rated impulse withstand voltage | 1 kV              | Power loss in accordance with IEC 60947-7-x  | 1.02 W |
| Pollution severity              | 3                 |  |        |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000897    | ETIM 7.0    | EC000897    |
| ETIM 8.0    | EC000897    | ETIM 9.0    | EC000897    |
| ECLASS 9.0  | 27-14-11-20 | ECLASS 9.1  | 27-14-11-20 |
| ECLASS 10.0 | 27-14-11-20 | ECLASS 11.0 | 27-14-11-20 |
| ECLASS 12.0 | 27-14-11-20 | ECLASS 13.0 | 27-25-01-02 |

Creation date May 2, 2024 4:49:31 AM CEST

**DK 4/35 LD GR 24VDC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Environmental Product Compliance**

|            |                                      |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1                       |
| SCIP       | c6099607-b1cd-4fc8-8f5b-8c2defa73093 |

**Approvals**

Approvals



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|   |   |
|---|---|
| Approval/Certificate/Document of Conformity | <a href="#">Declaration of Conformity</a><br><a href="#">UKCA declaration of conformity</a> |
| User Documentation                          | <a href="#">StorageConditionsTerminalBlocks</a>   |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>  |

## DK 4/35 LD GR 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## QB RA



Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | QB 3 WI RA6 IS             | Version  |
| Order No.  | <a href="#">0482800000</a> | Cross-connector (terminal), when screwed in, Number of poles: 3, |
| GTIN (EAN) | 4008190145217              | Pitch in mm (P): 6.00, Insulated: Yes, 27 A, grey                |
| Qty.       | 50 pc(s).                  |  |
| Type       | QB 4 WI RA6 IS             | Version  |
| Order No.  | <a href="#">0482900000</a> | Cross-connector (terminal), when screwed in, Number of poles: 4, |
| GTIN (EAN) | 4008190086169              | Pitch in mm (P): 6.00, Insulated: Yes, 27 A, grey                |
| Qty.       | 50 pc(s).                  |  |
| Type       | QB 2 WI RA6 IS             | Version  |
| Order No.  | <a href="#">0482700000</a> | Cross-connector (terminal), when screwed in, Number of poles: 2, |
| GTIN (EAN) | 4008190166021              | Pitch in mm (P): 6.00, Insulated: Yes, 27 A, grey                |
| Qty.       | 50 pc(s).                  |  |

## Test plugs



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

## General ordering data

|            |                            |                                |
|------------|----------------------------|--------------------------------|
| Type       | PS 2.3 RT                  | Version                        |
| Order No.  | <a href="#">0180400000</a> | Test adapter (terminal), 20 mA |
| GTIN (EAN) | 4008190060121              |                                |
| Qty.       | 20 pc(s).                  |                                |

## DK 4/35 LD GR 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | DEK 5/6 MC SDR             | Version   |
| Order No.  | <a href="#">1609830000</a> | Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 |
| GTIN (EAN) | 4008190456603              | Weidmueller, To customer specification                    |
| Qty.       | 200 pc(s).                 |   |
| Type       | DEK 5/6 PLUS MC SDR        | Version   |
| Order No.  | <a href="#">1038650000</a> | Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 |
| GTIN (EAN) | 4032248767908              | Weidmueller, To customer specification                    |
| Qty.       | 200 pc(s).                 |   |

## Screws



Depending on the terminal block or also accessories, we offer different types of screws as additional items or also spare parts.

## General ordering data

|            |                            |                                      |
|------------|----------------------------|--------------------------------------|
| Type       | KISC M3X15/6 SAK2.5        | Version                              |
| Order No.  | <a href="#">0359000000</a> | Clamping yoke, Mounting screw, Steel |
| GTIN (EAN) | 4008190061548              |                                      |
| Qty.       | 100 pc(s).                 |                                      |
| Type       | BFSC M2.5X14 SAKD2.5N      | Version                              |
| Order No.  | <a href="#">0266800000</a> | Mounting screw (Terminal)            |
| GTIN (EAN) | 4008190084899              |                                      |
| Qty.       | 100 pc(s).                 |                                      |

**DK 4/35 LD GR 24VDC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****W-Series**

W  
Series

A partition plate is used for the optical separation of circuits or used for electrical isolation from neighbouring cross-connectors. In contrast to the end plate, the contour can be larger than the adjacent terminal blocks. However, it should not be smaller, as otherwise the required clearance and creepage distances within the application can no longer be maintained.

**General ordering data**

|            |                            |   |
|------------|----------------------------|---|
| Type       | WTW EN                     | Version   |
| Order No.  | <a href="#">1058800000</a> | Partition plate (terminal), Intermediate plate, 86 mm x 62 mm, dark |
| GTIN (EAN) | 4008190140175              | beige   |
| Qty.       | 20 pc(s).                  |   |

**SAK-Series**

SAK  
Series

Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

**General ordering data**

|            |                            |   |
|------------|----------------------------|---|
| Type       | EW 35                      | Version   |
| Order No.  | <a href="#">0383560000</a> | End bracket, Wemid, beige, Rail: TS 35, when screwed in |
| GTIN (EAN) | 4008190181314              |   |
| Qty.       | 50 pc(s).                  |   |

**DK 4/35 LD GR 24VDC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****QB**

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

|            |                            |   |
|------------|----------------------------|---|
| Type       | QB 75/6.2/15               | Version   |
| Order No.  | <a href="#">0535200000</a> | Cross-connector (terminal), when screwed in, Number of poles: 75, |
| GTIN (EAN) | 4008190179168              | Pitch in mm (P): 6.00, Insulated: No, 27 A, grey                  |
| Qty.       | 10 pc(s).                  |   |
| Type       | QB 75/6.2/9/WI             | Version   |
| Order No.  | <a href="#">0526400000</a> | Cross-connector (terminal), when screwed in, Number of poles: 75, |
| GTIN (EAN) | 4008190099923              | Pitch in mm (P): 6.00, Insulated: No, 27 A, grey                  |
| Qty.       | 10 pc(s).                  |   |

**Connection sleeves****General ordering data**

|            |                            |  |
|------------|----------------------------|--|
| Type       | VL 2 AKZ4/DK4              | Version  |
| Order No.  | <a href="#">0446700000</a> | Cross-connector (terminal), when screwed in, Number of poles: 2, |
| GTIN (EAN) | 4008190055486              | Pitch in mm (P): 6.00, Insulated: No, 32 A, grey                 |
| Qty.       | 50 pc(s).                  |  |



## DK 4/35 LD GR 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## DEK 5/6



## WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

## Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | DEK 5/6 MM WS              | Version  |
| Order No.  | <a href="#">2007120000</a> | Dekafix, Terminal marker, 5 x 6 mm, Weidmueller, white |
| GTIN (EAN) | 4050118392104              |  |
| Qty.       | 600 pc(s).                 |  |

## Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snapped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

## General ordering data

|            |                            |                            |
|------------|----------------------------|----------------------------|
| Type       | BZT 1 ZA WS 10/5           | Version                    |
| Order No.  | <a href="#">1805520000</a> | Accessories, Marker holder |
| GTIN (EAN) | 4032248270248              |                            |
| Qty.       | 100 pc(s).                 |                            |
| Type       | BZT 1 WS 10/5              | Version                    |
| Order No.  | <a href="#">1805490000</a> | Accessories, Marker holder |
| GTIN (EAN) | 4032248270231              |                            |
| Qty.       | 100 pc(s).                 |                            |

## DK 4/35 LD GR 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Plus



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.


- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | DEK 5/6 PLUS MC NE WS      | Version   |
| Order No.  | <a href="#">1011320000</a> | Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 |
| GTIN (EAN) | 4032248717644              | Weidmueller, white  |
| Qty.       | 1,000 pc(s).               |   |

## SAK-Series



A partition plate is used for the optical separation of circuits or used for electrical isolation from neighbouring cross-connectors. In contrast to the end plate, the contour can be larger than the adjacent terminal blocks. However, it should not be smaller, as otherwise the required clearance and creepage distances within the application can no longer be maintained.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | TSCH 4 AKZ4                | Version   |
| Order No.  | <a href="#">0363360000</a> | Small partition (terminal), PA 66, beige, Continuous operating temp., |
| GTIN (EAN) | 4008190136680              | max.: 100 °C  |
| Qty.       | 100 pc(s).                 |   |

## DK 4/35 LD GR 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Q / AKZ



Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | Q 3 AKZ4                   | Version   |
| Order No.  | <a href="#">0336500000</a> | Cross-connector (terminal), when screwed in, Number of poles: 3,  |
| GTIN (EAN) | 4008190121730              | Pitch in mm (P): 6.10, Insulated: No, 24 A, grey                  |
| Qty.       | 50 pc(s).                  |   |
| Type       | Q 2 AKZ4                   | Version   |
| Order No.  | <a href="#">0336400000</a> | Cross-connector (terminal), when screwed in, Number of poles: 2,  |
| GTIN (EAN) | 4008190037680              | Pitch in mm (P): 6.10, Insulated: No, 24 A, grey                  |
| Qty.       | 50 pc(s).                  |   |
| Type       | Q 4 AKZ4                   | Version   |
| Order No.  | <a href="#">0336600000</a> | Cross-connector (terminal), when screwed in, Number of poles: 4,  |
| GTIN (EAN) | 4008190096656              | Pitch in mm (P): 6.10, Insulated: No, 24 A, grey                  |
| Qty.       | 50 pc(s).                  |   |
| Type       | Q 10 AKZ4                  | Version   |
| Order No.  | <a href="#">0368600000</a> | Cross-connector (terminal), when screwed in, Number of poles: 10, |
| GTIN (EAN) | 4008190056766              | Pitch in mm (P): 6.10, Insulated: No, 24 A, grey                  |
| Qty.       | 20 pc(s).                  |   |

## SAK-Series



End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | AP DK4 BL                  | Version                                      |
| Order No.  | <a href="#">0359280000</a> | End plate (terminals), 50 mm x 1.5 mm, blue  |
| GTIN (EAN) | 4008190031213              |  |
| Qty.       | 20 pc(s).                  |  |
| Type       | AP DK4                     | Version                                      |
| Order No.  | <a href="#">0359260000</a> | End plate (terminals), 50 mm x 1.5 mm, beige |
| GTIN (EAN) | 4008190012991              |  |
| Qty.       | 20 pc(s).                  |  |

## DK 4/35 LD GR 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

|            |                            |  |
|------------|----------------------------|--|
| Type       | AP DK4/380 Q               | Version                                      |
| Order No.  | <a href="#">0438560000</a> | End plate (terminals), 51 mm x 1.5 mm, beige |
| GTIN (EAN) | 4008190133351              |  |
| Qty.       | 20 pc(s).                  |  |

## Testsockets




Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

## General ordering data

|            |                            |                     |
|------------|----------------------------|---------------------|
| Type       | STB 8.5/D4/2.3/M2.5 AKZ    | Version             |
| Order No.  | <a href="#">0215700000</a> | Accessories, Socket |
| GTIN (EAN) | 4008190184872              |                     |
| Qty.       | 50 pc(s).                  |                     |

## TS 32



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | EWK 1                      | Version   |
| Order No.  | <a href="#">0206160000</a> | End bracket, Wemid, beige, Rail: TS 32, when screwed in |
| GTIN (EAN) | 4008190080020              |   |
| Qty.       | 50 pc(s).                  |   |

## DK 4/35 LD GR 24VDC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | DEK 5/6 MC NE GR           | Version   |
| Order No.  | <a href="#">1238330000</a> | Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 |
| GTIN (EAN) | 4050118323306              | Weidmueller, grey   |
| Qty.       | 1,000 pc(s).               |   |
| Type       | DEK 5/6 MC NE GN           | Version   |
| Order No.  | <a href="#">1238310000</a> | Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 |
| GTIN (EAN) | 4050118271812              | Weidmueller, green  |
| Qty.       | 1,000 pc(s).               |   |
| Type       | DEK 5/6 MC NE OR           | Version   |
| Order No.  | <a href="#">1912090000</a> | Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 |
| GTIN (EAN) | 4032248540525              | Weidmueller, orange                                       |
| Qty.       | 1,000 pc(s).               |   |
| Type       | DEK 5/6 MC NE BL           | Version   |
| Order No.  | <a href="#">1238290000</a> | Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 |
| GTIN (EAN) | 4050118267327              | Weidmueller, blue   |
| Qty.       | 1,000 pc(s).               |   |
| Type       | DEK 5/6 MC NE BR           | Version   |
| Order No.  | <a href="#">1454900000</a> | Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 |
| GTIN (EAN) | 4050118323313              | Weidmueller, brown  |
| Qty.       | 1,000 pc(s).               |   |
| Type       | DEK 5/6 MC NE WS           | Version   |
| Order No.  | <a href="#">1609820000</a> | Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 |
| GTIN (EAN) | 4008190203436              | Weidmueller, white  |
| Qty.       | 1,000 pc(s).               |   |
| Type       | DEK 5/6 MC NE GE           | Version   |
| Order No.  | <a href="#">1238280000</a> | Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 |
| GTIN (EAN) | 4050118038750              | Weidmueller, yellow                                       |
| Qty.       | 1,000 pc(s).               |   |