VP 11-K54

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	VPK (blanking plug in plastic), Blanking plug, in closed state, PG 11, 6.5 mm, IP65, Polyamid 6 (PA6 - GF30)
Order No.	0294860000
Type	VP 11-K54
GTIN (EAN)	4008190147822
Qty.	100 pc(s).

VP 11-K54

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	3.5 mm	Height (inches)	0.138 inch
Length	10 mm	Length (inches)	0.394 inch
Diameter	18.6 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	5.5 mm	Net weight	1.2 g

Temperatures

Operating temperature	-40 °C...100 °C

General information

Cable glands	PG	Diameter of sealing ring	18.6 mm
External thread	PG 11	Halogen	No
Head diameter	22 mm	Length of thread	6.5 mm
Material	Polyamid 6 (PA6 - GF30)	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Protection degree	IP54
Protection degree with GWDR	IP65	UL 94 flammability rating	V-2

Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
ETIM 8.0	EC000451	ETIM 9.0	EC000451
ECLASS 9.0	27-14-44-25	ECLASS 9.1	27-14-44-33
ECLASS 10.0	27-14-44-25	ECLASS 11.0	27-14-44-25
ECLASS 12.0	27-14-08-05	ECLASS 13.0	27-14-08-05

Approvals

ROHS	Conform

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	

VP 11-K54

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

