Q 10 AKZ4SS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

Version	SAK Series, Cross-connector, for cross-connection link, Number of poles: 10
Order No.	0369300000
Type	Q 10 AKZ4SS
GTIN (EAN)	4008190065744
Qty.	20 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2023-12-31

Q 10 AKZ4SS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	13 mm	Depth (inches)	0.512 inch
Height	4 mm	Height (inches)	0.157 inch
Width	59.9 mm	Width (inches)	2.358 inch
Net weight	10.6 g		

Temperatures

Storage temperature	-25 °C...55 °C

Material data

Material	Cu Zn	Colour	grey

System specifications

Version	for cross-connection link

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

Cross-connector

Number of cross-connected terminals	10	Rated current, 2-pole	20 A
Rated current, multi-pole	20 A	Type	Cross-connector

Dimensions

Pitch in mm (P)	5.1 mm

General

Installation advice	Direct mounting	Number of poles	10

Rating data

Rated current	32 A

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

Approvals

ROHS	Conform

Q 10 AKZ4SS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data	CAD data – STEP
Engineering Data	Zuken E3.S
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	