# Q 10 SAK10

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Product image



Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

### General ordering data

| | |
|---|---|
| Version | SAK Series, Cross-connector, for cross-connection link, Number of poles: 10 |
| Order No. | 0457400000 |
| Type | Q 10 SAK10 |
| GTIN (EAN) | 4008190016166 |
| Qty. | 20 pc(s). |

# Q 10 SAK10

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

| | | | |
|---|---|---|---|
| Depth | 20.5 mm | Depth (inches) | 0.807 inch |
| Height | 6 mm | Height (inches) | 0.236 inch |
| Width | 96.1 mm | Width (inches) | 3.783 inch |
| Net weight | 28.65 g | | |

### Temperatures

| | |
|---|---|
| Storage temperature | -25 °C...55 °C |

### Material data

| | | | |
|---|---|---|---|
| Material | CuSn | Colour | grey |

### System specifications

| | |
|---|---|
| Version | for cross-connection link |

### Additional technical data

| | | | |
|---|---|---|---|
| Explosion-tested version | No | Installation advice | Direct mounting |
| Type of fixing | when screwed in | | |

### Cross-connector

| | | | |
|---|---|---|---|
| Number of cross-connected terminals | 10 | Rated current, 2-pole | 57 A |
| Rated current, multi-pole | 57 A | Type | Cross-connector |

### Dimensions

| | |
|---|---|
| Pitch in mm (P) | 9.9 mm |

### General

| | | | |
|---|---|---|---|
| Installation advice | Direct mounting | Number of poles | 10 |

### Rating data

| | |
|---|---|
| Rated current | 57 A |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 6.0 | EC000489 | ETIM 7.0 | EC000489 |
| ETIM 8.0 | EC000489 | ETIM 9.0 | EC000489 |
| ECLASS 9.0 | 27-14-11-40 | ECLASS 9.1 | 27-14-11-40 |
| ECLASS 10.0 | 27-14-11-40 | ECLASS 11.0 | 27-14-11-40 |
| ECLASS 12.0 | 27-14-11-40 | ECLASS 13.0 | 27-25-03-03 |

### Approvals

| | |
|---|---|
| ROHS | Conform |

# Q 10 SAK10

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Technical data

### Downloads

| | |
|---|---|
| Engineering Data | CAD data – STEP |
| User Documentation | StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |