# ZSI 2.5/LD 60AC OR

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Product image

In some applications it is useful to protect the feed through connection with a separate fuse. Fuse terminal blocks are made up of one terminal block bottom section with a fuse insertion carrier. The fuses vary from pivoting fuse levers and pluggable fuse holders to screwable closures and flat plug-in fuses.

### General ordering data

| | |
|---|---|
| Version | Z-series, Fuse terminal, Rated cross-section: 2.5 mm², Tension-clamp connection |
| Order No. | 1082370000 |
| Type | ZSI 2.5/LD 60AC OR |
| GTIN (EAN) | 4032248881000 |
| Qty. | 50 pc(s). |

# ZSI 2.5/LD 60AC OR

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

| | | | |
|---|---|---|---|
| Depth | 73 mm | Depth (inches) | 2.874 inch |
| Depth including DIN rail | 74 mm | Height | 79.5 mm |
| Height (inches) | 3.13 inch | Width | 7.9 mm |
| Width (inches) | 0.311 inch | Net weight | 21.24 g |

### Temperatures

| | | | |
|---|---|---|---|
| Storage temperature | -25 °C...55 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 120 °C | | |

### Material data

| | | | |
|---|---|---|---|
| Material | Wemid | Colour | orange |
| UL 94 flammability rating | V-0 | | |

### System specifications

| | | | |
|---|---|---|---|
| Version | Tension-clamp connection, Fuse cartridge, with LED, for plug-in cross-connector, One end without connector | End cover plate required | Yes |
| Number of potentials | 1 | Number of levels | 1 |
| Number of clamping points per level | 2 | Number of potentials per tier | 1 |
| Levels cross-connected internally | No | PE connection | No |
| Rail | TS 35 | N-function | No |
| PE function | No | PEN function | No |

### Additional technical data

| | |
|---|---|
| Type of mounting | Snap-on |

### Conductors for clamping (additional connection)

| | | | |
|---|---|---|---|
| Connection direction | top | Connection type, additional connection | Tension-clamp connection |

### Conductors for clamping (rated connection)

| | | | |
|---|---|---|---|
| Number of connections | 2 | Type of connection | Tension-clamp connection |
| Type of connection 2 | Tension-clamp connection | | |

### Fuse terminals

| | | | |
|---|---|---|---|
| Cartridge fuse | G-Si. 5 x 20 | Operating voltage, max. | 60 V |
| Power loss for overload and short-circuit protection for a composite arrangement | 1.6 W at 6.3 A @ 41°C | Power loss for overload and short-circuit protection for an individual arrangement | 2.5 W at 2.5 A @ 27°C |
| Power loss for short-circuit protection only for a composite arrangement | 2.5 W at 6.3 A @ 55°C | Power loss for short-circuit protection only for an individual arrangement | 4.0 W at 6.3 A @ 52°C |

### General

| | |
|---|---|
| Rail | TS 35 |

# ZSI 2.5/LD 60AC OR

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Technical data

### Rating data

| | | | |
|---|---|---|---|
| Rated cross-section | 2.5 mm² | Rated voltage | 60 V |
| Rated voltage to adjoining terminal | 500 V | Rated DC voltage | 60 V |
| Rated current | 6.3 A | Volume resistance according to IEC 60947-7-x | 1.33 mΩ |
| Power loss in accordance with IEC 60947-7-x | 0.77 W | | |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 6.0 | EC000899 | ETIM 7.0 | EC000899 |
| ETIM 8.0 | EC000899 | ETIM 9.0 | EC000899 |
| ECLASS 9.0 | 27-14-11-16 | ECLASS 9.1 | 27-14-11-16 |
| ECLASS 10.0 | 27-14-11-16 | ECLASS 11.0 | 27-14-11-16 |
| ECLASS 12.0 | 27-14-11-16 | ECLASS 13.0 | 27-25-01-13 |

### Important note

| | |
|---|---|
| Product information | The voltage depends on the selected fuse element or the selected indicator light |

### Approvals

| | |
|---|---|
| Approvals | |
| ROHS | Conform |

### Downloads

| | |
|---|---|
| Approval/Certificate/Document of Conformity | CB Test Certificate<br>CB Certificate<br>RINA Certificate<br>CB Certificate<br>CB Certificate<br>CB Certificate<br>Declaration of Conformity<br>UKCA declaration of conformity |
| Engineering Data | CAD data – STEP |
| User Documentation | Beipackzettel_SAKS_GL_LD.pdf<br>StorageConditionsTerminalBlocks<br>User Manual Z-Series |
| Catalogues | Catalogues in PDF-format |

## ZSI 2.5/LD 60AC OR

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Drawings



# ZSI 2.5/LD 60AC OR

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Accessories

### ZGB pivotable group tag holder

The ZGB 15 is a hinged group tag carrier. The tag carrier can hold the dekafix 5, WS 12/5 terminal markers or the inlay tag ESO 15.
The ZGB 30 is a hinged group tag carrier. The tag carrier can hold the dekafix 5, WS 12/5 terminal markers or the inlay tag ESO 7.
Inlay tags and protective strips can be found under "Accessories".

#### General ordering data

| | | |
|---|---|---|
| Type | ZGB 15 | Version |
| Order No. | 1636530000 | Terminal markers, Terminal marker, 15 x 7 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190297053 | Weidmueller, white |
| Qty. | 20 pc(s). | |
| Type | ZGB 30 | Version |
| Order No. | 1611930000 | Terminal markers, Terminal marker, 32 x 7 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190002251 | Weidmueller, white |
| Qty. | 20 pc(s). | |
| Type | ZGB 30/3.5 | Version |
| Order No. | 1778290000 | Terminal markers, Terminal marker, 32 x 7 mm, Pitch in mm (P): 3.50 |
| GTIN (EAN) | 4032248161065 | white |
| Qty. | 20 pc(s). | |

### STR transparent strips

#### General ordering data

| | | |
|---|---|---|
| Type | STR 7 F.SCHT 7 | Version |
| Order No. | 0515300000 | Terminal markers, Protective cap, 27 x 6.3 mm, Transparent |
| GTIN (EAN) | 4008190182175 | |
| Qty. | 20 pc(s). | |

# ZSI 2.5/LD 60AC OR

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Accessories

### Z-Series

Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

### General ordering data

| | | |
|---|---|---|
| Type | ZTA 1 | Version |
| Order No. | 1609040000 | Accessories, Test adapter, 9 A |
| GTIN (EAN) | 4008190196851 | |
| Qty. | 25 pc(s). | |

| | | |
|---|---|---|
| Type | ZTA 1/ZA | Version |
| Order No. | 1609050000 | Accessories, Test adapter, 9 A |
| GTIN (EAN) | 4008190206543 | |
| Qty. | 25 pc(s). | |

### Z-Series

Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

### General ordering data

| | | |
|---|---|---|
| Type | ZST 1 | Version |
| Order No. | 1269070000 | Accessories, Accessories holder |
| GTIN (EAN) | 4050118094091 | |
| Qty. | 25 pc(s). | |

# ZSI 2.5/LD 60AC OR

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Accessories

### 5x20

For protection against overcurrent, we offer cartridge fuse with dimensions 5x20 mm in sizes from 100 mA to 6.3 A.

### General ordering data

| | | |
|---|---|---|
| Type | G 20/0.10A/F | Version |
| Order No. | 0430300000 | Miniature fuse, quick-acting, 0.1 A, G-Si. 5 x 20 |
| GTIN (EAN) | 4008190077174 | |
| Qty. | 10 pc(s). | |
| Type | G 20/4.00A/F | Version |
| Order No. | 0431200000 | Miniature fuse, quick-acting, 4 A, G-Si. 5 x 20 |
| GTIN (EAN) | 4008190022983 | |
| Qty. | 10 pc(s). | |
| Type | G 20/1.60A/F | Version |
| Order No. | 0430800000 | Miniature fuse, quick-acting, 1.6 A, G-Si. 5 x 20 |
| GTIN (EAN) | 4008190031503 | |
| Qty. | 10 pc(s). | |
| Type | G 20/2.50A/F | Version |
| Order No. | 0431000000 | Miniature fuse, quick-acting, 2.5 A, G-Si. 5 x 20 |
| GTIN (EAN) | 4008190085513 | |
| Qty. | 10 pc(s). | |
| Type | G 20/1.00A/F | Version |
| Order No. | 0430700000 | Miniature fuse, quick-acting, 1 A, G-Si. 5 x 20 |
| GTIN (EAN) | 4008190093877 | |
| Qty. | 10 pc(s). | |
| Type | G 20/6.30A/F | Version |
| Order No. | 0431400000 | Miniature fuse, quick-acting, 6.3 A, G-Si. 5 x 20 |
| GTIN (EAN) | 4008190086053 | |
| Qty. | 10 pc(s). | |
| Type | G 20/0.50A/F | Version |
| Order No. | 0430600000 | Miniature fuse, quick-acting, 0.5 A, G-Si. 5 x 20 |
| GTIN (EAN) | 4008190046835 | |
| Qty. | 10 pc(s). | |
| Type | G 20/0.25A/F | Version |
| Order No. | 0430500000 | Miniature fuse, quick-acting, 0.25 A, G-Si. 5 x 20 |
| GTIN (EAN) | 4008190153991 | |
| Qty. | 10 pc(s). | |
| Type | G 20/0.63A/F | Version |
| Order No. | 0439000000 | Miniature fuse, quick-acting, 0.63 A, G-Si. 5 x 20 |
| GTIN (EAN) | 4008190131210 | |
| Qty. | 10 pc(s). | |
| Type | G 20/5.00A/F | Version |
| Order No. | 0431300000 | Miniature fuse, quick-acting, 5 A, G-Si. 5 x 20 |
| GTIN (EAN) | 4008190185381 | |
| Qty. | 10 pc(s). | |

# ZSI 2.5/LD 60AC OR

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Accessories

| | | |
|---|---|---|
| Type | G 20/3.15A/F | Version |
| Order No. | 0431100000 | Miniature fuse, quick-acting, 3.15 A, G-Si. 5 x 20 |
| GTIN (EAN) | 4008190012977 | |
| Qty. | 10 pc(s). | |

| | | |
|---|---|---|
| Type | G 20/2.00A/F | Version |
| Order No. | 0430900000 | Miniature fuse, quick-acting, 2 A, G-Si. 5 x 20 |
| GTIN (EAN) | 4008190123567 | |
| Qty. | 10 pc(s). | |

| | | |
|---|---|---|
| Type | G 20/0.20A/F | Version |
| Order No. | 0430400000 | Miniature fuse, quick-acting, 0.2 A, G-Si. 5 x 20 |
| GTIN (EAN) | 4008190152383 | |
| Qty. | 10 pc(s). | |

### Blank

WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text.
WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

| | | |
|---|---|---|
| Type | WS 10/15 MC NE WS | Version |
| Order No. | 1854090000 | WS, Terminal marker, 10 x 15 mm, Pitch in mm (P): 15.00 |
| GTIN (EAN) | 4032248390694 | Weidmueller, Allen-Bradley, white |
| Qty. | 240 pc(s). | |

# ZSI 2.5/LD 60AC OR

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Accessories

### Blank



ZS markers - in proven MultiCard-format - have been developed specifically for the Z-series. They have a large printing area. The hinged mechanism even allows access to cross-connectors without dismantling. Quick installation is guaranteed by the fact that the single tags are clipped on in strips. The single tags are easy to separate.

- Hinged marker area
- Can be fitted in strips or individually
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

#### General ordering data

| | | |
|---|---|---|
| Type | ZS 10/5 MC NE WS | Version |
| Order No. | 1610000000 | ZS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4008190263171 | Allen-Bradley, white |
| Qty. | 480 pc(s). | |

### 2.5 mm²

End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

#### General ordering data

| | | |
|---|---|---|
| Type | ZAP TNHE/ZSI2.5 | Version |
| Order No. | 1610840000 | Z-series, End plate |
| GTIN (EAN) | 4008190263379 | |
| Qty. | 25 pc(s). | |
| Type | ZAP/TW 3 GR | Version |
| Order No. | 1683870000 | Z-series, End plate, Partition plate |
| GTIN (EAN) | 4008190477592 | |
| Qty. | 50 pc(s). | |
| Type | ZAP/TW 3 WS | Version |
| Order No. | 1683880000 | Z-series, End plate, Partition plate |
| GTIN (EAN) | 4008190477608 | |
| Qty. | 50 pc(s). | |
| Type | ZAP/TW 3 SW | Version |
| Order No. | 1683890000 | Z-series, End plate, Partition plate |
| GTIN (EAN) | 4008190477615 | |
| Qty. | 50 pc(s). | |

# ZSI 2.5/LD 60AC OR

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Accessories

| | | |
|---|---|---|
| Type | ZAP/TW 3 OR | Version |
| Order No. | 1608820000 | Z-series, End plate, Partition plate |
| GTIN (EAN) | 4008190190941 | |
| Qty. | 50 pc(s). | |

| | | |
|---|---|---|
| Type | ZAP/TW 3 | Version |
| Order No. | 1608800000 | Z-series, Accessories, End plate, Partition plate |
| GTIN (EAN) | 4008190190927 | |
| Qty. | 50 pc(s). | |

| | | |
|---|---|---|
| Type | ZAP/TW 3 RT | Version |
| Order No. | 1683820000 | Z-series, End plate, Partition plate |
| GTIN (EAN) | 4008190477547 | |
| Qty. | 50 pc(s). | |

| | | |
|---|---|---|
| Type | ZAP/TW 3 BL | Version |
| Order No. | 1608810000 | Z-series, End plate, Partition plate |
| GTIN (EAN) | 4008190190934 | |
| Qty. | 50 pc(s). | |

| | | |
|---|---|---|
| Type | ZAP/TW 3 GN | Version |
| Order No. | 1683840000 | Z-series, End plate, Partition plate |
| GTIN (EAN) | 4008190477561 | |
| Qty. | 50 pc(s). | |

### Blank

WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text.
WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

| | | |
|---|---|---|
| Type | WS 10/5 MC NE WS | Version |
| Order No. | 1635000000 | WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4008190261948 | Allen-Bradley, white |
| Qty. | 720 pc(s). | |

| | | |
|---|---|---|
| Type | WS 10/5 M MC NE WS | Version |
| Order No. | 1792000000 | WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248223862 | Allen-Bradley, white |
| Qty. | 720 pc(s). | |

# ZSI 2.5/LD 60AC OR

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Accessories

### 6 mm²

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

### General ordering data

| | | |
|---|---|---|
| Type | ZQV 6/3 GE | Version |
| Order No. | 1627860000 | Accessories, Cross-connector, 41 A |
| GTIN (EAN) | 4008190200435 | |
| Qty. | 60 pc(s). | |
| Type | ZQV 6/4 GE | Version |
| Order No. | 1627870000 | Accessories, Cross-connector, 41 A |
| GTIN (EAN) | 4008190200442 | |
| Qty. | 60 pc(s). | |
| Type | ZQV 6/2 GE | Version |
| Order No. | 1627850000 | Accessories, Cross-connector, 41 A |
| GTIN (EAN) | 4008190200428 | |
| Qty. | 60 pc(s). | |
| Type | ZQV 6/24 GE | Version |
| Order No. | 1908990000 | Accessories, Cross-connector, 41 A |
| GTIN (EAN) | 4032248535309 | |
| Qty. | 10 pc(s). | |
| Type | ZQV 6/32 GE | Version |
| Order No. | 1733640000 | Accessories, Cross-connector, 41 A |
| GTIN (EAN) | 4008190994334 | |
| Qty. | 10 pc(s). | |

# ZSI 2.5/LD 60AC OR

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Accessories

### Blank

ZS markers - in proven MultiCard-format - have been developed specifically for the Z-series. They have a large printing area. The hinged mechanism even allows access to cross-connectors without dismantling. Quick installation is guaranteed by the fact that the single tags are clipped on in strips. The single tags are easy to separate.

- Hinged marker area
- Can be fitted in strips or individually
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

#### General ordering data

| | | |
|---|---|---|
| Type | ZS 15/5 MC NE WS | Version |
| Order No. | 1646630000 | ZS, Terminal marker, 15 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4008190401214 | Allen-Bradley, white |
| Qty. | 480 pc(s). | |

### Marker holder

The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snaped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

#### General ordering data

| | | |
|---|---|---|
| Type | BZT 1 WS 10/5 | Version |
| Order No. | 1805490000 | Accessories, Marker holder |
| GTIN (EAN) | 4032248270231 | |
| Qty. | 100 pc(s). | |
| Type | BZT 1 ZA WS 10/5 | Version |
| Order No. | 1805520000 | Accessories, Marker holder |
| GTIN (EAN) | 4032248270248 | |
| Qty. | 100 pc(s). | |

# ZSI 2.5/LD 60AC OR

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Accessories

### Slotted screwdriver



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

#### General ordering data

| | | |
|---|---|---|
| Type | SDIS SLIM 0.6X3.5X100 | Version |
| Order No. | 2749610000 | Mounting tool, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade |
| GTIN (EAN) | 4050118896350 | thickness (A): 0.6 mm |
| Qty. | 1 pc(s). | |

### Blank

The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.
Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

#### General ordering data

| | | |
|---|---|---|
| Type | DEK 5/5 MC NE WS | Version |
| Order No. | 1609801044 | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190397111 | Weidmueller, white |
| Qty. | 1,000 pc(s). | |

# ZSI 2.5/LD 60AC OR

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Accessories

### Blank

ZS markers - in proven MultiCard-format - have been developed specifically for the Z-series. They have a large printing area. The hinged mechanism even allows access to cross-connectors without dismantling. Quick installation is guaranteed by the fact that the single tags are clipped on in strips. The single tags are easy to separate.

- Hinged marker area
- Can be fitted in strips or individually
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

| | | |
|---|---|---|
| Type | ZS 12/6 MC NE WS | Version |
| Order No. | 1610020000 | ZS, Terminal marker, 12 x 6 mm, Pitch in mm (P): 6.00 Weidmueller, |
| GTIN (EAN) | 4008190444600 | Allen-Bradley, white |
| Qty. | 400 pc(s). | |