# POK MOPL 1212 MINI

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Similar to illustration



Similar to illustration

The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.
Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- 
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

### General ordering data

| | |
|---|---|
| Version | Klippon POK (polyester empty enclosure), Mounting plate, Height: 77 mm, Width: 109 mm, Depth: 1.5 mm, Material: Sheet steel, galvanized, galvanized, silver |
| Order No. | 1534340000 |
| Type | POK MOPL 1212 MINI |
| GTIN (EAN) | 4050118338218 |
| Qty. | 1 pc(s). |

# POK MOPL 1212 MINI

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

| | | | |
|---|---|---|---|
| Depth | 1.5 mm | Depth (inches) | 0.059 inch |
| Height | 77 mm | Height (inches) | 3.031 inch |
| Width | 109 mm | Width (inches) | 4.291 inch |
| Mounting dimension - height | 52 mm | Mounting dimension - width | 95 mm |
| Net weight | 88 g | | |

### General information

| | | | |
|---|---|---|---|
| Material | Sheet steel, galvanized | Material thickness | 1.5 mm |
| Surface finish | galvanized | | |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 6.0 | EC000213 | ETIM 7.0 | EC000213 |
| ETIM 8.0 | EC000213 | ETIM 9.0 | EC000213 |
| ECLASS 9.0 | 27-40-06-39 | ECLASS 9.1 | 27-18-92-90 |
| ECLASS 10.0 | 27-40-06-39 | ECLASS 11.0 | 27-40-06-39 |
| ECLASS 12.0 | 27-40-06-39 | ECLASS 13.0 | 27-40-06-39 |

### Downloads

| | |
|---|---|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

# POK MOPL 1212 MINI

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Accessories

### Depth 7.5 mm



The system accessories for the Klippon® K enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.
- DIN Rails TS 35 and TS15
- Mounting plates
- Hinges
- Wall-mounted holder

### General ordering data

| | | |
|---|---|---|
| Type | TS35X7.5 ST K41 | Version |
| Order No. | 8000003439 | Rail, TS 35, TS 35 x 7.5, Width: 105 mm, without slot, Steel, galvanic |
| GTIN (EAN) | 4050118652628 | zinc plated and passivated |
| Qty. | 20 pc(s). | |