KCMA-8-1200-5A-10VA1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Current transformers for retrofitting
Features:
- especially suitable for use in hard-to-reach places
- no cutting of the primary conductors necessary
- Unfolding of the current transformer without additional tools

General ordering data

Version	Primary current: 1200 A, Secondary current max.: 5 A, Load: 10 VA, Tolerance class: 1, Split-core current transformer
Order No.	2728140000
Type	KCMA-8-1200-5A-10VA1
GTIN (EAN)	4050118809992
Qty.	1 pc(s).
Manufacturer	MBS AG

KCMA-8-1200-5A-10VA1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	58 mm	Depth (inches)	2.283 inch
Height	198 mm	Height (inches)	7.795 inch
Width	155 mm	Width (inches)	6.102 inch
Net weight	1,500 g		

Dimensions of live conductors

Type of conductor	Insulated conductor only	Round conductor	80 mm
Rail	80 x 120 mm	Installation location	Indoor use

Electrical attributes

Load	10 VA	Primary current	1,200 A
Secondary current	0...5 A	Tolerance class	1

Technical properties

Insulation class	E	Nominal frequency	50 Hz
Protection degree	IP20	Thermal rated continuous current $I_{thermal}$	1.2 x I_{rated}

Classifications

ETIM 6.0	EC002048	ETIM 7.0	EC002048
ETIM 8.0	EC002048	ETIM 9.0	EC002048
ECLASS 9.0	27-21-09-02	ECLASS 9.1	27-21-09-02
ECLASS 10.0	27-21-09-02	ECLASS 11.0	27-21-09-02
ECLASS 12.0	27-21-09-02	ECLASS 13.0	27-21-09-02

Approvals

ROHS	Conform

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity
User Documentation	Device description – Betriebsanleitung deutsch Device description – Instruction sheet english
Catalogues	Catalogues in PDF-format

KCMA-8-1200-5A-10VA1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings







