KCMA-42-600-5A-2.5VA-0.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image, Similar to illustration



Current transformers for retrofitting
Features:
- especially suitable for use in hard-to-reach places
- no cutting of the primary conductors necessary
- Unfolding of the current transformer without additional tools

General ordering data

Version	Primary current: 600 A, Secondary current max.: 5 A, Load: 2.5 VA, Tolerance class: 0,5, Split-core current transformer
Order No.	2753260000
Type	KCMA-42-600-5A-2.5VA-0.5
GTIN (EAN)	4050118896688
Qty.	1 pc(s).
Manufacturer	MBS AG

KCMA-42-600-5A-2.5VA-0.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	69 mm	Depth (inches)	2.717 inch
Height	96 mm	Height (inches)	3.78 inch
Width	67 mm	Width (inches)	2.638 inch
Net weight	427 g		

Temperatures

Operating temperature	-5 °C...50 °C

Dimensions of live conductors

Type of conductor	Insulated conductor only	Round conductor	42 mm
Installation location	Indoor use		

Electrical attributes

Load	2.5 VA	Primary current	600 A
Secondary current	0...5 A	Tolerance class	0,5

Technical properties

Cable length	0.5 m	Protection degree	IP20

Classifications

ETIM 6.0	EC002048	ETIM 7.0	EC002048
ETIM 8.0	EC002048	ETIM 9.0	EC002048
ECLASS 9.0	27-21-09-02	ECLASS 9.1	27-21-09-02
ECLASS 10.0	27-21-09-02	ECLASS 11.0	27-21-09-02
ECLASS 12.0	27-21-09-02	ECLASS 13.0	27-21-09-02

Approvals

ROHS	Conform

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity
Catalogues	Catalogues in PDF-format

KCMA-42-600-5A-2.5VA-0.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



