MP TBF 30/19

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration



The enclosures of the TBF series are made of extremely tough glass fibre-reinforced polyester. These enclosures are ideal for applications that call for low weight coupled with high shock resistance. The weather-resistant TBF enclosures are designed for a wide range of applications. Together with their comprehensive range of accessories, they provide universal solutions for accommodating built-in items such as regulators, measuring instruments, valves and other equipment.
Features:

- 9 sizes in 2 versions, with grey and transparent lids
- Cover with nylon screws
- Fixing holes outside the sealed area
- Thread for fitting to terminal rails and mounting plates
- Comprehensive accessories
- Weidmüller can manufacture and supply this enclosure to match customer specifications, fitted with all necessary terminals and cable glands.

General ordering data

Version	TBF (polyester empty enclosure), Mounting plate, Mounting plate, Height: 249 mm, Width: 134 mm, Depth: 2 mm, Material: Sheet steel, galvanized, galvanized, silver
Order No.	3018950000
Type	MP TBF 30/19
GTIN (EAN)	4032248008759
Qty.	1 pc(s).

MP TBF 30/19

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	2 mm	Depth (inches)	0.079 inch
Height	249 mm	Height (inches)	9.803 inch
Width	134 mm	Width (inches)	5.276 inch
Net weight	503 g		

General information

Material	Sheet steel, galvanized	Material thickness	2 mm
Surface finish	galvanized	Type of fixing	when screwed in

Classifications

ETIM 6.0	EC000213	ETIM 7.0	EC000213
ETIM 8.0	EC000213	ETIM 9.0	EC000213
ECLASS 9.0	27-40-06-39	ECLASS 9.1	27-18-92-90
ECLASS 10.0	27-40-06-39	ECLASS 11.0	27-40-06-39
ECLASS 12.0	27-40-06-39	ECLASS 13.0	27-40-06-39

Approvals

ROHS	Conform

Downloads

Catalogues	Catalogues in PDF-format
Brochures	