WIDERSTANDSBOX 8X18K 3W

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Order No.	8943120000
Type	WIDERSTANDSBOX 8X18K 3W
GTIN (EAN)	4032248752713
Qty.	1 pc(s).

WIDERSTANDSBOX 8X18K 3W

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	100 mm	Height (inches)	3.937 inch
Width	55.5 mm	Width (inches)	2.185 inch
Length	125 mm	Length (inches)	4.921 inch
Net weight	425 g		

Temperatures

Storage temperature	-40...70 °C	Ambient temperature	+70 °C
Operating temperature	-25...70		

Connection data

Type of connection	Tension-clamp connection

Insulation coordination (EN50178)

Pollution severity level	2

Connection field

Clamping range, max.	1 mm²	Clamping range, min.	0.08 mm²
Stripping length	7 mm	Type of connection	Tension-clamp connection

Input

Resistance	8 x 3,6 kΩ 1 W

Classifications

ETIM 6.0	EC002024	ETIM 7.0	EC002024
ETIM 8.0	EC002024	ECLASS 10.0	27-26-01-90
ECLASS 11.0	27-26-01-90		

Approvals

ROHS	Conform

Downloads

Catalogues	Catalogues in PDF-format