


**NT 6/35 10X3 KRG/BL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Installation terminal blocks have been specially developed for use in sub-distribution cabinets. Due to their design, they still fit under the cover of the respective sub-distribution after wiring. The product range includes both multi-level terminal blocks and single-level N-disconnect terminal blocks with contour-rich feed-through and PE terminal blocks. Depending on the application, a busbar can optionally be integrated in the modular terminal block system.

**General ordering data**

Version	SAK Series, Neutral conductor disconnect terminal, Rated cross-section: 6 mm <sup>2</sup> , Screw connection, Rail, TS 35
Order No.	<a href="#">0501470000</a>
Type	NT 6/35 10X3 KRG/BL
GTIN (EAN)	4008190041052
Qty.	100 pc(s).
Delivery status	<b>Discontinued</b>
Available until	2020-12-31
Alternative product	<a href="#">1010880000</a>

Creation date March 29, 2024 6:16:46 AM CET

Catalogue status 23.03.2024 / We reserve the right to make technical changes.

## NT 6/35 10X3 KRG/BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	44 mm	Depth (inches)	1.732 inch
Height	49 mm	Height (inches)	1.929 inch
Width	8 mm	Width (inches)	0.315 inch
Net weight	20.16 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

## Material data

Material	KrG	Colour	blue
UL 94 flammability rating	V-0, 5VA		

## System specifications

Version	Screw connection, with busbar connection 10x3, One end without connector	End cover plate required	Yes
Number of potentials	1	Number of levels	1
Number of clamping points per level	1	Number of potentials per tier	1
Levels cross-connected internally	No	PE connection	No
Rail	TS 35	N-function	Yes
PE function	No	PEN function	No

## Additional technical data

Installation advice	Rail, TS 35	Open sides	right
Type of mounting	Snap-on		

## CSA rating data

Certificate No. (CSA)	12400-160	Current size B (CSA)	40 A
Current size C (CSA)	40 A	Current size D (CSA)	10 A
Voltage size B (CSA)	300 V	Voltage size C (CSA)	300 V
Voltage size D (CSA)	300 V	Wire cross section max. (CSA)	10 AWG
Wire cross section min. (CSA)	20 AWG		

## NT 6/35 10X3 KRG/BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Conductors for clamping (rated connection)

Blade size	0.8 x 4.0 mm	Clamping range, max.	10 mm <sup>2</sup>
Clamping range, min.	0.5 mm <sup>2</sup>	Clamping screw	M 3.5
Connection cross-section, stranded, max.	10 mm <sup>2</sup>	Connection cross-section, stranded, min.	0.5 mm <sup>2</sup>
Connection direction	on side	Gauge to IEC 60947-1	A5
Number of connections	2	Stripping length	12 mm
Tightening torque, max.	1.4 Nm	Tightening torque, min.	0.8 Nm
Type of connection	Screw connection	Wire connection cross section AWG, max.	AWG 10
Wire connection cross section AWG, min.	AWG 20	Wire connection cross section, finely stranded, max.	10 mm <sup>2</sup>
Wire connection cross section, finely stranded, min.	0.5 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	6 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.5 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max.	6 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	0.5 mm <sup>2</sup>	Wire connection cross-section, solid core, max.	10 mm <sup>2</sup>
Wire connection cross-section, solid core, min.	0.5 mm <sup>2</sup>		

## Dimensions

TS 35 offset	20 mm
--------------	-------

## General

Installation advice	Rail, TS 35	Rail	TS 35
Standards	In accordance with IEC 60947-7-1	Wire connection cross section AWG, max.	AWG 10
Wire connection cross section AWG, min.	AWG 20		

## PE rating data

PEN function	No
--------------	----

## Rating data

Rated cross-section	6 mm <sup>2</sup>	Rated voltage	400 V
Rated DC voltage	400 V	Rated current	41 A
Current at maximum wires	41 A	Standards	In accordance with IEC 60947-7-1
Volume resistance according to IEC 60947-7-x	0.78 mΩ	Rated impulse withstand voltage	6 kV
Power loss in accordance with IEC 60947-7-x	1.31 W	Pollution severity	3

## UL rating data

Certificate No. (UR)	E60693	Conductor size Factory wiring max. (UR)	8 AWG
Conductor size Factory wiring min. (UR)	26 AWG	Conductor size Field wiring max. (UR)	8 AWG
Conductor size Field wiring min. (UR)	22 AWG	Current size C (UR)	40 A
Voltage size C (UR)	300 V		

## NT 6/35 10X3 KRG/BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Classifications

ETIM 6.0	EC000902	ETIM 7.0	EC000902
ETIM 8.0	EC000902	ETIM 9.0	EC000902
ECLASS 9.0	27-14-11-26	ECLASS 9.1	27-14-11-26
ECLASS 10.0	27-14-11-26	ECLASS 11.0	27-14-11-26
ECLASS 12.0	27-14-11-26	ECLASS 13.0	27-25-01-09

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E60693

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">Declaration of Conformity</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**NT 6/35 10X3 KRG/BL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****QL / RSF1+2**

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Type	QL 3 RSF1+2	Version
Order No.	<a href="#">0267500000</a>	SAK Series, Cross-connector, Cross-connector, Number of poles: 3
GTIN (EAN)	4008190116835	
Qty.	50 pc(s).	
Type	QL 2 RSF1+2	Version
Order No.	<a href="#">0267400000</a>	SAK Series, Cross-connector, Cross-connector, Number of poles: 2
GTIN (EAN)	4008190139988	
Qty.	50 pc(s).	
Type	QL 10 RSF1+2	Version
Order No.	<a href="#">0341700000</a>	SAK Series, Cross-connector, Cross-connector, Number of poles: 10
GTIN (EAN)	4008190003173	
Qty.	20 pc(s).	
Type	QL 4 RSF1+2	Version
Order No.	<a href="#">0267600000</a>	SAK Series, Cross-connector, Cross-connector, Number of poles: 4
GTIN (EAN)	4008190174859	
Qty.	50 pc(s).	

## NT 6/35 10X3 KRG/BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/5 MC NE WS	Version
Order No.	<a href="#">1609801044</a>	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00
GTIN (EAN)	4008190397111	Weidmueller, white
Qty.	1,000 pc(s).	

## SAK-Series



End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

## General ordering data

Type	AP SAK4-10 I	Version
Order No.	<a href="#">0117910000</a>	SAK Series, End plate, 1.5 mm, Light Grey, Direct mounting
GTIN (EAN)	4008190183707	
Qty.	20 pc(s).	
Type	AP SAK4-10 DB	Version
Order No.	<a href="#">0105100000</a>	SAK Series, End plate, 1.5 mm, dark beige, Direct mounting
GTIN (EAN)	4008190394875	
Qty.	20 pc(s).	
Type	AP SAK4-10 RT	Version
Order No.	<a href="#">0117900000</a>	SAK Series, End plate, 1.5 mm, red, Direct mounting
GTIN (EAN)	4008190125059	
Qty.	20 pc(s).	

## NT 6/35 10X3 KRG/BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	AP SAK4-10	Version
Order No.	<a href="#">0117960000</a>	SAK Series, End plate, 1.5 mm, beige, Direct mounting
GTIN (EAN)	4008190081485	
Qty.	20 pc(s).	
Type	AP SAK4-10 KRG/BL	Version
Order No.	<a href="#">0117970000</a>	SAK Series, End plate, 1.5 mm, blue, Direct mounting
GTIN (EAN)	4008190049607	
Qty.	20 pc(s).	
Type	TW SAKB/C/T1	Version
Order No.	<a href="#">0242960000</a>	SAK Series, Partition plate, 1.5 mm, beige, Direct mounting
GTIN (EAN)	4008190104092	
Qty.	20 pc(s).	
Type	AP RSF2 KRG	Version
Order No.	<a href="#">0301420000</a>	SAK Series, End plate, 3 mm, medium yellow, Direct mounting
GTIN (EAN)	4008190168537	
Qty.	10 pc(s).	
Type	AP SAKB/C/T KRG	Version
Order No.	<a href="#">0146720000</a>	SAK Series, End plate, 3 mm, dark beige, yellow, Direct mounting
GTIN (EAN)	4008190027995	
Qty.	20 pc(s).	
Type	AP SAK4-10 KRG	Version
Order No.	<a href="#">0117920000</a>	SAK Series, End plate, 1.5 mm, dark beige, yellow, Direct mounting
GTIN (EAN)	4008190135904	
Qty.	20 pc(s).	
Type	AP SAK4-10 BL	Version
Order No.	<a href="#">0117980000</a>	SAK Series, End plate, 1.5 mm, blue, Direct mounting
GTIN (EAN)	4008190171087	
Qty.	20 pc(s).	

## Shorting elements



The short current bridges are inserted into two instrument transformer wiring terminal blocks. By using the short-circuit bridge, the desired short-circuit could be realized within the application for maintenance work.

## General ordering data

Type	QS 2/8/4	Version
Order No.	<a href="#">0270960000</a>	SAK Series, Short-circuit plug, For the terminals, Number of poles: 2
GTIN (EAN)	4008190077006	
Qty.	20 pc(s).	
Type	QVS 2 SAKT1+2	Version
Order No.	<a href="#">0307300000</a>	SAK Series, Cross-connector, Cross-connector, Number of poles: 2
GTIN (EAN)	4008190036140	
Qty.	20 pc(s).	

## NT 6/35 10X3 KRG/BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	QVS 3 SAKT1+2	Version
Order No.	<a href="#">0329300000</a>	SAK Series, Cross-connector, Cross-connector, Number of poles: 3
GTIN (EAN)	4008190084714	
Qty.	20 pc(s).	
Type	QVS 2/S SAKT1+2	Version
Order No.	<a href="#">0358460000</a>	SAK Series, Cross-connector, Cross-connector, Number of poles: 2
GTIN (EAN)	4008190157937	
Qty.	20 pc(s).	
Type	QVSK 2 SAKT1	Version
Order No.	<a href="#">1670360000</a>	SAK Series, Cross-connector, Cross-connector, Number of poles: 2
GTIN (EAN)	4008190431242	
Qty.	20 pc(s).	

## Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/8 MC SDR	Version
Order No.	<a href="#">1856750000</a>	Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00
GTIN (EAN)	4032248400867	Weidmueller, To customer specification
Qty.	160 pc(s).	
Type	DEK 5/8 PLUS MC SDR	Version
Order No.	<a href="#">1046370000</a>	Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00
GTIN (EAN)	4032248782079	Weidmueller, To customer specification
Qty.	160 pc(s).	



## NT 6/35 10X3 KRG/BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Insulation caps



With our accessories for the bus bar taps, you can quickly and easily insulate the tap terminals and visualize the potential through the color coding.

## General ordering data

Type	IK 4 GG ZB4	Version
Order No.	<a href="#">0475460000</a>	Accessories, Special terminal, Rated cross-section: PA, Green/yellow,
GTIN (EAN)	4008190065348	Busbar
Qty.	50 pc(s).	
Type	IK 16/ZB16 GG	Version
Order No.	<a href="#">0502960000</a>	Accessories, Special terminal, Rated cross-section: PA, Green/yellow
GTIN (EAN)	4008190113438	
Qty.	50 pc(s).	
Type	IK 6 GG ZBE6K	Version
Order No.	<a href="#">0526060000</a>	Accessories, Special terminal, Rated cross-section: PA, Green/yellow,
GTIN (EAN)	4008190128647	Busbar
Qty.	50 pc(s).	
Type	IK 4 BL ZB4	Version
Order No.	<a href="#">0475480000</a>	Accessories, Special terminal, Rated cross-section: PA, blue, Busbar
GTIN (EAN)	4008190145668	
Qty.	50 pc(s).	
Type	IK 16/ZB16 BL	Version
Order No.	<a href="#">0502980000</a>	Accessories, Special terminal, Rated cross-section: PA, blue, Busbar
GTIN (EAN)	4008190159696	
Qty.	50 pc(s).	
Type	IK 35/ZB35 BL	Version
Order No.	<a href="#">0502780000</a>	Accessories, Special terminal, Rated cross-section: PA, blue, Busbar
GTIN (EAN)	4008190141455	
Qty.	50 pc(s).	

**NT 6/35 10X3 KRG/BL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Plus**

The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Type	DEK 5/8 PLUS MC NE WS	Version
Order No.	<a href="#">1046350000</a>	Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00
GTIN (EAN)	4032248782055	Weidmueller, white
Qty.	800 pc(s).	

**Mounting rail support**

Mounting rail supports can be used to mount din rails at any location in the cabinet. The resulting raised or angled din rail offers the installer both easier component mounting and wiring.

**General ordering data**

Type	SH 2	Version
Order No.	<a href="#">0494920000</a>	Accessories, Rail support, KrG
GTIN (EAN)	4008190007584	
Qty.	10 pc(s).	

## NT 6/35 10X3 KRG/BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Testsockets



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

## General ordering data

Type	STB 17/D6/4/M4 SAKC10	Version
Order No.	<a href="#">0147100000</a>	SAK Series, Socket
GTIN (EAN)	4008190183042	
Qty.	50 pc(s).	
Type	STB 14/D6/4/M3 SAK10	Version
Order No.	<a href="#">0169900000</a>	Accessories, Socket
GTIN (EAN)	4008190076665	
Qty.	50 pc(s).	
Type	SB 14	Version
Order No.	<a href="#">0135300000</a>	Accessories, Socket
GTIN (EAN)	4008190169558	
Qty.	50 pc(s).	

## Connection sleeves



## General ordering data

Type	VH 12/4.9/3.3	Version
Order No.	<a href="#">0249000000</a>	SAK Series, Connecting sleeve, for cross-connection link, Number of poles:
GTIN (EAN)	4008190129507	
Qty.	100 pc(s).	
Type	VL 2 SAK6N/SAKT	Version
Order No.	<a href="#">0194700000</a>	SAK Series, Cross-connector, for cross-connection link, Number of poles: 2
GTIN (EAN)	4008190148027	
Qty.	50 pc(s).	
Type	VH 19/5/3.4	Version
Order No.	<a href="#">0285100000</a>	SAK Series, Connecting sleeve, for cross-connection link, Number of poles: 1
GTIN (EAN)	4008190189297	
Qty.	50 pc(s).	

## NT 6/35 10X3 KRG/BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	VL 2 SAK6/10/SAKB	Version
Order No.	<a href="#">0135900000</a>	SAK Series, Cross-connector, for cross-connection link, Number of
GTIN (EAN)	4008190036409	poles: 2
Qty.	50 pc(s).	
Type	VH 19/6.3/4.3	Version
Order No.	<a href="#">0318000000</a>	SAK Series, Connecting sleeve, for cross-connection link, Number of
GTIN (EAN)	4008190059460	poles: 1
Qty.	50 pc(s).	

## QL / SAK 6N



Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

## General ordering data

Type	QL 15 SAK6N	Version
Order No.	<a href="#">0221200000</a>	SAK Series, Cross-connector, Cross-connector, Number of poles: 15
GTIN (EAN)	4008190042110	
Qty.	10 pc(s).	
Type	QL 4 SAK6N	Version
Order No.	<a href="#">0194500000</a>	SAK Series, Cross-connector, Cross-connector, Number of poles: 4
GTIN (EAN)	4008190025601	
Qty.	50 pc(s).	
Type	QL 3 SAK6N	Version
Order No.	<a href="#">0194400000</a>	SAK Series, Cross-connector, for cross-connection link, Number of
GTIN (EAN)	4008190063351	poles: 3
Qty.	50 pc(s).	
Type	QL 2 SAK6N	Version
Order No.	<a href="#">0194300000</a>	SAK Series, Cross-connector, for cross-connection link, Number of
GTIN (EAN)	4008190182854	poles: 2
Qty.	50 pc(s).	
Type	QL 10 SAK6N	Version
Order No.	<a href="#">0338300000</a>	SAK Series, Cross-connector, for cross-connection link, Number of
GTIN (EAN)	4008190176679	poles: 10
Qty.	20 pc(s).	

## NT 6/35 10X3 KRG/BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/6 MC NE WS	Version
Order No.	<a href="#">1609820000</a>	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
GTIN (EAN)	4008190203436	Weidmueller, white
Qty.	1,000 pc(s).	

## SchT group marker carrier



The SchT 5 S group tag carriers are clipped directly onto the TS 32 mounting rail (G-rail) or the TS 35 mounting rail (top-hat rail). It is therefore possible to label the terminal strip irrespective of the terminal and the type of terminal. SchT 5 and SchT 5 S are fitted with ESO 5, STR 5 protective strips.

The SchT 7 is a hinged group tag carrier for inlay tags which enables easy access to the clamping screw.

The SchT 7 is fitted with ESO 7, STR 7 protective strips or DEK 5.

Inlay tags and protective strips can be found under "Accessories".

## General ordering data

Type	SCHT 7	Version
Order No.	<a href="#">0517960000</a>	SCHT, Terminal marker, 39.3 x 8 mm, Pitch in mm (P): 7.00
GTIN (EAN)	4008190001742	Weidmueller, white
Qty.	20 pc(s).	

## NT 6/35 10X3 KRG/BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Brass



Brass bus bars, as a copper alloy, has positive properties in terms of electrical conductivity and at the same time has a higher strength than copper against mechanical stress.

## General ordering data

Type	SA 3.00X10.00X1000 CUZN ...	Version
Order No.	<a href="#">0259800000</a>	Accessories, Busbar, Brass
GTIN (EAN)	4008190049300	
Qty.	1 m	

## Q / SAK



Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

## General ordering data

Type	Q 2 SAK6N	Version
Order No.	<a href="#">0456700000</a>	SAK Series, Cross-connector, for cross-connection link, Number of
GTIN (EAN)	4008190150044	poles: 2
Qty.	50 pc(s).	
Type	Q 10 SAK6N	Version
Order No.	<a href="#">0457000000</a>	SAK Series, Cross-connector, for cross-connection link, Number of
GTIN (EAN)	4008190153762	poles: 10
Qty.	20 pc(s).	
Type	Q 3 SAK6N	Version
Order No.	<a href="#">0456800000</a>	SAK Series, Cross-connector, for cross-connection link, Number of
GTIN (EAN)	4008190110277	poles: 3
Qty.	50 pc(s).	
Type	Q 4 SAK6N	Version
Order No.	<a href="#">0456900000</a>	SAK Series, Cross-connector, for cross-connection link, Number of
GTIN (EAN)	4008190032579	poles: 4
Qty.	50 pc(s).	

## NT 6/35 10X3 KRG/BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Fixing screws



Fixing screws fix the short current bridge within the application. If the short current bridge is slid between two adjacent terminal blocks into the short circuit position, it can be fixed by means of a fastening screw. This ensures a permanent connection or short circuit.

## General ordering data

Type	KISC M3X20 SAK10 CU5	Version
Order No.	<a href="#">0377100000</a>	SAK Series, Mounting screw, Copper
GTIN (EAN)	4008190060350	
Qty.	100 pc(s).	

## Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/6 MC SDR	Version
Order No.	<a href="#">1609830000</a>	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
GTIN (EAN)	4008190456603	Weidmueller, To customer specification
Qty.	200 pc(s).	

## NT 6/35 10X3 KRG/BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Copper



Of all the metals used, copper has the best electrical conductivity, which results in the highest short-circuit resistance. This makes the copper busbar the most widely used variant.

## General ordering data

Type	NSCH 1M	Version
Order No.	<a href="#">0280200000</a>	Accessories, Busbar, Copper
GTIN (EAN)	4008190012953	
Qty.	10 m	

## Screws



Depending on the terminal block or also accessories, we offer different types of screws as additional items or also spare parts.

## General ordering data

Type	BFSC M4X6	Version
Order No.	<a href="#">0149700000</a>	Accessories, Mounting screw, for busbars
GTIN (EAN)	4008190016098	
Qty.	100 pc(s).	
Type	BFSC M3X22 PA/RT	Version
Order No.	<a href="#">0128900000</a>	Accessories, Mounting screw, for cross-connection link
GTIN (EAN)	4008190084158	
Qty.	100 pc(s).	
Type	BFSC M3X25	Version
Order No.	<a href="#">0292500000</a>	Accessories, Mounting screw, for cross-connection link
GTIN (EAN)	4008190177027	
Qty.	100 pc(s).	



## NT 6/35 10X3 KRG/BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## DEK 5/8



## WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

## Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

## General ordering data

Type	DEK 5/8 MM WS	Version
Order No.	<a href="#">2007130000</a>	Dekafix, Terminal marker, 5 x 8 mm, Weidmueller, white
GTIN (EAN)	4050118392012	
Qty.	500 pc(s).	

## QL / SAKH 10



Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

## General ordering data

Type	QL 2 SAKH10	Version
Order No.	<a href="#">0131400000</a>	SAK Series, Cross-connector, Cross-connector, Number of poles: 2
GTIN (EAN)	4008190114237	
Qty.	50 pc(s).	
Type	QL 3 SAKH10	Version
Order No.	<a href="#">0131500000</a>	SAK Series, Cross-connector, Cross-connector, Number of poles: 3
GTIN (EAN)	4008190056490	
Qty.	50 pc(s).	

## NT 6/35 10X3 KRG/BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## DEK 5/6



## WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

## Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

## General ordering data

Type	DEK 5/6 MM WS	Version
Order No.	<a href="#">2007120000</a>	Dekafix, Terminal marker, 5 x 6 mm, Weidmueller, white
GTIN (EAN)	4050118392104	
Qty.	600 pc(s).	

## Switch lock



The switch lock can be easily inserted into the terminal from above. The switch lock prevents unauthorised opening or closing of circuits as it blocks the disconnect lever in its respective position.

## General ordering data

Type	SSP 3 SAKT1	Version
Order No.	<a href="#">0531760000</a>	SAK Series, Lockout device
GTIN (EAN)	4008190130787	
Qty.	100 pc(s).	
Type	SSP WTL6/2	Version
Order No.	<a href="#">1604200000</a>	SAK Series, Lockout device
GTIN (EAN)	4008190080532	
Qty.	100 pc(s).	

## NT 6/35 10X3 KRG/BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## W-Series



## Building installation wiring

For building installations, we offer a complete system that revolves around the 10×3 copper rail and comprises perfectly coordinated components: from installation terminal blocks, neutral conductor terminal blocks and distribution terminal blocks to comprehensive accessories such as busbars and busbar holders.

## General ordering data

Type	HP NT6/10 BL	Version
Order No.	<a href="#">0352880000</a>	SAK Series, Fixing plate, blue, 2 mm
GTIN (EAN)	4008190135126	
Qty.	20 pc(s).	

## Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snapped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

## General ordering data

Type	BZT 1 ZA WS 10/5	Version
Order No.	<a href="#">1805520000</a>	Accessories, Marker holder
GTIN (EAN)	4032248270248	
Qty.	100 pc(s).	
Type	BZT 1 WS 10/5	Version
Order No.	<a href="#">1805490000</a>	Accessories, Marker holder
GTIN (EAN)	4032248270231	
Qty.	100 pc(s).	

## NT 6/35 10X3 KRG/BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## SAK-Series



A partition plate is used for the optical separation of circuits or used for electrical isolation from neighbouring cross-connectors. In contrast to the end plate, the contour can be larger than the adjacent terminal blocks. However, it should not be smaller, as otherwise the required clearance and creepage distances within the application can no longer be maintained.

## General ordering data

Type	TW SAK4-10 KRG	Version
Order No.	<a href="#">0130120000</a>	SAK Series, Partition plate, 2.25 mm, dark beige, yellow, Direct
GTIN (EAN)	4008190139117	mounting
Qty.	20 pc(s).	
Type	TW 4 SAK4-10	Version
Order No.	<a href="#">0130160000</a>	SAK Series, Partition plate, 1.5 mm, beige
GTIN (EAN)	4008190096335	
Qty.	20 pc(s).	
Type	TSCH 3 SAKD2.5 N	Version
Order No.	<a href="#">0366860000</a>	SAK Series, Small partition, beige, 5 mm
GTIN (EAN)	4008190010928	
Qty.	100 pc(s).	
Type	TSCH 2	Version
Order No.	<a href="#">0353660000</a>	SAK Series, Small partition, beige, 0.6 mm
GTIN (EAN)	4008190128432	
Qty.	100 pc(s).	
Type	TW SAK4-10 KRG/BL	Version
Order No.	<a href="#">0130170000</a>	SAK Series, Partition plate, 2.25 mm, blue, Direct mounting
GTIN (EAN)	4008190063757	
Qty.	20 pc(s).	
Type	TW SAK4-10 HP/DBR/0.5	Version
Order No.	<a href="#">0197100000</a>	SAK Series, Partition plate, 0.5 mm, brown, dark beige, Direct
GTIN (EAN)	4008190146627	mounting
Qty.	20 pc(s).	
Type	TW AST1/PA HP/DBR/0.5	Version
Order No.	<a href="#">0474700000</a>	SAK Series, Partition plate, 0.5 mm, dark brown
GTIN (EAN)	4008190078508	
Qty.	20 pc(s).	
Type	TW 4 SAK4-10 BL	Version
Order No.	<a href="#">0130180000</a>	SAK Series, Partition plate, 1.5 mm, blue
GTIN (EAN)	4008190114138	
Qty.	20 pc(s).	
Type	TSCH 4 AKZ4	Version
Order No.	<a href="#">0363360000</a>	SAK Series, Small partition, beige, 6 mm
GTIN (EAN)	4008190136680	
Qty.	100 pc(s).	
Type	TSCH 1	Version
Order No.	<a href="#">0319160000</a>	SAK Series, Small partition, beige, 2 mm
GTIN (EAN)	4008190097219	
Qty.	100 pc(s).	

## NT 6/35 10X3 KRG/BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	TSCH 6 DKI S4	Version
Order No.	<a href="#">0190260000</a>	SAK Series, Small partition, beige, 5 mm
GTIN (EAN)	4008190051075	
Qty.	100 pc(s).	

## Steel



Steel bus bars, together with stainless steel, have the highest strength among metallic busbars and are used in applications where short-circuit resistance plays only a secondary role.

## General ordering data

Type	ESCH 1 M	Version
Order No.	<a href="#">0280300000</a>	Accessories, Busbar, Steel
GTIN (EAN)	4008190143053	
Qty.	10 m	

## Copper



Of all the metals used, copper has the best electrical conductivity, which results in the highest short-circuit resistance. This makes the copper busbar the most widely used variant.

## General ordering data

Type	SSCH 7.3X1.2X1000	Version
Order No.	<a href="#">1071200000</a>	Accessories, Busbar, Copper
GTIN (EAN)	4008190279172	
Qty.	1 m	
Type	SSCH 15X6X1000 CU/SN	Version
Order No.	<a href="#">0357400000</a>	Accessories, Busbar, Copper
GTIN (EAN)	4008190169572	
Qty.	1 m	
Type	SSCH 10X3X1000 CU/SN	Version
Order No.	<a href="#">0348900000</a>	Accessories, Busbar, Copper
GTIN (EAN)	4008190024802	
Qty.	1 m	

## NT 6/35 10X3 KRG/BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	SSCH 6X6X1000 CU/SN	Version
Order No.	<a href="#">0571300000</a>	Accessories, Busbar, Copper
GTIN (EAN)	4008190015039	
Qty.	1 m	

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/6.5 MC NE WS	Version
Order No.	<a href="#">1609840000</a>	Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50
GTIN (EAN)	4008190203429	Weidmueller, white
Qty.	900 pc(s).	

## Insulated



Bus bar taps with insulation offer finger safety on the one hand. On the other hand, the colored insulation also indicates the respective potential, such as the neutral conductor or PE.

## General ordering data

Type	ZBE 6K SW	Version
Order No.	<a href="#">0525910000</a>	Accessories, Clamping yoke for busbar, Rated cross-section: Clamping yoke, PA, black, Busbar, Direct mounting
GTIN (EAN)	4008190977054	
Qty.	50 pc(s).	
Type	ZB 4/6K BL	Version
Order No.	<a href="#">0565480000</a>	Accessories, Clamping yoke for busbar, Rated cross-section: Clamping yoke, PA, blue, Feed-through (bushing)
GTIN (EAN)	4008190086831	
Qty.	50 pc(s).	

Creation date March 29, 2024 6:16:46 AM CET

## NT 6/35 10X3 KRG/BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	ZB 35K BL M6X16	Version
Order No.	<a href="#">0502680000</a>	Accessories, Clamping yoke for busbar, Rated cross-section: 35 mm <sup>2</sup> ,
GTIN (EAN)	4008190004385	Clamping yoke, PA, blue, Feed-through (bushing)
Qty.	20 pc(s).	
Type	ZB 4K SW	Version
Order No.	<a href="#">0475310000</a>	Accessories, Clamping yoke for busbar, Rated cross-section: Clamping
GTIN (EAN)	4008190008406	yoke, PA, Feed-through (bushing)
Qty.	50 pc(s).	
Type	ZB 4G BL	Version
Order No.	<a href="#">0322180000</a>	Accessories, Clamping yoke for busbar, Rated cross-section: Clamping
GTIN (EAN)	4008190050504	yoke, PA, blue, Feed-through (bushing)
Qty.	50 pc(s).	
Type	ZB 35K SW M6X16	Version
Order No.	<a href="#">0502610000</a>	Accessories, Clamping yoke for busbar, Rated cross-section: Clamping
GTIN (EAN)	4008190332587	yoke, PA, black, Feed-through (bushing)
Qty.	20 pc(s).	
Type	ZB 16K BL	Version
Order No.	<a href="#">0502880000</a>	Accessories, Clamping yoke for busbar, Rated cross-section: Clamping
GTIN (EAN)	4008190014186	yoke, PA, blue, Feed-through (bushing)
Qty.	50 pc(s).	
Type	ZBE 6K BL	Version
Order No.	<a href="#">0525980000</a>	Accessories, Clamping yoke for busbar, Rated cross-section: 6 mm <sup>2</sup> ,
GTIN (EAN)	4008190060886	Clamping yoke, PA, blue, Busbar, Direct mounting
Qty.	50 pc(s).	
Type	ZB 4K GE/GN	Version
Order No.	<a href="#">0475360000</a>	Accessories, Clamping yoke for busbar, Rated cross-section: Clamping
GTIN (EAN)	4008190188047	yoke, PA, Green/yellow, Feed-through (bushing)
Qty.	50 pc(s).	
Type	ZB 4K GG HENSEL	Version
Order No.	<a href="#">1824560000</a>	Accessories, Clamping yoke for busbar, Rated cross-section: Clamping
GTIN (EAN)	4032248330973	yoke, PA, Green/yellow, Feed-through (bushing)
Qty.	50 pc(s).	
Type	ZB 4K BL	Version
Order No.	<a href="#">0475380000</a>	Accessories, Clamping yoke for busbar, Rated cross-section: 4 mm <sup>2</sup> ,
GTIN (EAN)	4008190010942	Clamping yoke, PA, blue, Feed-through (bushing)
Qty.	50 pc(s).	
Type	ZB 4G GN/GE	Version
Order No.	<a href="#">0322160000</a>	Accessories, Clamping yoke for busbar, Rated cross-section: Clamping
GTIN (EAN)	4008190014278	yoke, PA, Green/yellow, Feed-through (bushing)
Qty.	50 pc(s).	
Type	ZB 4G SW	Version
Order No.	<a href="#">0322110000</a>	Accessories, Clamping yoke for busbar, Rated cross-section: Clamping
GTIN (EAN)	4008190189310	yoke, PA, black, Feed-through (bushing)
Qty.	50 pc(s).	
Type	ZB 16K SW	Version
Order No.	<a href="#">0502810000</a>	Accessories, Clamping yoke for busbar, Rated cross-section: Clamping
GTIN (EAN)	4008190332563	yoke, PA, black, Feed-through (bushing)
Qty.	50 pc(s).	
Type	ZBE 6K GE/GN	Version
Order No.	<a href="#">0525960000</a>	Accessories, Clamping yoke for busbar, Rated cross-section: Clamping
GTIN (EAN)	4008190145026	yoke, PA, Green/yellow, Busbar, Direct mounting
Qty.	50 pc(s).	

## NT 6/35 10X3 KRG/BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold


Germany

www.weidmueller.com

## Accessories

Type	ZB 35K GE/GN M6X16	Version
Order No.	<a href="#">0502660000</a>	Accessories, Clamping yoke for busbar, Rated cross-section: Clamping
GTIN (EAN)	4008190052294	yoke, PA, Green/yellow, Feed-through (bushing)
Qty.	20 pc(s).	
Type	ZB 16K GE/GN	Version
Order No.	<a href="#">0502860000</a>	Accessories, Clamping yoke for busbar, Rated cross-section: Clamping
GTIN (EAN)	4008190188795	yoke, PA, Green/yellow, Feed-through (bushing)
Qty.	50 pc(s).	
Type	ZB 4/6K GE/GN	Version
Order No.	<a href="#">0565460000</a>	Accessories, Clamping yoke for busbar, Rated cross-section: Clamping
GTIN (EAN)	4008190032609	yoke, PA, Green/yellow, Feed-through (bushing)
Qty.	50 pc(s).	

## Test plugs



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

## General ordering data

Type	FZS 2/4 RT/80 SAKT4	Version
Order No.	<a href="#">1276300000</a>	Accessories, Adapter plug
GTIN (EAN)	4008190026080	
Qty.	20 pc(s).	
Type	PS 4 F.STB 4	Version
Order No.	<a href="#">0299600000</a>	Accessories, Test plug
GTIN (EAN)	4008190074043	
Qty.	20 pc(s).	
Type	ZS 2.3/4	Version
Order No.	<a href="#">0249600000</a>	Accessories, Adapter plug
GTIN (EAN)	4008190022785	
Qty.	20 pc(s).	
Type	PS 2.0 OR	Version
Order No.	<a href="#">0293800000</a>	Accessories, Test plug
GTIN (EAN)	4008190042356	
Qty.	20 pc(s).	
Type	PS 2.3 RT	Version
Order No.	<a href="#">0180400000</a>	Accessories, Test plug
GTIN (EAN)	4008190060121	
Qty.	20 pc(s).	



## NT 6/35 10X3 KRG/BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Uninsulated



Uninsulated bus bar tap-off terminals offer a space-saving option for connecting conductors on a bus bar.

## General ordering data

Type	ZB 4	Version
Order No.	<a href="#">0316500000</a>	Accessories, Clamping yoke for busbar, Rated cross-section: Clamping
GTIN (EAN)	4008190061999	yoke, Feed-through (bushing)
Qty.	50 pc(s).	
Type	ZB 4/6	Version
Order No.	<a href="#">0556700000</a>	Accessories, Clamping yoke for busbar, Rated cross-section: Clamping
GTIN (EAN)	4008190188412	yoke, Feed-through (bushing)
Qty.	50 pc(s).	
Type	ZB 35/M6X16	Version
Order No.	<a href="#">0266500000</a>	Accessories, Clamping yoke for busbar, Rated cross-section: Clamping
GTIN (EAN)	4008190102814	yoke, Feed-through (bushing)
Qty.	20 pc(s).	
Type	ZBE 6	Version
Order No.	<a href="#">0459500000</a>	Accessories, Clamping yoke for busbar, Rated cross-section: Clamping
GTIN (EAN)	4008190032692	yoke, Busbar, Direct mounting
Qty.	50 pc(s).	
Type	ZB 16 ZKSC	Version
Order No.	<a href="#">0316600000</a>	Accessories, Clamping yoke for busbar, Rated cross-section: Clamping
GTIN (EAN)	4008190145989	yoke, Feed-through (bushing)
Qty.	50 pc(s).	

## NT 6/35 10X3 KRG/BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/8 MC NE WS	Version
Order No.	<a href="#">1856740000</a>	Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00
GTIN (EAN)	4032248400850	Weidmueller, white
Qty.	800 pc(s).	

## Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/6.5 MC SDR	Version
Order No.	<a href="#">1609850000</a>	Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50
GTIN (EAN)	4008190456610	Weidmueller, To customer specification
Qty.	180 pc(s).	

## NT 6/35 10X3 KRG/BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## SAK-Series



Warning covers with a flash symbol provide more safety for man and machine. They are used where external voltage must be indicated within the application.

## General ordering data

Type	AD 4 SAK6N	Version
Order No.	<a href="#">0196600000</a>	SAK Series, cover plate, yellow, 31.6 mm
GTIN (EAN)	4008190169336	
Qty.	50 pc(s).	

## Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/5 MC SDR	Version
Order No.	<a href="#">1609810000</a>	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00
GTIN (EAN)	4008190456597	Weidmueller, To customer specification
Qty.	200 pc(s).	