

KLIPPON POK 252512 EX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

| | |
|---------------|--|
| Version | Klippon POK (polyester empty enclosure), Empty enclosure, Height: 250 mm, Width: 255 mm, Depth: 120 mm, Material: Glass fibre-reinforced polyester, untreated, polished, black |
| Order No. | 1306120000 |
| Type | KLIPPON POK 252512 EX |
| GTIN (EAN) | 4050118108491 |
| Qty. | 1 pc(s). |
| Required tool | 9008540000 |

KLIPPON POK 252512 EX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|----------------------------|-------------|-----------------------------|------------|
| Depth | 120 mm | Depth (inches) | 4.724 inch |
| Height | 250 mm | Height (inches) | 9.842 inch |
| Height of lowest version | 120 mm | Width | 255 mm |
| Width (inches) | 10.039 inch | Mounting dimension - height | 200 mm |
| Mounting dimension - width | 235 mm | Net weight | 2,841 g |

Temperatures

| | |
|-----------------------|------------------|
| Operating temperature | -55 °C... 100 °C |
|-----------------------|------------------|

Cable glands, left

| | | | |
|-----|----|-----|----|
| M12 | 32 | M16 | 21 |
| M20 | 15 | M25 | 8 |
| M32 | 3 | M40 | 3 |
| M50 | 2 | | |

Cable glands, right

| | | | |
|-----|----|-----|----|
| M12 | 32 | M16 | 21 |
| M20 | 15 | M25 | 8 |
| M32 | 3 | M40 | 3 |
| M50 | 2 | | |

Cable glands, top/bottom

| | | | |
|-----|----|-----|----|
| M12 | 36 | M16 | 32 |
| M20 | 10 | M25 | 10 |
| M32 | 8 | M40 | 3 |
| M50 | 2 | | |

Certificate numbers enclosure

| | | | |
|---|---|--|---------------------------|
| Approval conditions | ATEX, DNV, IECEX, LR, RMRS, UL AEx Class Div., UL AEx Class Zone, cULus, KC, CCC, INMETRO | Attestation of Conformatiy No. (AoC) | DE PS2600 160308 001ISS01 |
| Certificate No. (ATEX) | IBEXU13ATEX1003U | Certificate No. (DNV) | TAE00002R2 |
| Certificate No. (IECEX) | IECEXIBE13.0003U | Certificate no. (cULus) | E256877 |
| Certificate no. Terminal Box (AEx) | E223792 | Certificate no. Terminal Box (ATEX) | IBEXU13ATEX1004 X |
| Certificate no. Terminal Box (IECEX) | IECEX IBE 13.0004X | Certificate no. Terminal Box (INMETRO) | LMP 21.0021X |
| Certificate no. Terminal Box (KOSHA) | 16-AV4BO-0246X | Certificate no. empty enclosure (AEx) | E223792 |
| Certificate no. empty enclosure (ATEX) | IBEXU13ATEX1003 U | Certificate no. empty enclosure (IECEX) | IECEX IBE 13.0003U |
| Certificate no. empty enclosure (INMETRO) | LMP 23.0528U | Declaration of Conformatiy No. (DoC LVD) | DE_PS2600_160412_001ISS01 |

KLIPPON POK 252512 EX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

General information

| | | | |
|---------------------------------|---|-----------------------------|---|
| Access opening: height | 238.02 mm | Access opening: width | 243.02 mm |
| Areas of use | Explosive risk zone, Harbour facilities, Machine construction, Process industry, Transportation | Enclosure attachment | Installation through the housing rear wall, Fixing lugs |
| Flange plate | No | Impact resistance | 7 J ATEX version |
| Lid | Yes | Lid attachment | Slotted/Phillips screws |
| Material | Glass fibre-reinforced polyester | Material thickness of cover | 5 mm |
| Material thickness of enclosure | 5.99 mm | Number of lid screws | 4 |
| Operating temperature, max. | 100 °C | Operating temperature, min. | -55 °C |
| Protection class (UL) | Type 4, Type 4X | Protection degree | IP66 |
| Seal material | Silicone | Standards | DIN EN 62208 - Empty enclosure standard, IEC 60079-0, IEC 60079-7, IEC 60079-31 |
| Surface finish | untreated, polished | Torque for lid screws | 2.5 Nm |
| UL 94 flammability rating | V-0 | | |

horizontal assembly

| | | | |
|-----------------------------|------|-----------------|------|
| WDU 10 / ZDU 10 | 2x19 | WDU 16 / ZDU 16 | 2x15 |
| WDU 2,5 / ZDU 2,5 / IDU 2,5 | 2x38 | WDU 4 / ZDU 4 | 2x31 |
| WDU 6 / ZDU 6 | 2x23 | | |

vertical assembly

| | | | |
|-----------------------------|---|---------------|---|
| WDU 2,5 / ZDU 2,5 / IDU 2,5 | * | WDU 4 / ZDU 4 | * |
|-----------------------------|---|---------------|---|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002503 | ETIM 7.0 | EC002503 |
| ETIM 8.0 | EC002503 | ETIM 9.0 | EC002503 |
| ECLASS 9.0 | 27-18-05-02 | ECLASS 9.1 | 27-18-05-02 |
| ECLASS 10.0 | 27-18-05-02 | ECLASS 11.0 | 27-18-05-02 |
| ECLASS 12.0 | 27-18-05-02 | ECLASS 13.0 | 27-18-05-02 |

Environmental Product Compliance

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | afb385d0-c52b-4449-8502-203596817ab0 |

KLIPPON POK 252512 EX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

Approvals



| | |
|-------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E256877 |

Downloads


| | |
|---|--|
| Approval/Certificate/Document of Conformity | CCC 2020322303002628 POK Assembly Enclosure UKCA TÜV 22 UKEX 7093 X UKCA TÜV 22 UKEX 7092 U Attestation of Conformity - KlippON POK Empty Enclosures - AoC DE PS2600 160308 001ISS03 14 20001 TAE00002R2 IECEXIBE13.0004X 16-AV4BO-246X IBEXU13ATEX1003U IBEXU13ATEX1004X IECEXIBE13.0003U INMETRO CERTIFICADO LMP 2.1.0021X KLIPPON POK EU Declaration of Conformity - KlippON POK Empty Enclosures Ex - DoC DE PS2600 160412 001ISS02 |
| Engineering Data | CAD data – STEP |
| Tender specification | KlippON POK 252512 Ex_1306120000_DE KlippON POK 252512 Ex_1306120000_EN |
| Catalogues | Catalogues in PDF-format |
| Brochures | MB OVERV. PROCESS WD DE MB KLIPPON ENCL.TECN EN MB PROCESS EN FL KLIPPON POK EN FL SHIPBUILDING 2016 EN FL SHIPBUILDING 2016 EN |

KLIPPON POK 252512 EX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



KLIPPON POK 252512 EX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Depth 15 mm**

The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
-
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | TS35X15 ST POK 2525 | Version |
| Order No. | 8000073214 | Rail, TS 35, TS 35 x 15, with slot, Steel, galvanic zinc plated and |
| GTIN (EAN) | 4064675356714 | passivated |
| Qty. | 20 pc(s). | |

KLIPPON POK 252512 EX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Klippon® POK standard mounting plates**

The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

| Type | POK MOPL 2525 | Version |
|------------|----------------------------|--|
| Order No. | 9510640000 | Klippon POK (polyester empty enclosure), Mounting plate, Height: |
| GTIN (EAN) | 4008190498283 | 233 mm, Width: 238 mm, Depth: 1.5 mm, Material: Sheet steel, |
| Qty. | 1 pc(s). | galvanized, Miscellaneous, silver |

KLIPPON POK 252512 EX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Klippon® POK mounting plates in combination with earthing plates



The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

| Type | POK MOPL 2525 MINI | Version |
|------------|----------------------------|--|
| Order No. | 1534410000 | Klippon POK (polyester empty enclosure), Mounting plate, Height: |
| GTIN (EAN) | 4050118338232 | 203 mm, Width: 238 mm, Depth: 1.5 mm, Material: Sheet steel, |
| Qty. | 1 pc(s). | galvanized, galvanized, silver |

KLIPPON POK 252512 EX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Klippon® POK earthing plates



The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | KLIPPON COPL 252512/16 | Version |
| Order No. | 1391030000 | Klippon POK (polyester empty enclosure), Earthing plate, |
| GTIN (EAN) | 4050118191219 | Miscellaneous, Height: 85.5 mm, Width: 424 mm, Depth: 0.8 mm, |
| Qty. | 5 pc(s). | Material: Brass, polished, untreated |

KLIPPON POK 252512 EX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Klippon® POK installation material



The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

| Type | TPSD FIXING SET POK | Version |
|------------|----------------------------|--|
| Order No. | 1435840000 | Klippon POK (polyester empty enclosure), Type plate fixings set, |
| GTIN (EAN) | 4050118240771 | Height: 12 mm, Width: 12 mm, Depth: 15.06 mm, Material: Stainless |
| Qty. | 1 pc(s). | steel, rust-proof, untreated |
| Type | SD FIXING SET POK | Version |
| Order No. | 1463490000 | Klippon POK (polyester empty enclosure), Identification plate fixing |
| GTIN (EAN) | 4050118299878 | set, Height: 12 mm, Width: 12 mm, Depth: 16.4 mm, Material: |
| Qty. | 1 pc(s). | Stainless steel 1.4305 (303), untreated |

KLIPPON POK 252512 EX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Depth 7.5 mm



The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | TS35X7.5 ST POK 2525 | Version |
| Order No. | 8000003912 | Rail, TS 35, TS 35 x 7.5, Width: 239 mm, without slot, Steel, galvanic |
| GTIN (EAN) | 4050118652727 | zinc plated and passivated |
| Qty. | 80 pc(s). | |

Spacer



Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new

Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Spacer

Stainless steel spacers in four lengths to increase the distance between the mounting rails or DIN rails and the rear wall of the enclosure.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | SP M6 10 S2 | Version |
| Order No. | 0935110000 | Klippon TB (Terminal Box), Spacer, Height: 11.2 mm, Width: 10 mm, |
| GTIN (EAN) | 4032248699049 | Depth: 10 mm, Material: Stainless steel 1.4305 (303) |
| Qty. | 4 pc(s). | |

KLIPPON POK 252512 EX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|---|
| Type | SP M6 15 S2 | Version |
| Order No. | 0935120000 | Klippon TB (Terminal Box), Spacer, Height: 11.2 mm, Width: 10 mm, |
| GTIN (EAN) | 4032248699056 | Depth: 15 mm, Material: Stainless steel 1.4305 (303) |
| Qty. | 4 pc(s). | |
| Type | SP M6 20 S2 | Version |
| Order No. | 0935130000 | Klippon TB (Terminal Box), Spacer, Height: 11.2 mm, Width: 10 mm, |
| GTIN (EAN) | 4032248699001 | Depth: 20 mm, Material: Stainless steel 1.4305 (303) |
| Qty. | 4 pc(s). | |
| Type | SP M6 30 S2 | Version |
| Order No. | 0935140000 | Klippon TB (Terminal Box), Spacer, Height: 11.2 mm, Width: 10 mm, |
| GTIN (EAN) | 4032248699117 | Depth: 30 mm, Material: Stainless steel 1.4305 (303) |
| Qty. | 4 pc(s). | |

Installation material

**Integrate, expand and customise - the perfect supplement to every application**

The fully structured range of system accessories for the new Klippon® TB enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

Mounting hardware kits

Mounting hardware kits are available for quick and easy installation of type label holders, document holders and rain hoods.

The **label fastening set – SD** is required to install a plastic (Trafolyte) ID or type label. With the aid of this set can you mount the ID or type label directly on the enclosure cover. The label fastening set has been specially developed for this purpose. Only by using this fastening set can you ensure that there will be no leaks into the enclosure or damage to the label.

The **universal fastening set – TPSD** has been developed to enable secure and quick installation of type label holders, rain covers or document holders, for example. By using this fastening set, the risk of leaks can be minimised, if not avoided.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | FKSC M6X8 D9/SW3 | Version |
| Order No. | 0642600000 | Klippon TB (Terminal Box), Mounting screw, Material: Steel |
| GTIN (EAN) | 4008190058258 | |
| Qty. | 50 pc(s). | |

KLIPPON POK 252512 EX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Klippon® POK mounting feet



The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

| Type | MF POK BIG | Version |
|------------|----------------------------|--|
| Order No. | 9510910000 | Klippon POK (polyester empty enclosure), Mounting foot, Fixing lugs, |
| GTIN (EAN) | 4032248009756 | Height: 16 mm, Width: 51 mm, Depth: 6 mm, Material: Stainless steel |
| Qty. | 1 pc(s). | 1.4301, Miscellaneous |

KLIPPON POK 252512 EX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Klippon® POK earthing stud



The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | PEBZ M10 BR SET | Version |
| Order No. | 1277220000 | Klippon POK (polyester empty enclosure), Earthing stud, |
| GTIN (EAN) | 4050118067019 | Miscellaneous, Height: 21 mm, Width: 21 mm, Depth: 48.7 mm, |
| Qty. | 1 pc(s). | Material: Brass |
| Type | PEBZ M6 S4 SET | Version |
| Order No. | 1283430000 | Klippon POK (polyester empty enclosure), Earthing stud, |
| GTIN (EAN) | 4050118073607 | Miscellaneous, Height: 12.3 mm, Width: 12.3 mm, Depth: 42 mm, |
| Qty. | 1 pc(s). | Material: Stainless steel 1.4404 (316L) |
| Type | PEBZ M6 BR SET | Version |
| Order No. | 1277250000 | Klippon POK (polyester empty enclosure), Earthing stud, |
| GTIN (EAN) | 4050118067149 | Miscellaneous, Height: 12.3 mm, Width: 12.3 mm, Depth: 42 mm, |
| Qty. | 1 pc(s). | Material: Brass |
| Type | PEBZ M10 S4 SET | Version |
| Order No. | 1283440000 | Klippon POK (polyester empty enclosure), Earthing stud, |
| GTIN (EAN) | 4050118073362 | Miscellaneous, Height: 21 mm, Width: 21 mm, Depth: 48.7 mm, |
| Qty. | 1 pc(s). | Material: Stainless steel 1.4404 (316L) |

KLIPPON POK 252512 EX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Spacer**

Stainless steel spacers in three lengths to increase the distance between the mounting rails or DIN rails and the rear wall of the enclosure.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | SP M6 20 MSZN | Version |
| Order No. | 3896200000 | Klippon EB (Essential Box), Spacer, Height: 11.2 mm, Width: 10 mm, |
| GTIN (EAN) | 4008190850234 | Depth: 20 mm, Material: Steel, silver |
| Qty. | 2 pc(s). | |
| Type | SP M6 15 MSZN | Version |
| Order No. | 3896100000 | Klippon EB (Essential Box), Spacer, Height: 11.2 mm, Width: 10 mm, |
| GTIN (EAN) | 4008190857851 | Depth: 15 mm, Material: Steel, silver |
| Qty. | 2 pc(s). | |
| Type | SP M6 30 MSZN | Version |
| Order No. | 3896300000 | Klippon EB (Essential Box), Spacer, Height: 11.2 mm, Width: 10 mm, |
| GTIN (EAN) | 4008190850241 | Depth: 30 mm, Material: Steel, silver |
| Qty. | 2 pc(s). | |