

**HDC 24D TSBO 1M25G****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**IP65**

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

**General ordering data**

|            |   |
|------------|---|
| Version    | HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on upper side, high, Size of cable entries: M 25 |
| Order No.  | <a href="#">1787260000</a>  |
| Type       | HDC 24D TSBO 1M25G  |
| GTIN (EAN) | 4032248204601   |
| Qty.       | 1 pc(s).  |

**HDC 24D TSBO 1M25G****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |       |                 |            |
|------------|-------|-----------------|------------|
| Height     | 72 mm | Height (inches) | 2.835 inch |
| Width      | 55 mm | Width (inches)  | 2.165 inch |
| Net weight | 250 g |                 |            |

**Temperatures**

|                   |                   |
|-------------------|-------------------|
| Limit temperature | -40 °C ... 125 °C |
|-------------------|-------------------|

**Dimensions**

|                      |           |                     |       |
|----------------------|-----------|---------------------|-------|
| Cable entry          | w. thread | Height of housing B | 72 mm |
| Total length housing | 73 mm     | Width housing C     | 43 mm |

**General data**

|                             |                             |                       |                             |
|-----------------------------|-----------------------------|-----------------------|-----------------------------|
| EMC housings                | No                          | Housing main material | diecast aluminium           |
| Material of locking element |                             | Protection degree     | IP65 (in plugged condition) |
| Surface finish              | Stainless steel, rust-proof |                       |                             |
|                             | Powder coating              |                       |                             |

**Version**

|                              |                                  |                                |                                     |
|------------------------------|----------------------------------|--------------------------------|-------------------------------------|
| BG                           | 4                                | Cable entry                    | w. thread                           |
| Clamp version                | Side-locking clamp               | Colour (RAL)                   | RAL 7035                            |
| Design                       |                                  | Design of housing              | Cable entry from side, Plug housing |
|                              | high                             |                                |                                     |
| Design of locking system     | Side-locking clamp on upper side | Internal thread                | M 25                                |
| Number of cable entry on top | 0                                | Number of cable entry sideways | 1                                   |
| Size                         | 4                                | Size of cable entries          | M 25                                |
| Suitable for ModuPlug®       | Yes                              | Top part/bottom part/lid       | upper part                          |
| Type                         | Plug                             |                                |                                     |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000437    | ETIM 7.0    | EC000437    |
| ETIM 8.0    | EC000437    | ETIM 9.0    | EC000437    |
| ECLASS 9.0  | 27-44-02-02 | ECLASS 9.1  | 27-44-02-02 |
| ECLASS 10.0 | 27-44-02-02 | ECLASS 11.0 | 27-44-02-02 |
| ECLASS 12.0 | 27-44-02-02 | ECLASS 13.0 | 27-44-02-02 |

|                     |                         |
|---------------------|-------------------------|
| Substance           | Acetone                 |
| Chemical resistance | Conditionally resistant |
| Substance           | Drilling oil            |
| Chemical resistance | Resistant               |
| Substance           | Diesel                  |
| Chemical resistance | Resistant               |
| Substance           | Ethyl alcohol           |
| Chemical resistance | Resistant               |
| Substance           | Transmission oil        |
| Chemical resistance | Resistant               |

Creation date July 25, 2024 2:24:59 AM CEST

## HDC 24D TSBO 1M25G

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

|                     |                         |
|---------------------|-------------------------|
| Substance           | Hydraulic oil           |
| Chemical resistance | Resistant               |
| Substance           | Coolant                 |
| Chemical resistance | Resistant               |
| Substance           | Petroleum benzine       |
| Chemical resistance | Resistant               |
| Substance           | Sweat                   |
| Chemical resistance | Resistant               |
| Substance           | Premium gasoline        |
| Chemical resistance | Conditionally resistant |
| Substance           | Water                   |
| Chemical resistance | Resistant               |
| Substance           | UV                      |
| Chemical resistance | Unstable                |
| Substance           | Ozone                   |
| Chemical resistance | Unstable                |

## Environmental Product Compliance

|                                      |  |
|--------------------------------------|--|
| REACH SVHC                           | Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3  |
| SCIP                                 | e98b2b24-ba23-41bf-8d19-Odda3647412f   |
| Chemical resistance                  | de.myview.objectmodel.impl.BlockImpl@316dca15 de.myview.objectmodel.impl.BlockImpl@1e9fc2dc<br>de.myview.objectmodel.impl.BlockImpl@ce17d8 de.myview.objectmodel.impl.BlockImpl@4d1679f0<br>de.myview.objectmodel.impl.BlockImpl@12743f25 de.myview.objectmodel.impl.BlockImpl@729d8695<br>de.myview.objectmodel.impl.BlockImpl@29d3fc9 de.myview.objectmodel.impl.BlockImpl@7c3a0f93<br>de.myview.objectmodel.impl.BlockImpl@4f848a26 de.myview.objectmodel.impl.BlockImpl@5133146d<br>de.myview.objectmodel.impl.BlockImpl@3a3b1af5 de.myview.objectmodel.impl.BlockImpl@1651dcb6<br>de.myview.objectmodel.impl.BlockImpl@7d6fa1e0 |
| RoHS Compliance Status               | Compliant with exemption   |
| RoHS Exemption (if applicable/known) | 6bl  |

## Approvals

Approvals



|                         |            |
|-------------------------|------------|
| ROHS                    | Conform    |
| UL File Number Search   | UL Website |
| Certificate No. (cURus) | E92202     |

## HDC 24D TSBO 1M25G

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Approval/Certificate/Document of Con-  
formity

[Manufacturer's declaration](#)

Engineering Data

[CAD data – STEP](#)

Product Change Notification

[20220214 Technical change to HDC housings](#)  
[20220214 Technische Änderung bei HDC-Gehäusen](#)

Technical Documentation

[1787260000 HDC\\_24D\\_TSBO\\_1M25G\\_STP\\_Blatt\\_1.pdf](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures


[FL FIELDWIRING EN](#)  
[FL FIELDWIRING EN](#)

### HDC 24D TSBO 1M25G

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



**HDC 24D TSBO 1M25G****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Cover**

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

**General ordering data**

|            |                            |  |
|------------|----------------------------|--|
| Type       | HDC 10B DMDQ 4BO           | Version  |
| Order No.  | <a href="#">1665250000</a> | HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cover for upper part of housing, Side-locking clamp on upper side, Standard |
| GTIN (EAN) | 4008190421953              |  |
| Qty.       | 1 pc(s).                   |  |