

RF RS 70 MI/A6 OR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The RS 70 profile is supplied in fixed lengths. The desired length is obtained by connecting the individual pieces together. The PCB is pushed into the side of the profile. End cover plates close off the sides of the profile.. Elements for terminal rails and direct mounting are available here. The clip-on feet are permanently attached to the profile. Marking options are integrated into the side pieces.

General ordering data

| | |
|------------|---|
| Version | Clip-in foot, RS 70 orange, Intermediate part, Clip-in foot, Width: 10 mm |
| Order No. | 0213760000 |
| Type | RF RS 70 MI/A6 OR |
| GTIN (EAN) | 4008190148850 |
| Qty. | 20 pc(s). |

RF RS 70 MI/A6 OR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|--------------------------|------------|-----------------|------------|
| Depth | 28.6 mm | Depth (inches) | 1.126 inch |
| Height | 70 mm | Height (inches) | 2.756 inch |
| Height of lowest version | 32 mm | Width | 10 mm |
| Width (inches) | 0.394 inch | Net weight | 4.8 g |

Material data

| | | | |
|----------------------------------|-----------|---------------------|-------|
| Comparative Tracking Index (CTI) | 600 ≤ CTI | Insulating material | PA 66 |
| UL 94 flammability rating | V-2 | | |

General data

| | | | |
|----------------------|--------------|------------------------|----------|
| Colour | orange | Colour chart (similar) | RAL 2000 |
| Encapsulation option | No | Protection degree | IP00 |
| Rail | TS 32, TS 35 | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 7.0 | EC002779 | ETIM 8.0 | EC002779 |
| ETIM 9.0 | EC002779 | ECLASS 11.0 | 27-18-27-92 |
| ECLASS 12.0 | 27-18-27-92 | ECLASS 13.0 | 27-19-06-04 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|---|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |
| Brochures | FL ANALO.SIGN.CONV. EN MB DEVICE MANUF. EN FL MACHINE SAFETY EN FL 72H SAMPLE SER EN PO OMNIMATE EN PO OMNIMATE EN |

RF RS 70 MI/A6 OR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

LOCKING-FOOT MIDDLE

