# AP SAK95 KRG/BL

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Product image



Similar to illustration

End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

### General ordering data

| | |
|---|---|
| Version | SAK Series, End plate, 3 mm, blue, Direct mounting |
| Order No. | 0550970000 |
| Type | AP SAK95 KRG/BL |
| GTIN (EAN) | 4008190087968 |
| Qty. | 10 pc(s). |
| Delivery status | Discontinued |
| Available until | 2020-12-31 |

# AP SAK95 KRG/BL

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

| | | | |
|---|---|---|---|
| Depth | 84 mm | Depth (inches) | 3.307 inch |
| Height | 83.5 mm | Height (inches) | 3.287 inch |
| Width | 3 mm | Width (inches) | 0.118 inch |
| Net weight | 30.4 g | | |

### Temperatures

| | | | |
|---|---|---|---|
| Storage temperature | -25 °C...55 °C | Continuous operating temp., min. | -60 °C |
| Continuous operating temp., max. | 130 °C | | |

### Material data

| | | | |
|---|---|---|---|
| Material | KrG | Colour | blue |
| UL 94 flammability rating | V-0 | | |

### System specifications

| | |
|---|---|
| Version | End plate |

### Additional technical data

| | | | |
|---|---|---|---|
| Installation advice | Direct mounting | Snap-on | Yes |

### General

| | |
|---|---|
| Installation advice | Direct mounting |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 6.0 | EC000886 | ETIM 7.0 | EC000886 |
| ETIM 8.0 | EC000886 | ETIM 9.0 | EC000886 |
| ECLASS 9.1 | 27-14-11-33 | ECLASS 10.0 | 27-14-11-33 |
| ECLASS 11.0 | 27-14-11-33 | ECLASS 12.0 | 27-14-11-33 |
| ECLASS 13.0 | 27-25-03-01 | | |

### Approvals

| | |
|---|---|
| ROHS | Conform |

### Downloads

| | |
|---|---|
| User Documentation | StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |