

**SAI-M23-KS-L-7/12****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The M23 round plug-in connectors offer a high number of mating cycles, high current-carrying capacity and high contact-density coupled with minimum dimensions. Enclosures, inserts and crimp contacts need to be ordered separately.

**General ordering data**

Version	Sensor/Actuator plug-in connector, Empty enclosure
Order No.	<a href="#">1170270000</a>
Type	SAI-M23-KS-L-7/12
GTIN (EAN)	4032248962259
Qty.	1 pc(s).

**SAI-M23-KS-L-7/12****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Net weight	82 g
------------	------

**Technical data customisable plug-in connectors**

Cable diameter, max.	12 mm	Cable diameter, min.	7 mm
Housing main material	Copper-zinc alloy	Plugging cycles	> 1000
Pollution severity	3	Protection degree	IP67, IP69K
Shield connection	Yes	Temperature range of housing	-40...+125 °C

**Classifications**

ETIM 6.0	EC000437	ETIM 7.0	EC003556
ETIM 8.0	EC003556	ETIM 9.0	EC003556
ECLASS 9.1	27-44-02-02	ECLASS 10.0	27-44-02-24
ECLASS 11.0	27-44-02-24	ECLASS 12.0	27-44-02-24
ECLASS 13.0	27-44-02-24		

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	1c533b66-fcff-4da5-b89f-fd55fbf5cb55

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E344862

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>


## SAI-M23-KS-L-7/12

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

## Dimensioned drawing



## SAI-M23-KS-L-7/12

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Inserts without contacts



The M23 round plug-in connectors offer a high number of mating cycles, high current-carrying capacity and high contact-density coupled with minimum dimensions. Enclosures, inserts and crimp contacts need to be ordered separately.

## General ordering data

Type	SAI-M23-SE-L-6	Version
Order No.	<a href="#">1170350000</a>	Sensor/Actuator plug-in connector, Insert
GTIN (EAN)	4032248962303	
Qty.	1 pc(s).	
Type	SAI-M23-SE-L-4/4	Version
Order No.	<a href="#">1170380000</a>	Sensor/Actuator plug-in connector, Insert
GTIN (EAN)	4032248962518	
Qty.	1 pc(s).	
Type	SAI-M23-BE-L-4/4	Version
Order No.	<a href="#">1995810000</a>	Sensor/Actuator plug-in connector, Insert
GTIN (EAN)	4032248925674	
Qty.	1 pc(s).	
Type	SAI-M23-BE-L-6	Version
Order No.	<a href="#">1170370000</a>	Sensor/Actuator plug-in connector, Insert
GTIN (EAN)	4032248962266	
Qty.	1 pc(s).	

# Cable connector

