

VGM40/1-SS68 20-32 BG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

| | |
|------------|--|
| Version | Heavy-duty connectors, Accessories, Cable glands, Stainless steel 1.4305 (303) |
| Order No. | 1205920000 |
| Type | VGM40/1-SS68 20-32 BG |
| GTIN (EAN) | 4032248987825 |
| Qty. | 10 pc(s). |

VGM40/1-SS68 20-32 BG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|---------|-----------------|------------|
| Length | 82 mm | Length (inches) | 3.228 inch |
| Net weight | 323.6 g | | |

Temperatures

| | |
|-------------------|-------------------|
| Limit temperature | -40 °C ... 130 °C |
|-------------------|-------------------|

General information

| | | | |
|---------------------------|------------------------------|------------------|-----------------|
| AF size | 45 mm | Cable glands | M 40 |
| External thread | M 40 | Length of thread | 8 mm |
| Material | Stainless steel 1.4305 (303) | O-Ring | Silicone |
| Protection degree | IP68 - 15 bar | Standards | EN 45545-2:2013 |
| UL 94 flammability rating | V-0 | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000441 | ETIM 7.0 | EC000441 |
| ETIM 8.0 | EC000441 | ETIM 9.0 | EC000441 |
| ECLASS 9.0 | 27-14-44-32 | ECLASS 9.1 | 27-14-44-32 |
| ECLASS 10.0 | 27-14-44-32 | ECLASS 11.0 | 27-14-44-32 |
| ECLASS 12.0 | 27-14-08-01 | ECLASS 13.0 | 27-14-08-01 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |
| Brochures | FL FIELDWIRING EN FL FIELDWIRING EN |