

**WIL-NT-STANDARD****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Power supply IP65 for WIL standard family 85V-264V AC  
input, 24V DC output 400mA

**General ordering data**

Order No.	<a href="#">2598350000</a>
Type	WIL-NT-STANDARD
GTIN (EAN)	4050118611168
Qty.	1 pc(s).

## WIL-NT-STANDARD

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	34 mm	Depth (inches)	1.339 inch
Height	32 mm	Height (inches)	1.26 inch
Width	100 mm	Width (inches)	3.937 inch
Net weight	292 g		

## Temperatures

Operating temperature	-30 - 50°C
-----------------------	------------

## Cable technical specifications

Cable Material	TPE	Sheathing colour	black
Cable length	3	Core cross-section	0.75 mm <sup>2</sup>

## Electric data

Rated voltage	24 V DC	Rated current	1,10 A
---------------	---------	---------------	--------

## General technical data

Type of mounting	Screw mounting	Protection degree	IP65 when locked
------------------	----------------	-------------------	------------------

## Material data

Housing main material	PBT	Threaded ring material	Nickel-plated CuZn
-----------------------	-----	------------------------	--------------------

## Power supply / input

Input frequency	47 - 63 Hz	Input fuse (internal)	Yes
Version	Cable end open	Connecting thread	without
Circuitry	Blue -, Black +		

## Power supply / output

Connection system	Screw connection	Output current, max.	0.4 A
Version	Socket connector	Connecting thread	M12
Circuitry	PIN 3: - (blue), PIN 4: + (black)		

## Power supply / safety

Safety standard	SELV according to EN 60950, EN 61347-2-13	Short-circuit protection	Yes
Overload protection	Yes	Protection against over-heating	Yes
Protection class	II	Safety extra-low voltage	Yes

## Classifications

ETIM 6.0	EC002540	ETIM 7.0	EC002540
ETIM 8.0	EC002540	ETIM 9.0	EC002540
ECLASS 9.0	27-04-07-01	ECLASS 9.1	27-04-07-01
ECLASS 10.0	27-04-07-01	ECLASS 11.0	27-04-07-01
ECLASS 12.0	27-04-07-01	ECLASS 13.0	27-04-90-02

## WIL-NT-STANDARD

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

Approvals



ROHS

Conform

### Downloads

Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)

## WIL-NT-STANDARD

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

## Dimensioned drawing

