

**QL 4 SAKS1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

|            |  |
|------------|--|
| Version    | Cross-connector (terminal), when screwed in, Number of poles: 4, Pitch in mm (P): 13.00, Insulated: No, 47 A, grey |
| Order No.  | <a href="#">0191600000</a>   |
| Type       | QL 4 SAKS1   |
| GTIN (EAN) | 4008190105518  |
| Qty.       | 20 pc(s).  |

**QL 4 SAKS1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 2 mm    | Depth (inches)  | 0.079 inch |
| Height     | 6 mm    | Height (inches) | 0.236 inch |
| Width      | 44.7 mm | Width (inches)  | 1.76 inch  |
| Net weight | 3.79 g  |                 |            |

**Temperatures**

|                     |                |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

**Material data**

|          |       |        |      |
|----------|-------|--------|------|
| Material | Cu Zn | Colour | grey |
|----------|-------|--------|------|

**System specifications**

|         |                           |
|---------|---------------------------|
| Version | for cross-connection link |
|---------|---------------------------|

**Additional technical data**

|                          |                 |                     |                 |
|--------------------------|-----------------|---------------------|-----------------|
| Explosion-tested version | No              | Installation advice | Direct mounting |
| Type of fixing           | when screwed in |                     |                 |

**Cross-connector**

|                                     |      |                       |                 |
|-------------------------------------|------|-----------------------|-----------------|
| Number of cross-connected terminals | 4    | Rated current, 2-pole | 47 A            |
| Rated current, multi-pole           | 36 A | Type                  | Cross-connector |

**Dimensions**

|                 |       |
|-----------------|-------|
| Pitch in mm (P) | 13 mm |
|-----------------|-------|

**General**

|                     |                 |                 |   |
|---------------------|-----------------|-----------------|---|
| Installation advice | Direct mounting | Number of poles | 4 |
|---------------------|-----------------|-----------------|---|

**Rating data**

|               |      |
|---------------|------|
| Rated current | 47 A |
|---------------|------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000489    | ETIM 7.0    | EC000489    |
| ETIM 8.0    | EC000489    | ETIM 9.0    | EC000489    |
| ECLASS 9.0  | 27-14-11-40 | ECLASS 9.1  | 27-14-11-40 |
| ECLASS 10.0 | 27-14-11-40 | ECLASS 11.0 | 27-14-11-40 |
| ECLASS 12.0 | 27-14-11-40 | ECLASS 13.0 | 27-25-03-03 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### QL 4 SAKS1

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

User Documentation

[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)

**QL 4 SAKS1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Screws**

Depending on the terminal block or also accessories, we offer different types of screws as additional items or also spare parts.

**General ordering data**

|            |                            |                                      |
|------------|----------------------------|--------------------------------------|
| Type       | KISC M3X6 SAKS1            | Version                              |
| Order No.  | <a href="#">0346200000</a> | Clamping yoke, Mounting screw, Steel |
| GTIN (EAN) | 4008190175658              |                                      |
| Qty.       | 100 pc(s).                 |                                      |