

**QL 4 SAKS1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, grey, 47 A, Number of poles: 4, Pitch in mm (P): 13.00, Insulated: No, Width: 44.7 mm
Order No.	<a href="#">0191600000</a>
Type	QL 4 SAKS1
GTIN (EAN)	4008190105518
Qty.	20 pc(s).

**QL 4 SAKS1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	2 mm	Depth (inches)	0.079 inch
Height	6 mm	Height (inches)	0.236 inch
Width	44.7 mm	Width (inches)	1.76 inch
Net weight	3.79 g		

**Temperatures**

Storage temperature	-25 °C...55 °C
---------------------	----------------

**Material data**

Material	Cu Zn	Colour	grey
----------	-------	--------	------

**System specifications**

Version	for cross-connection link
---------	---------------------------

**Additional technical data**

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

**Cross-connector**

Number of cross-connected terminals	4	Rated current, 2-pole	47 A
Rated current, multi-pole	36 A	Type	Cross-connector

**Dimensions**

Pitch in mm (P)	13 mm
-----------------	-------

**General**

Installation advice	Direct mounting	Number of poles	4
---------------------	-----------------	-----------------	---

**Rating data**

Rated current	47 A
---------------	------

**Classifications**

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

**Environmental Product Compliance**

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

## QL 4 SAKS1

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

ROHS	Conform
------	---------

### Downloads

User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## QL 4 SAKS1

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Screws



Depending on the terminal block or also accessories, we offer different types of screws as additional items or also spare parts.

## General ordering data

Type	KISC M3X6 SAKS1	Version
Order No.	<a href="#">0346200000</a>	Clamping yoke, Mounting screw, Steel
GTIN (EAN)	4008190175658	
Qty.	100 pc(s).	