

CLI C 02-3 GE/SW X MP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

General ordering data

| | |
|------------|--|
| Version | CableLine, Conductor and cable markers, 1.3 - 3 mm, 3 x 3.4 mm, yellow |
| Order No. | 0252111687 |
| Type | CLI C 02-3 GE/SW X MP |
| GTIN (EAN) | 4008190059705 |
| Qty. | 200 pc(s). |

CLI C 02-3 GE/SW X MP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 3.5 mm | Depth (inches) | 0.138 inch |
| Height | 3 mm | Height (inches) | 0.118 inch |
| Width | 3.4 mm | Width (inches) | 0.134 inch |
| Net weight | 0.03 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

General data

| | | |
|--|--|----------------|
| Colour | yellow | |
| Colour of printing | black | |
| Halogen | Yes | |
| Material | PVC, soft, without Cadmium | |
| Material colour according to resistance code | 4 | |
| Number of markers per combination | 1 Component part = Conductor and cable markers | |
| Number of markers per packaging unit | Form of supply | Component part |
| Operating temperature range | -30...80 °C | |
| Operating temperature range, max. | 80 °C | |
| Operating temperature range, min. | -30 °C | |
| Orientation of print | horizontal | |
| Printed characters | Upper-case letters | |
| Printing | X | |
| Printing method | hot-embossing | |
| Recommended industries | Process, Machinery | |
| Type of printing | Standard | |
| UL 94 flammability rating | V-0 | |
| Version | MultiPack | |
| Width | 3.4 mm | |

Conductor and cable markers

| | | | |
|-------------------------------|---------------------|----------------------------------|---------------------------|
| Conductor O.D. | 1.3 - 3 mm | Conductor O.D., max. | 3 mm |
| Conductor O.D., min. | 1.3 mm | Conductor cross-section, max. | 1.5 mm ² |
| Conductor cross-section, min. | 0.2 mm ² | Cross-section for connected wire | 0.2 - 1.5 mm ² |
| Halogen | Yes | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ECLASS 9.0 | 27-40-04-01 | ECLASS 9.1 | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |
| ECLASS 14.0 | 27-28-11-02 | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| REACH SVHC | / |
| RoHS Compliance Status | Compliant without exemption |

CLI C 02-3 GE/SW X MP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|-----------------------------|--|
| Product Change Notification | PCN CableLine_DE PCN CableLine_EN |
| Catalogues | Catalogues in PDF-format |

CLI C 02-3 GE/SW X MP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings



Similar to illustration

CLI C 02-3 GE/SW X MP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Mandrels single



The CableLine range of wire and cable marker products provides users with solutions for the most diverse applications. The range of applications extends from narrow wires right up to cables with large outside diameters.

General ordering data

| | | |
|------------|----------------------------|-----------------------------|
| Type | CLI R 02 F, CLI C 02-3 | Version |
| Order No. | 0559900000 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190081645 | |
| Qty. | 20 pc(s). | |

A - Z



The CableLine range of wire and cable marker products provides users with solutions for the most diverse applications. The range of applications extends from narrow wires right up to cables with large outside diameters.

General ordering data

| | | |
|------------|----------------------------|-----------------------------|
| Type | CLI R 02-3 GE/SW F | Version |
| Order No. | 0560001648 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190989873 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW X | Version |
| Order No. | 0560001693 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190990053 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW W | Version |
| Order No. | 0560001684 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190990046 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW D | Version |
| Order No. | 0560001644 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190989859 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW T | Version |
| Order No. | 0560001678 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190990015 | |
| Qty. | 10 pc(s). | |

CLI C 02-3 GE/SW X MP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|-----------------------------|
| Type | CLI R 02-3 GE/SW S | Version |
| Order No. | 0560001675 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190990008 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW A | Version |
| Order No. | 0560001638 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190989828 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW C | Version |
| Order No. | 0560001642 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190989842 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW I | Version |
| Order No. | 0560001654 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190989903 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW Y | Version |
| Order No. | 0560001697 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190990060 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW J | Version |
| Order No. | 0560001656 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190989910 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW G | Version |
| Order No. | 0560001650 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190989880 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW N | Version |
| Order No. | 0560001664 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190989958 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW K | Version |
| Order No. | 0560001658 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190989927 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW Q | Version |
| Order No. | 0560001670 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190989989 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW B | Version |
| Order No. | 0560001640 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190989835 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW E | Version |
| Order No. | 0560001646 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190989866 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW M | Version |
| Order No. | 0560001662 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190989941 | |
| Qty. | 10 pc(s). | |

Creation date August 25, 2024 4:57:17 AM CEST

Catalogue status 17.08.2024 / We reserve the right to make technical changes.

CLI C 02-3 GE/SW X MP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|-----------------------------|
| Type | CLI R 02-3 GE/SW H | Version |
| Order No. | 0560001652 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190989897 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW U | Version |
| Order No. | 0560001680 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190990022 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW P | Version |
| Order No. | 0560001668 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190989972 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW L | Version |
| Order No. | 0560001660 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190989934 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW V | Version |
| Order No. | 0560001682 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190990039 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW O | Version |
| Order No. | 0560001666 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190989965 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW Z | Version |
| Order No. | 0560001699 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190990077 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW R | Version |
| Order No. | 0560001672 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190989996 | |
| Qty. | 10 pc(s). | |

Special characters



The CableLine range of wire and cable marker products provides users with solutions for the most diverse applications. The range of applications extends from narrow wires right up to cables with large outside diameters.

General ordering data

| | | |
|------------|----------------------------|-----------------------------|
| Type | CLI R 02-3 GE/SW . | Version |
| Order No. | 0560001749 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190990138 | |
| Qty. | 10 pc(s). | |

Creation date August 25, 2024 4:57:17 AM CEST

Catalogue status 17.08.2024 / We reserve the right to make technical changes.

CLI C 02-3 GE/SW X MP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|-----------------------------|
| Type | CLI R 02-3 GE/SW + | Version |
| Order No. | 0560001738 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190990084 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW - | Version |
| Order No. | 0560001740 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190990091 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW ET | Version |
| Order No. | 0560001745 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190990121 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW / | Version |
| Order No. | 0560001743 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190990114 | |
| Qty. | 10 pc(s). | |

0 - 9



The CableLine range of wire and cable marker products provides users with solutions for the most diverse applications. The range of applications extends from narrow wires right up to cables with large outside diameters.

General ordering data

| | | |
|------------|----------------------------|-----------------------------|
| Type | CLI R 02-3 GE/SW 2 | Version |
| Order No. | 0560001507 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190083137 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW 1 | Version |
| Order No. | 0560001504 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190046590 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW 8 | Version |
| Order No. | 0560001525 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190154875 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW 3 | Version |
| Order No. | 0560001510 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190046941 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW 6 | Version |
| Order No. | 0560001519 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190019129 | |
| Qty. | 10 pc(s). | |

CLI C 02-3 GE/SW X MP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|-----------------------------|
| Type | CLI R 02-3 GE/SW 0 | Version |
| Order No. | 0560001501 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190063498 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW 9 | Version |
| Order No. | 0560001528 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190141516 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW 5 | Version |
| Order No. | 0560001516 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190188436 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW 7 | Version |
| Order No. | 0560001522 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190185213 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 GE/SW 4 | Version |
| Order No. | 0560001513 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190186081 | |
| Qty. | 10 pc(s). | |

Others



The CableLine range of wire and cable marker products provides users with solutions for the most diverse applications. The range of applications extends from narrow wires right up to cables with large outside diameters.

General ordering data

| | | |
|------------|----------------------------|-----------------------------|
| Type | CLI R 02-3 RT/WS + | Version |
| Order No. | 0560001739 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190990145 | |
| Qty. | 10 pc(s). | |
| Type | CLI R 02-3 BL/WS - | Version |
| Order No. | 0560001741 | CableLine, Mounting mandrel |
| GTIN (EAN) | 4008190990107 | |
| Qty. | 10 pc(s). | |