

**QS 2/12/4****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	Cross-connector (terminal), Plugged, Number of poles: 2, Pitch in mm (P): 12.00, Insulated: Yes, 44 A, beige
Order No.	<a href="#">0270760000</a>
Type	QS 2/12/4
GTIN (EAN)	4008190011420
Qty.	20 pc(s).

QS 2/12/4

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Depth	34.5 mm	Depth (inches)	1.358 inch
Height	20 mm	Height (inches)	0.787 inch
Width	12 mm	Width (inches)	0.472 inch
Net weight	7 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

### Material data

Material	PA 66	Colour	beige
UL 94 flammability rating	V-2		

### System specifications

Version	for cross-connection link
---------	---------------------------

### Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	Plugged		

### Cross-connector

Number of cross-connected terminals	2	Rated current, multi-pole	44 A
Type	Cross-connector		

### Dimensions

Pitch in mm (P)	12 mm
-----------------	-------

### General

Installation advice	Direct mounting	Number of poles	2
---------------------	-----------------	-----------------	---

### Rating data

Rated current	44 A
---------------	------

### Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	20993c56-321a-4ec1-8646-b7d545a927f2

**QS 2/12/4**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	