

**AD 3 SAK4****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Similar to illustration

Warning covers with a flash symbol provide more safety for man and machine. They are used where external voltage must be indicated within the application.

**General ordering data**

|            |  |
|------------|--|
| Version    | Terminal cover, yellow, PVC, Height: 25 mm, Width: 19.5 mm, Depth: 1 mm, V-2 |
| Order No.  | <a href="#">0297600000</a>   |
| Type       | AD 3 SAK4  |
| GTIN (EAN) | 4008190173395  |
| Qty.       | 50 pc(s).  |

**AD 3 SAK4****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 1 mm    | Depth (inches)  | 0.039 inch |
| Height     | 25 mm   | Height (inches) | 0.984 inch |
| Width      | 19.5 mm | Width (inches)  | 0.768 inch |
| Net weight | 0.56 g  |                 |            |

**Temperatures**

|                                  |                |                                  |        |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature              | -25 °C...55 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 100 °C         |                                  |        |

**Material data**

|                           |     |        |        |
|---------------------------|-----|--------|--------|
| Material                  | PVC | Colour | yellow |
| UL 94 flammability rating | V-2 |        |        |

**System specifications**

|         |                            |
|---------|----------------------------|
| Version | End and intermediate plate |
|---------|----------------------------|

**Additional technical data**

|         |    |
|---------|----|
| Snap-on | No |
|---------|----|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002848    | ETIM 7.0    | EC002848    |
| ETIM 8.0    | EC002848    | ETIM 9.0    | EC002848    |
| ECLASS 9.0  | 27-14-11-92 | ECLASS 9.1  | 27-14-11-92 |
| ECLASS 10.0 | 27-14-11-92 | ECLASS 11.0 | 27-14-11-92 |
| ECLASS 12.0 | 27-14-11-92 | ECLASS 13.0 | 27-25-03-90 |

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| REACH SVHC             | /                           |
| RoHS Compliance Status | Compliant without exemption |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                    |   |
|--------------------|---|
| User Documentation | <a href="#">StorageConditionsTerminalBlocks</a> |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>        |

**AD 3 SAK4****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Screws**

Depending on the terminal block or also accessories, we offer different types of screws as additional items or also spare parts.

**General ordering data**

|            |                            |  |
|------------|----------------------------|--|
| Type       | BFSC M3X22 PA/RT           | Version  |
| Order No.  | <a href="#">0128900000</a> | Mounting screw (Terminal), Polyamide 66, Height: 22 mm |
| GTIN (EAN) | 4008190084158              |  |
| Qty.       | 100 pc(s).                 |  |