

IH 2.8 DB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

With insulating sleeve for cable lug, an increase of the rated voltage within the application is possible.

General ordering data

| | |
|------------|-----------------------------|
| | |
| Version | W-Series, Insulating sleeve |
| Order No. | 0386060000 |
| Type | IH 2.8 DB |
| GTIN (EAN) | 4008190043414 |
| Qty. | 100 pc(s). |

IH 2.8 DB

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 5.1 mm | Depth (inches) | 0.201 inch |
| Height | 18 mm | Height (inches) | 0.709 inch |
| Width | 3.6 mm | Width (inches) | 0.142 inch |
| Net weight | 0.18 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|-----------------------|-----------|
| Storage temperature | -25 °C...55 °C | Operating temperature | -50 °C... |
| Continuous operating temp., max. | 120 °C | | |

Material data

| | | | |
|---------------------------|-------|--------|------------|
| Material | Wemid | Colour | dark beige |
| UL 94 flammability rating | V-0 | | |

Additional technical data

| | | | |
|--------------------------|----|---------------------|-----------------|
| Explosion-tested version | No | Installation advice | Direct mounting |
|--------------------------|----|---------------------|-----------------|

General

| | |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

UL rating data

| | |
|----------------------|--------|
| Certificate No. (UR) | E60693 |
|----------------------|--------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002848 | ETIM 7.0 | EC002848 |
| ETIM 8.0 | EC002848 | ETIM 9.0 | EC002848 |
| ECLASS 9.0 | 27-14-11-92 | ECLASS 9.1 | 27-14-11-92 |
| ECLASS 10.0 | 27-14-11-92 | ECLASS 11.0 | 27-14-11-92 |
| ECLASS 12.0 | 27-14-11-92 | ECLASS 13.0 | 27-25-03-90 |

Approvals

Approvals



| | |
|-----------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E60693 |

Downloads

| | |
|---|--|
| Approval/Certificate/Document of Conformity | Confirmation of Standards EN 45545-2_2020-10 |
| Engineering Data | CAD data – STEP |
| User Documentation | StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |