

Q 2 SAK4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

Version	Cross-connector (terminal), when screwed in, grey, 32 A, Number of poles: 2, Pitch in mm (P): 6.00, Insulated: No, Width: 11 mm
Order No.	0336700000
Type	Q 2 SAK4
GTIN (EAN)	4008190033842
Qty.	50 pc(s).

Q 2 SAK4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	20.5 mm	Depth (inches)	0.807 inch
Height	6 mm	Height (inches)	0.236 inch
Width	11 mm	Width (inches)	0.433 inch
Net weight	4.82 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	CuSn	Colour	grey
----------	------	--------	------

System specifications

Version	for cross-connection link
---------	---------------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

Cross-connector

Number of cross-connected terminals	2	Rated current, 2-pole	41 A
Rated current, multi-pole	41 A	Type	Cross-connector

Dimensions

Pitch in mm (P)	6 mm
-----------------	------

General

Installation advice	Direct mounting	Number of poles	2
---------------------	-----------------	-----------------	---

Rating data

Rated current	32 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03
ECLASS 14.0	27-25-03-03		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Q 2 SAK4

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format