

P 18/25 D02 GE SAKS5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

Gauge rings are used to protect against the using of incorrectly selected fuse sizes. They are simply inserted into the respective fuse base and prevent the using of bigger fuses.

General ordering data

| | |
|------------|--|
| Version | Fuse gauge ring (terminal), Height: 11 mm, Depth: 10.5 mm, Aluminium, yellow |
| Order No. | 0361900000 |
| Type | P 18/25 D02 GE SAKS5 |
| GTIN (EAN) | 4008190091101 |
| Qty. | 50 pc(s). |

P 18/25 D02 GE SAKS5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|----------|---------|-----------------|------------|
| Depth | 10.5 mm | Depth (inches) | 0.413 inch |
| Height | 11 mm | Height (inches) | 0.433 inch |
| Diameter | 16.6 mm | Net weight | 0.56 g |

Material data

| | | | |
|----------|-----------|--------|--------|
| Material | Aluminium | Colour | yellow |
|----------|-----------|--------|--------|

System specifications

| | |
|---------|----------------|
| Version | Fuse cartridge |
|---------|----------------|

Additional technical data

| | |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

Dimensions

| | |
|----------|---------|
| Diameter | 16.6 mm |
|----------|---------|

Fuse cartridges

| | | | |
|----------------|----------------|--------|----------------------------|
| Cartridge fuse | E18 | Colour | yellow |
| Current | 25 A | Type | Gauge ring for inserts E18 |
| Version | Fuse cartridge | | 25 A |

General

| | |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

Rating data

| | |
|---------------|------|
| Rated current | 25 A |
|---------------|------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002848 | ETIM 7.0 | EC002848 |
| ETIM 8.0 | EC002848 | ETIM 9.0 | EC002848 |
| ECLASS 9.0 | 27-14-11-92 | ECLASS 9.1 | 27-14-11-92 |
| ECLASS 10.0 | 27-14-11-92 | ECLASS 11.0 | 27-14-11-92 |
| ECLASS 12.0 | 27-14-11-92 | ECLASS 13.0 | 27-25-03-90 |
| ECLASS 14.0 | 27-25-03-90 | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| REACH SVHC | / |
| RoHS Compliance Status | Compliant without exemption |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

P 18/25 D02 GE SAKS5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

| | |
|--------------------|---|
| User Documentation | StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |
| Brochures | |