

IK 35/ZB35 BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

With our accessories for the bus bar taps, you can quickly and easily insulate the tap terminals and visualize the potential through the color coding.

General ordering data

| Version | Terminal (busbar connection) |
|------------|------------------------------|
| Order No. | 0502780000 |
| Type | IK 35/ZB35 BL |
| GTIN (EAN) | 4008190141455 |
| Qty. | 50 pc(s). |

IK 35/ZB35 BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|--------|-----------------|------------|
| Depth | 8.6 mm | Depth (inches) | 0.339 inch |
| Height | 32 mm | Height (inches) | 1.26 inch |
| Width | 14 mm | Width (inches) | 0.551 inch |
| Net weight | 1.34 g | | |

Temperatures

| | | | |
|----------------------------------|--------|----------------------------------|--------|
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 100 °C |
|----------------------------------|--------|----------------------------------|--------|

Material data

| | | | |
|----------|--------------|---------------------------|-----|
| Material | Polyamide 66 | Insulating material | PA |
| Colour | silver | UL 94 flammability rating | V-2 |

System specifications

| | |
|---------|----------------------|
| Version | for busbar 10 x 3 mm |
|---------|----------------------|

Additional technical data

| | |
|---------------------|--------|
| Installation advice | Busbar |
|---------------------|--------|

General

| | | | |
|---------------------|--------|-----------------------------------|--------|
| Installation advice | Busbar | Operating temperature range, max. | 100 °C |
|---------------------|--------|-----------------------------------|--------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000001 | ETIM 7.0 | EC000001 |
| ETIM 8.0 | EC000001 | ETIM 9.0 | EC000001 |
| ECLASS 9.0 | 27-14-11-46 | ECLASS 9.1 | 27-14-11-46 |
| ECLASS 10.0 | 27-14-11-46 | ECLASS 11.0 | 27-14-11-46 |
| ECLASS 12.0 | 27-14-11-46 | ECLASS 13.0 | 27-25-01-16 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|---|
| User Documentation | StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |