

**SCT-C 7.9/360****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

Cable ties are characterised by maximum tying force and a long life. Steel cable ties also offer permanent fastening under extreme conditions such as high temperatures or severe chemical effects.

- Fully coated stainless steel cable ties
- Secure ball locking mechanism for a fast and simple installation
- Can be attached manually or using a tool
- These cables ties are recommended for special applications, such as for use with saline spray, extreme temperatures or corrosive surroundings.

**General ordering data**

Version	Cable ties, 7.9 x 360 mm, Stainless steel, polyester coated, 1112 N
Order No.	<a href="#">1015320000</a>
Type	SCT-C 7.9/360
GTIN (EAN)	4032248724291
Qty.	100 pc(s).

## SCT-C 7.9/360

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	0.26 mm	Depth (inches)	0.01 inch
Height	360 mm	Height (inches)	14.173 inch
Width	7.9 mm	Width (inches)	0.311 inch
Net weight	7.48 g		

## Temperatures

Operating temperature range	-80...150 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	165 °C		

## Installation materials

Bundle diameter, max.	100 mm	Bundle diameter, min.	20 mm
Cable diameter, max.	100 mm	For re-opening	No
Halogen	No	Material	Stainless steel, polyester coated
Operating temperature range, max.	150 °C	Operating temperature range, min.	-80 °C
Tensile strength	1,112 N	Tensile strength (Pound-force)	250 lbf
UV-resistant	No		

## Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ETIM 9.0	EC000046
ECLASS 9.0	27-14-07-02	ECLASS 9.1	27-14-07-02
ECLASS 10.0	27-14-07-02	ECLASS 11.0	27-14-07-02
ECLASS 12.0	27-14-07-02	ECLASS 13.0	27-14-07-02

## Environmental Product Compliance

REACH SVHC /

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E524836

## Downloads

Catalogues [Catalogues in PDF-format](#)

## SCT-C 7.9/360

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

## Drawing

