

SCT-C 7.9/360**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

Cable ties are characterised by maximum tying force and a long life. Steel cable ties also offer permanent fastening under extreme conditions such as high temperatures or severe chemical effects.

- Fully coated stainless steel cable ties
- Secure ball locking mechanism for a fast and simple installation
- Can be attached manually or using a tool
- These cables ties are recommended for special applications, such as for use with saline spray, extreme temperatures or corrosive surroundings.

General ordering data

Version	Cable ties, 7.9 x 360 mm, Stainless steel, polyester coated, 1112 N
Order No.	1015320000
Type	SCT-C 7.9/360
GTIN (EAN)	4032248724291
Qty.	100 pc(s).

SCT-C 7.9/360

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.26 mm	Depth (inches)	0.01 inch
Height	360 mm	Height (inches)	14.173 inch
Width	7.9 mm	Width (inches)	0.311 inch
Net weight	7.48 g		

Temperatures

Operating temperature range	-80...150 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	165 °C		

Installation materials

Bundle diameter, max.	100 mm	Bundle diameter, min.	20 mm
Cable diameter, max.	100 mm	For re-opening	No
Halogen	No	Material	Stainless steel, polyester coated
Operating temperature range, max.	150 °C	Operating temperature range, min.	-80 °C
Tensile strength	1,112 N	Tensile strength (Pound-force)	250 lbf
UV-resistant	No		

Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ETIM 9.0	EC000046
ECLASS 9.0	27-14-07-02	ECLASS 9.1	27-14-07-02
ECLASS 10.0	27-14-07-02	ECLASS 11.0	27-14-07-02
ECLASS 12.0	27-14-07-02	ECLASS 13.0	27-14-07-02

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E524836

Downloads

Catalogues [Catalogues in PDF-format](#)

SCT-C 7.9/360

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing

